
2SD755, 2SD756, 2SD756A

Silicon NPN Epitaxial


HITACHI

Application

- Low frequency high voltage amplifier
- Complementary pair with 2SB715, 2SB716 and 2SB716A

Outline

TO-92MOD



1. Emitter
2. Collector
3. Base

2SD755, 2SD756, 2SD756A

Absolute Maximum Ratings (Ta = 25°C)





Item	Symbol	2SD755	2SD756	2SD756A	Unit
Collector to base voltage	V _{CBO}	100	120	140	V
Collector to emitter voltage	V _{CEO}	100	120	140	V
Emitter to base voltage	V _{EBO}	5	5	5	V
Collector current	I _C	50	50	50	mA
Collector power dissipation	P _C	750	750	750	mW
Junction temperature	T _j	150	150	150	°C
Storage temperature	T _{stg}	−55 to +150	−55 to +150	−55 to +150	°C




Electrical Characteristics (Ta = 25°C)


Item	Symbol	2SD755			2SD756			2SD756A			Unit	Test conditions
		Min	Typ	Max	Min	Typ	Max	Min	Typ	Max		
Collector to emitter breakdown voltage	V _{(BR)CEO}	100	—	—	120	—	—	140	—	—	V	I _C = 1 mA, R _{BE} = ∞
Collector to base breakdown voltage	V _{(BR)CBO}	100	—	—	120	—	—	140	—	—	V	I _C = 10 μA, I _E = 0
Collector cutoff current	I _{CBO}	—	—	0.5	—	—	0.5	—	—	0.5	μA	V _{CB} = 100 V, I _E = 0
DC current transfer ratio	h _{FE1} ^{*1}	250	—	1200	250	—	800	250	—	500		V _{CE} = 12 V, I _C = 2 mA
	h _{FE2}	125	—	—	125	—	—	125	—	—		V _{CE} = 12 V, I _C = 10 mA
Base to emitter voltage	V _{BE}	—	—	0.75	—		0.75	—	—	0.75	V	V _{CE} = 12 V, I _C = 2 mA
Collector to emitter saturation voltage	V _{CE(sat)}	—	—	0.2	—	—	0.2	—	—	0.2	V	I _C = 10 mA, I _B = 1 mA
Gain bandwidth product	f _T	—	350	—	—	350	—	—	350	—	MHz	V _{CE} = 12 V, I _C = 5 mA
Collector output capacitance	Cob	—	1.6	—	—	1.6	—	—	1.6	—	pF	V _{CB} = 25 V, I _E = 0, f = 1 MHz

Note: 1. The 2SD755, 2SD756 and 2SD756A are grouped by h_{FE1} as follows.

	D	E	F
2SD755	250 to 500	400 to 800	600 to 1200
2SD756	250 to 500	400 to 800	—
2SD756A	250 to 500	—	—







Hitachi Code	TO-92 Mod
JEDEC	—
EIAJ	Conforms
Weight (reference value)	0.35 g

Cautions

1. Hitachi neither warrants nor grants licenses of any rights of Hitachi's or any third party's patent, copyright, trademark, or other intellectual property rights for information contained in this document. Hitachi bears no responsibility for problems that may arise with third party's rights, including intellectual property rights, in connection with use of the information contained in this document.
2. Products and product specifications may be subject to change without notice. Confirm that you have received the latest product standards or specifications before final design, purchase or use.
3. Hitachi makes every attempt to ensure that its products are of high quality and reliability. However, contact Hitachi's sales office before using the product in an application that demands especially high quality and reliability or where its failure or malfunction may directly threaten human life or cause risk of bodily injury, such as aerospace, aeronautics, nuclear power, combustion control, transportation, traffic, safety equipment or medical equipment for life support.
4. Design your application so that the product is used within the ranges guaranteed by Hitachi particularly for maximum rating, operating supply voltage range, heat radiation characteristics, installation conditions and other characteristics. Hitachi bears no responsibility for failure or damage when used beyond the guaranteed ranges. Even within the guaranteed ranges, consider normally foreseeable failure rates or failure modes in semiconductor devices and employ systemic measures such as fail-safes, so that the equipment incorporating Hitachi product does not cause bodily injury, fire or other consequential damage due to operation of the Hitachi product.
5. This product is not designed to be radiation resistant.
6. No one is permitted to reproduce or duplicate, in any form, the whole or part of this document without written approval from Hitachi.
7. Contact Hitachi's sales office for any questions regarding this document or Hitachi semiconductor products.

HITACHI

Hitachi, Ltd.

Semiconductor & Integrated Circuits.
Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan
Tel: Tokyo (03) 3270-2111 Fax: (03) 3270-5109

URL	NorthAmerica	:	http://semiconductor.hitachi.com/
	Europe	:	http://www.hitachi-eu.com/hel/ecg
	Asia (Singapore)	:	http://www.has.hitachi.com.sg/grp3/sicd/index.htm
	Asia (Taiwan)	:	http://www.hitachi.com.tw/E/Product/SICD_Frame.htm
	Asia (HongKong)	:	http://www.hitachi.com.hk/eng/bo/grp3/index.htm
	Japan	:	http://www.hitachi.co.jp/Sicd/indx.htm

For further information write to:

Hitachi Semiconductor (America) Inc. 179 East Tasman Drive, San Jose, CA 95134 Tel: <1> (408) 433-1990 Fax: <1> (408) 433-0223	Hitachi Europe GmbH Electronic components Group Dornacher Straße 3 D-85622 Feldkirchen, Munich Germany Tel: <49> (89) 9 9180-0 Fax: <49> (89) 9 29 30 00 Hitachi Europe Ltd. Electronic Components Group. Whitebrook Park Lower Cookham Road Maidenhead Berkshire SL6 8YA, United Kingdom Tel: <44> (1628) 585000 Fax: <44> (1628) 778322
--	---

Hitachi Asia Pte. Ltd. 16 Collyer Quay #20-00 Hitachi Tower Singapore 049318 Tel: 535-2100 Fax: 535-1533 Hitachi Asia Ltd. Taipei Branch Office 3F, Hung Kuo Building. No.167, Tun-Hwa North Road, Taipei (105) Tel: <886> (2) 2718-3666 Fax: <886> (2) 2718-8180
--

Hitachi Asia (Hong Kong) Ltd. Group III (Electronic Components) 7/F., North Tower, World Finance Centre, Harbour City, Canton Road, Tsim Sha Tsui, Kowloon, Hong Kong Tel: <852> (2) 735 9218 Fax: <852> (2) 730 0281 Telex: 40815 HITEC HX
--

Copyright ' Hitachi, Ltd., 1999. All rights reserved. Printed in Japan.