

PRODUCT NUMBER
73324-YXXLF

PLATING, SEE TABLE

LEAD FREE OPTION
SEE NOTE 6

TOTAL NB OF POS

TOP VIEW

NOTE 5

NOTE 5

NOTES:

- 1 - MATERIAL HOUSING: THERMOPLASTIC POLYESTER 30% GLASS FILLED COLOUR BLUE, FLAME RETARDANT PER UL-94 CATEGORY VO.
- 2 - MATERIAL PIN: COPPER ALLOY.
- 3 - MIN PUSH OUT FORCE TERMINAL : 15N
- 4 - MAX PROTUSION 0.3 MAX IN 4 PLACES. IN BOTH DIRECTIONS.
- 5 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS PER ROW, $N \times 2.54 = 20.32\text{mm}$
- 6 - "LF" MEANS THAT THE PRODUCT IS RoHS COMPLIANT THEN MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-47-0004


THERE IS NO NECESSARY A GROOVE
IN EVERY POSITION ON THIS SIDE.

DRILLED HOLE $\phi 1.15 \pm 0.025$ DIA.

COPPER PLATING 0.025 MIN. 0.075 MAX.

TIN/LEAD PLATING 0.005 MIN. 0.015 MAX.

FINISHED HOLE $\phi 0.94$ MIN. $\phi 1.09$ MAX.



$(N \times 2.54) - 0.18 \pm 0.15$

NOTE 5

$(N-1) \times 2.54$


NOTE 5

2.54

$\phi 0.15$

RECOMMENDED HOLE PATTERN

(CONTACT AREA)



mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX HDR			
ltr	ecn no	dr	date	tolerances unless otherwise specified					title PRESS FIT SINGLE ROW				
H	B-19286	AMA	14.11.03	angles	linear								
J	F-21810	AMA	15.06.19										
								scale 1/3					
D	F20102	DLE	02.01.09	dr	P NIZZI		97.06.19		dwg no		sheet 1 of 1	size	
E	F06-0228	LMU	06.07.11	engr	JM PHAMVAN		97.06.19		73324		A3		
F	F06-0298	LMU	06.10.18	chr	P NIZZI		97.06.19						
G	F08-0147	YOV	08.04.14	appd	JMP		97.06.19		type CUSTOMER Drawing				
sheet index		revision sheet											