



LOC	DIST	P	F	REVISIONS					
				ZONE	LTR	DESCRIPTION	DATE	APPD	
DF	X0				L	REV PER 0H14-0170-04	CT	3-9-04	SG

ASSEMBLED VIEW



- FOR USE WITH RG-223/U, 142A/U & 142B/U COAX CABLE.
- FERRULE CRIMPING TOOL: AMP TOOL #220066-1 OR 220066-2 CRIMP B.
- CONTACT CRIMPING TOOL:M22520/2-01 OR AMP TOOL NUMBER 1-601966-6, SETTING NUMBER 5. DANIELS POSITIONER PART NO. K345 OR AMP TOOL NO. 1-601966-6.
- SEE I.S.2348.
- DANIELS MANUFACTURING CORP
2266 FRANKLIN ROAD
BLOOMFIELD HILLS, MI 48013
- OUTER JACKET OF CABLE MUST BE TRIMMED TO ALLOW PROPER INTER-PIN CONTACT LOCATION AFTER FERRULE CRIMP OPERATION.
- PARTS SHIPPED UNASSEMBLED AND CABLE IS SUPPLIED BY CUSTOMER.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 [0.13] ANGLES ± - MATERIAL SEE CALLOUTS FINISH SEE CALLOUTS	DR 9-12-94 C.C.THOMAS	AMP AMP Incorporated Harrisburg, PA 17105-3608		
	CHK 9-23-94 J.CABARLO			
	APPD 9-23-94 J.CABARLO	NAME CONNECTOR, COAXIAL, RF SOCKET SIZE 5, ARINC (HEX CRIMP)		
	RLSE 9-23-94 C.C.THOMAS			
	PRODUCT SPEC -	SIZE C 00779 C=225791-2		
	APPLICATION SPEC -	CAGE CODE 00779		
	WEIGHT -	DRAWING NO C=225791-2		
		SCALE 5:1		
		SHEET 1 OF 1		