




# HERMAPHRODITIC BLADE AND RECEPTACLE CONNECTOR

Wire-to-Board, Board-to-Board and Dust Cover

---

# HERMAPHRODITIC BLADE AND RECEPTACLE CONNECTOR

## WIRE-TO-BOARD

The wire-to-board connector is a plug connector that mates to the latest part number series of the surface mount hermaphroditic blade and receptacle board to board connectors. The connector provides power to the first LED printed circuit board in a string of rigid printed circuit board light strips.

### KEY FEATURES

- Available in 2, 4, and 6 positions
- Connector mates to hermaphroditic blade and receptacle board-to-board part numbers with latching feature
- Positive Latching
- Connector accepts crimp snap contacts
- Contacts accept 18 AWG – 22 AWG stranded wire
- Contacts packaged on 24 inch reels for high speed lead termination
- Housings are bulk packaged
- RoHS compliant
- Custom length wire-to-board cable assemblies are available upon request

### APPLICATIONS

- LED Lighting Controls
- LED Lighting Strips
- Channel Lettering

### ELECTRICAL

- Operating Current : 6 AMPS
- Operating Voltage : 125VAC/125VDC
- Dielectric Withstanding Voltage : 1500VAC

### MECHANICAL

- Operating Temperature: -40°C to +105°C
- Mating cycles: 10

### MATERIALS

- Housings: UL 94 V-0
- Contacts: Tin plated brass

### STANDARDS & SPECIFICATIONS

- Wire-to-Board Application Specification: [114-13252](#)
- Wire-to-Board Product Specification: [108-2387](#)
- UL and cUL recognized : File No. E28476

### APPLICATION TOOLING

- PRO-CRIMPER III Hand Tool (includes die set): [2063778-1](#)
- Die Set for Hand Tool: [2063778-2](#)

For more information visit: [tooling.te.com](http://tooling.te.com)

# HERMAPHRODITIC BLADE AND RECEPTACLE CONNECTOR

## BOARD-TO-BOARD

The hermaphroditic blade and receptacle connector is a latest surface mount technology (SMT) connector and is intended for use with in-line board-to-board applications.

### KEY FEATURES

- Available in 2, 4, and 6 positions
- Connector mates to itself
- Single part to be stocked and placed onto pcb per position
- Connector mates and unmates horizontally and vertically
- Connector can be articulated from 90° to 180°
- Tape and reel packed for high speed SMT processes
- Low profile flat surface is compatible with SMT and reflow processing
- Rounded corners to minimize shadowing
- Redundant SMT pads
- Optional 2, 4 and 6 position dust cover available
- RoHS compliant

### APPLICATIONS

- LED Lighting Controls
- LED Lighting Strips
- Channel Lettering

### ELECTRICAL

- Operating Current : 6 AMPS
- Operating Voltage : 125VAC/125VDC
- Dielectric Withstanding Voltage : 1500VAC

### MECHANICAL

- Operating Temperature: -40°C to +105°C

### MATERIALS

- Housings: UL 94V-0 high temperature resistant thermoplastic
- Contacts: Copper Alloy, tin over nickel plated
- Dust Cover : Polybutylene terephthalate (PBT)

### STANDARDS & SPECIFICATIONS

- Board-to-Board Application Specification: [114-13225](#)
- Board-to-Board Product Specification: [108-2342](#)
- UL and cUL recognized : File No. E28476

## PRODUCT OFFERING

### Blade and Receptacle SMT Connectors


| Part Number                 | Position | Color |
|-----------------------------|----------|-------|
| <a href="#">2058703-1</a>   | 2        | White |
| <a href="#">2058703-2</a>   | 4        | White |
| <a href="#">2058703-3</a>   | 6        | White |
| <a href="#">1-2058703-1</a> | 2        | Black |
| <a href="#">1-2058703-2</a> | 4        | Black |
| <a href="#">1-2058703-3</a> | 6        | Black |

### Dust Cover


| Part Number                 | Position | Color   |
|-----------------------------|----------|---------|
| <a href="#">2058128-1</a>   | 2        | Natural |
| <a href="#">2058128-2</a>   | 4        | Natural |
| <a href="#">2058128-3</a>   | 6        | Natural |
| <a href="#">1-2058128-1</a> | 2        | Black   |
| <a href="#">1-2058128-2</a> | 4        | Black   |
| <a href="#">1-2058128-3</a> | 6        | Black   |

PRODUCT DIMENSIONS

Board-to-Board



Dust cover



PRODUCT OFFERING AND DIMENSIONS


Wire-to-Board

Housings

| Part Number                 | Position | Color   |
|-----------------------------|----------|---------|
| <a href="#">2058299-1</a>   | 2        | Natural |
| <a href="#">2058299-2</a>   | 4        | Natural |
| <a href="#">2058299-3</a>   | 6        | Natural |
| <a href="#">1-2058299-1</a> | 2        | Black   |
| <a href="#">1-2058299-2</a> | 4        | Black   |
| <a href="#">1-2058299-3</a> | 6        | Black   |

Contacts

|                           |                              |
|---------------------------|------------------------------|
| <a href="#">2058301-1</a> | Blade Contact                |
| <a href="#">2058301-2</a> | Blade Contact - Loose Piece  |
| <a href="#">2058302-1</a> | Socket Contact               |
| <a href="#">2058302-2</a> | Socket Contact - Loose Piece |



---

## TE TECHNICAL SUPPORT CENTER

|                   |                       |
|-------------------|-----------------------|
| Internet:         | te.com/help           |
| USA:              | +1 (800) 522-6752     |
| Canada:           | +1 (905) 475-6222     |
| Mexico            | +52 (0) 55-1106-0800  |
| Latin/S. America: | +54 (0) 11-4733-2200  |
| Germany:          | +49 (0) 6251-133-1999 |
| UK:               | +44 (0) 800-267666    |
| France:           | +33 (0) 1-3420-8686   |
| Netherlands:      | +31 (0) 73-6246-999   |
| China:            | +86 (0) 400-820-6015  |

---

## [te.com/hermaphroditic-connectors](https://te.com/hermaphroditic-connectors)

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

©2025 TE Connectivity. All Rights Reserved.

06-25