





NOTES:
1. ALL DIMENSIONS FOR REFERENCE ONLY.
2. 0.250 MAXIMUM PANEL THICKNESS.
3. SOLDER TERMINALS MAY BE SOLDERED TO PC BOARD.

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					UNLESS OTHERWISE SPECIFIED	SIZE	WIDTH	MULT	LBS/M	TEMPER
					1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.	FINISH		MATERIAL		
					2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002	SPEC No.		SPEC No.		
					3. REMOVE ALL BURRS	FIRST USED ON		SCALE 2:1		Switchcraft®
L		ECO #22413	8-13-98	RC	EBR	DATE DRAWN	BY	CHKD	APVD	
REV		ECO NUMBER	DATE	BY	APVD	4-JUNE-79	JZG	CD 9-10-79	PN 5-22-80	SHEET 1 OF 1
REVISIONS					DO NOT SCALE DRAWING	NAME TINI Q-G MALE CHASSIS PANEL MOUNT RECEPTACLE				PART No. TB_M SERIES
										REV L

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[TB6M](#) [TB4M](#) [TB5M](#) [TB3MB](#) [TB4MB](#) [TB5MB](#) [TB7M](#) [TB8M](#) [TB3M](#)