

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 854751

RoHS COMPLIANT



BOURNS®

Features

- SMD Single-Turn / Cermet / Industrial Open Frame
- Cross slot rotor designs suitable for automatic adjustment equipment
- Supplied in 12 mm embossed tape, compatible with automatic pick-and-place assembly equipment
- Recommended for reflow solder processing only
- RoHS compliant* - see [processing information](#) on lead free surface mount trimmers

3364 - 4 mm Square Trimming Potentiometer

Electrical Characteristics

Standard Resistance Range
.....100 ohms to 1 megohm
(see standard resistance table)
Resistance Tolerance $\pm 25\%$ std.
End Resistance
 <1K20 ohms max.
 >1K2 %
Contact Resistance Variation
(Voltage Divider)5 % max.
Resolution.....Infinite
Adjustment Angle..... $260^\circ \pm 20^\circ$

Environmental Characteristics

Power Rating (50 volts max.)
 70 °C0.2 watt
Temperature Range-40 °C to +100 °C
Temperature Coefficient ± 250 ppm/°C
Humidity500 hours (5 % Δ TR)
Load Life500 hours
 0.2 watt @ 70 °C (5 % Δ TR)
Rotational Life20 cycles (15% Δ TR)

Physical Characteristics




Torque20 to 200 g-cm
Mechanical AngleContinuous
MarkingResistance code,
 manufacturer's full part number
 and date code on packaging
Terminals.....Solder coated
Standard Packaging
 1000 pcs./7 " reel
Adjustment ToolH-90
Reflow solder processing recommended

How To Order


3364 X - 1 - 103 E

Model _____
Style _____
Orientation of parts in tape:
 Styles W,A
 Terminals toward sprocket holes
 Styles X,B
 Terminals away from sprocket holes
Standard Product _____
Resistance Code _____
Embossed Tape Designator _____
 E = 1000 pcs./7 " reel (-1 standard)
 G = 5000 pcs./14.5 " reel (-1 optional)
Consult factory for other available options.




Common Dimensions 3364W, X 3-Terminal




SUGGESTED PWB LAYOUT



3364A, B 3-Terminal



SUGGESTED PWB LAYOUT



TOLERANCES: ± 0.25 (.010) EXCEPT WHERE NOTED



DIMENSIONS ARE: $\frac{\text{MM}}{\text{(INCHES)}}$

*RoHS Directive 2002/95/EC Jan 27 2003 including Annex.
Specifications are subject to change without notice.
Customers should verify actual device performance in their specific applications.

3364 - 4 mm Square Trimming Potentiometer

BOURNS®

Packaging Specifications



Conforms with EIA specification RS-481.

Standard Resistance Table

Resistance (Ohms)	Resistance Code	Part Marking
100	101	12
200	201	22
500	501	52
1,000	102	13
2,000	202	23
5,000	502	53
10,000	103	14
20,000	203	24
50,000	503	54
100,000	104	15
200,000	204	25
500,000	504	55
1,000,000	105	16

Popular distribution resistance values listed in boldface.