




- 1 HOUSING MATERIAL: GLASS-FILLED POLYMER.
- 2 POST MATERIAL: COPPER ALLOY.
- 3 POST FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON POSTS.
- 4 [PART NUMBER, DATE CODE] MARKED THIS APPROXIMATE AREA.
- 5 MARKING ON THIS SIDE.
- 6 RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR ONTO PC BOARD.
- 7 CONTACT AREA FINISH: 0.00076 [.000030] MIN GOLD OVER 0.00127 [.000050] MIN NICKEL. TAIL FINISH: 0.0025 [.000100] MIN MATTE TIN OVER 0.00127 [.000050] MIN NICKEL.
- 8 CONTACT AREA FINISH: 0.00127 [.000050] MIN GOLD OVER 0.00127 [.000050] MIN NICKEL. TAIL FINISH: 0.0025 [.000100] MIN MATTE TIN OVER 0.00127 [.000050] MIN NICKEL.

SUPERSEDED BY 5650473-5		1-32	X	X	X	-	96	7-5650473-5
		1-32	X	X	X	7	96	5650473-6
		1-32	X	X	X	3	96	5650473-5
		1-32	X	X	X	8	96	5650473-1
POSITIONS LOADED			C	B	A	FINISH	NO. OF LOADED POSITIONS	PART NUMBER
			ROWS LOADED					

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE OSMAYOS	TE TE Connectivity							
		CHK A. SHARPE OSMAYOS								
		APVD A. SHARPE OSMAYOS								
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME ASSEMBLY, PIN EUROCARD, TYPE C, 96 POSITION, .104 SOLDER POST							
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC - APPLICATION SPEC -				SIZE A1	CAGE CODE 00779	DRAWING NO 5650473	RESTRICTED TO -
MATERIAL	FINISH	WEIGHT -	CUSTOMER DRAWING							
12		3	SCALE 5:1 SHEET 1 OF 1 REV C							