

REVISIONS					
P	LTR	DESCRIPTION		DATE	DWN APVD
	AA	REVISED PER	ECO-16-011265	12AUG2016	NK MZ

D

C

B





A

D

C

B


A



RECOMMENDED PC BOARD LAYOUT

- 1 NYLON, UL 94V-0 RATED, RED.
- 2 BRASS PER ASTM B36.
- 3 3.81um [.000150] MIN TIN-LEAD OVER 2.54um [.000100] MIN COPPER OR 1.27um [.000050] MIN NICKEL.
- 4 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 5 0.38um [.000015] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 6 .000150 MIN TIN OVER .000100 MIN COPPER OR .000050 MIN NICKEL.
- 7 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

11.79[.464]	4.60±0.64[.181±.025]	YES	7	NO	1-206763-4
11.79[.464]	4.60±0.64[.181±.025]	YES	7	YES	1-206763-3
11.79[.464]	4.60±0.64[.181±.025]	YES	6	NO	1-206763-2
11.79[.464]	4.60±0.64[.181±.025]	YES	6	YES	1-206763-1
OBSOLETE	11.79[.464]	4.60±0.64[.181±.025]	NO	YES	206763-9
OBSOLETE	13.31[.524]	4.60±0.64[.181±.025]	YES	NO	206763-8
11.79[.464]	4.60±0.64[.181±.025]	YES	4	NO	206763-4
11.79[.464]	4.60±0.64[.181±.025]	YES	4	YES	206763-3
11.79[.464]	4.60±0.64[.181±.025]	YES	3	NO	206763-2
11.79[.464]	4.60±0.64[.181±.025]	YES	3	YES	206763-1
B		A	LATCHES	CONTACT FINISH	MOUNTING TABS
					PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN L.SIPE 03/11/92	 TE Connectivity			
DIMENSIONS: mm [INCHES]			CHK R.STONE 3-17-92				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD A. TRAVIS 3-17-92		NAME			
		PRODUCT SPEC 108-10033		PIN HEADER ASSEMBLY, 24 POSITION, METRIMATE			
		APPLICATION SPEC					
		MATERIAL HOUSING: 1		FINISH CONTACT: SEE TABLE	SIZE A1	CAGE CODE 00779	DRAWING NO 206763
		WEIGHT -					
		CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1	REV AA	