


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

BANDING PART NUMBER	COIL BAND WIDTH ±.010" [0.25]	MAT'L TYPE	MAT'L COATING	REQ'D. BANDING HEAD PART NUMBER	MAT'L LENGTH	MAT'L THICKNESS ±.001" [0.03]	MAT'L EDGES
MBS-TLR	.173 [4.39]	304	-----	MTHS-C	250.0' [76.2m]	.010" [.25]	NOTE 5
MBH-TLR	.312 [7.92]	304	-----	MTHH-C	250.0' [76.2m]	.010" [.25]	NOTE 5
MBS-TLR316	.173 [4.39]	316	-----	MTHS-C316	250.0' [76.2m]	.010" [.25]	NOTE 5
MBH-TLR316	.312 [7.92]	316	-----	MTHH-C316	250.0' [76.2m]	.010" [.25]	NOTE 5
MBCH-QR316	.312" [7.93]	316	POLYESTER	MTHCH-C316	82.5' [25.0m]	.010" [.25]	NOTE 6



NOTES:

1. INSTALLATION TOOLS:
PPTMT, GS4MT, ST2MT, HTMT & ST3MT.
2. UNLESS OTHERWISE SPECIFIED,
DIMS IN [] ARE IN mm
3. SEE TABLE FOR COMPATIBLE
BANDING HEAD PART NUMBERS.
4. TOLERANCES UNLESS OTHERWISE SPECIFIED:
.X ± .13 [3.30]
5. FULLY ROUNDED EDGES.
6. FULLY COATED MATERIAL.
COATING THICKNESS:
.003"/.007" [.08/.18] PER SIDE

						TITLE		
						STAINLESS STEEL METAL BANDING CONTINUOUS		
						CUSTOMER DRAWING		
						ITEM REVISION NAME		
						N41194BS/03		
						DATASET FILE NAME		
						N41194BS_DC/03A		
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		
						.x ± .1 [2.54] .xxx ± .005 [.127]		
						.xx ± .01 [.25] ANGLES ± 5 °		
						THIRD ANGLE PROJECTION		
						DRAWING NUMBER: N41194BS_DC		
						DRAWN BY DATE CHK SCALE		
						JAMB 10/04 EJD NONE		
						SHT 1 OF 1		
						SIZE		
						A		