





- Wide Array of DIP Jumper Configurations
- Reliable, Electronically-tested Solder Connections
- Strain Relief by Ultrasonically-welded Protective Covers
- Easy Identification and Tracing with 10-color Cable



Centers “C”	Dim. “D”	Dim. “H”	Available Sizes
0.300 [7.62]	0.395 [10.03]	0.390 [9.90]	8, 14, 16, 18, 20
0.400 [10.16]	0.495 [12.57]	0.490 [12.45]	22
0.600 [15.24]	0.695 [17.65]	0.690 [17.54]	24, 28, 40



"A" = (No. of Conductors x 0.050 [1.27]) + 0.095 [2.41]
 "B" = (No. of Conductors - 1) x 0.050 [1.27]
 "E" = (No. of Conductors + 1) x 0.050 [1.27]
 "F" = (No. of Conductors - 1) x 0.050 [1.27]

Technical drawing of a 16-pin connector assembly showing three views: front, side, and top. Dimensions are in inches and millimeters. Key features include a .040 inch thick top plate, .015 inch thick side rails, and a .150 inch thick base. The drawing specifies a .003 inch tolerance for the top plate thickness and a .003 inch tolerance for the side rail thickness. The drawing also shows a .019 inch thick potting layer and a .100 inch thick base. The drawing includes a note "PIN NO. 11.D. W/ CHAMFER" and a note "TOL. NON-CUM."

vers

**HEADER
DETAIL**

"A"

4 3 2 1

PIN NO. 1 I.D.
W/ CHAMFER

5 6 7 8

.019 ± .002
[.48 ± .05]

.270
[6.86]

"D"

.015 ± .002
[.38 ± .05]

.100 ± .003
[2.54 ± .08]

"C"

± .003 [.08]

TOL. NON-CUM.

"B"













± .003 [.08]

.150 [3.81]

11012
Rev. 6.1
1 of 2



Series 200 thru 216 Male/Female DIP Jumpers



ALL DIMENSIONS: INCHES [MILLIMETERS]
ALL TOLERANCES: ± 0.005 [0.13] UNLESS OTHERWISE SPECIFIED
CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS

CUSTOMIZATION: ARIES SPECIALIZES IN CUSTOM DESIGN AND PRODUCTION.
SPECIAL MATERIALS, PLATINGS, SIZES, AND CONFIGURATIONS CAN BE
FURNISHED, DEPENDING ON QUANTITY.

ARIES RESERVES THE RIGHT TO CHANGE PRODUCT GENERAL SPECIFICATIONS
WITHOUT NOTICE

PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE
CONSIDERED UNCONTROLLED



ARIES
ELECTRONICS, INC.

2609 Bartram Road • Bristol, PA 19007-6810 USA
TEL 215-781-9956 • FAX 215-781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



11012
Rev. 6.1
2 of 2