

MATERIALS AND FINISHES





BODY ZINC ALLOY
PLATED SEE TABLE

OUTER CONTACT BERYLLIUM COPPER
PLATED GOLD (10 MICROINCHES MIN)

CENTER CONTACT BRASS
PLATED GOLD (10 MICROINCHES MIN)

INSULATOR TEFLON

FERRULE BRASS
PLATED SEE TABLE



PART # SEE TABLE

73366-0301	GOLD (1 MICROINCHES MIN)
73366-0300	NICKEL (70 MICROINCHES MIN)
PART NO.	PLATING

AS-73392-0060	CABLE ASSEMBLY INSTR.
SPECIFICATION	DESCRIPTION

UNLESS OTHERWISE SPECIFIED DIMS
ARE MILLIMETERS AND ANGLES ARE DEGREES.

- ALL OVER.
- NO CHATTER OR NON-UNIFORM
SURFACE FINISH ALLOWED.
- PARTS TO BE FREE OF BURRS
& SHARP EDGES 0.13(.005) MAX BREAK.
- EXTERNAL THREADS TO BE ROLLED
OR SINGLE POINT.
- DIAMETERS TO BE CONCENTRIC
WITHIN 0.08(.003) TIR.

CHG: LOADED INTO
WORKMANAGER
REDREW IN SD
CHANGED ALL DIMS
FROM IN/MM TO MM/IN
ADDED CABLED AND
ISO VIEWS
ADDED PLATING
THICKNESSES
REMOVED SHEET 2
ADDED PLATING
TABLE
ADDED AS-73392-0060

EC NO: URF2005-0227
DRWN: TELAHRT 2004/12/02
CHKD: SSHAH 2004/12/02
APPR: JWIENER 2004/12/02
REV
A1

QUALITY
SYMBOLS
=0
=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .003	± .0003
2 PLACES	± .002	± .0002
1 PLACE	± .001	± .0001

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY DATE
CLAIRE 2001/04/02

CHECKED BY DATE

APPROVED BY DATE

MATERIAL NO.
SEE TABLE

SIZE
C

SCALE
DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
MCX PLUG, STR. FOR RG316
50 OHMS, CRIMP/CRIMP
EWR-2672 MCX-PC

MOLEX INCORPORATED

DOCUMENT NO.
SD-73366-030

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION