



SS Series

Features

- 85°C, 1,000 hours assured
- Standard micro miniature size with 5mm height
- RoHS Compliance



Sleeve & Marking Color: Black & White



Specifications

Items	Performance																																							
Category Temperature Range	-40℃ ~ +85℃																																							
Capacitance Tolerance	±20% (at 120Hz, 20℃)																																							
Leakage Current (at 20℃)	I = 0.01CV or 3 (μA) whichever is greater (after 2 minutes) Where, C = rated capacitance in μF V = rated DC working voltage in V																																							
Tanδ (at 120Hz, 20℃)	<table><tr><td>Rated Voltage</td><td>4</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>Tanδ (max)</td><td>0.35</td><td>0.25</td><td>0.20</td><td>0.17</td><td>0.15</td><td>0.13</td><td>0.10</td></tr></table>								Rated Voltage	4	6.3	10	16	25	35	50	Tanδ (max)	0.35	0.25	0.20	0.17	0.15	0.13	0.10																
Rated Voltage	4	6.3	10	16	25	35	50																																	
Tanδ (max)	0.35	0.25	0.20	0.17	0.15	0.13	0.10																																	
Low Temperature Characteristics (at 120Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td colspan="2">Rated Voltage</td><td>4</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td rowspan="2">Impedance Ratio</td><td>Z(-25℃)/Z(+20℃)</td><td>7</td><td>6</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z(-40℃)/Z(+20℃)</td><td>15</td><td>12</td><td>8</td><td>6</td><td>4</td><td>4</td><td>4</td></tr></table>								Rated Voltage		4	6.3	10	16	25	35	50	Impedance Ratio	Z(-25℃)/Z(+20℃)	7	6	4	3	2	2	2	Z(-40℃)/Z(+20℃)	15	12	8	6	4	4	4						
Rated Voltage		4	6.3	10	16	25	35	50																																
Impedance Ratio	Z(-25℃)/Z(+20℃)	7	6	4	3	2	2	2																																
	Z(-40℃)/Z(+20℃)	15	12	8	6	4	4	4																																
Endurance	<table><tr><td>Test Time</td><td colspan="7">1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td colspan="7">Within ±30% of initial value for 4 ~ 6.3V; Within ±25% of initial value for 10 ~ 50V</td></tr><tr><td>Tanδ</td><td colspan="7">Less than 200% of specified value</td></tr><tr><td>Leakage Current</td><td colspan="7">Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20℃ after the rated voltage applied with rated ripple current for 1,000 hours at 85℃.								Test Time	1,000 Hrs							Capacitance Change	Within ±30% of initial value for 4 ~ 6.3V; Within ±25% of initial value for 10 ~ 50V							Tanδ	Less than 200% of specified value							Leakage Current	Within specified value						
Test Time	1,000 Hrs																																							
Capacitance Change	Within ±30% of initial value for 4 ~ 6.3V; Within ±25% of initial value for 10 ~ 50V																																							
Tanδ	Less than 200% of specified value																																							
Leakage Current	Within specified value																																							
Shelf Life Test	Test time: 500 hours; other items are the same as those for the Endurance.																																							
Ripple Current & Frequency Multipliers	<table><tr><td> Freq.(Hz) Cap.(μF) </td><td>60 (50)</td><td>120</td><td>500</td><td>1k</td><td>10k up</td></tr><tr><td>Under 47</td><td>0.75</td><td>1.00</td><td>1.15</td><td>1.34</td><td>1.50</td></tr><tr><td>100 to 330</td><td>0.80</td><td>1.00</td><td>1.08</td><td>1.20</td><td>1.30</td></tr></table>								Freq.(Hz) Cap.(μF)	60 (50)	120	500	1k	10k up	Under 47	0.75	1.00	1.15	1.34	1.50	100 to 330	0.80	1.00	1.08	1.20	1.30														
Freq.(Hz) Cap.(μF)	60 (50)	120	500	1k	10k up																																			
Under 47	0.75	1.00	1.15	1.34	1.50																																			
100 to 330	0.80	1.00	1.08	1.20	1.30																																			

Diagram of Dimensions

1. $\phi D = 3\text{mm}$ 2. $\phi D \geq 4\text{mm}$

Unit: mm



Lead Spacing and Diameter

ϕD	3	4	5	6.3	8
P	1.0	1.5	2.0	2.5	2.5
ϕd	0.4	0.45			
α	1.0				
β	0.5				

Dimension & Permissible Ripple Current

Dimension: $\phi D \times L(\text{mm})$

Ripple Current: mA/rms at 120 Hz, 85°C

V. DC	4V (0G)	6.3V (0J)	10V (1A)	16V (1C)	25V (1E)	35V (1V)	50V (1H)
μF	Contents	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
0.33	R33						
0.47	R47						
1	010						
2.2	2R2						
3.3	3R3						
4.7	4R7						
10	100						
22	220						
33	330						
47	470						
100	101						
220	221						
330	331						

Part Numbering System

SS series	330μF	±20%	6.3V	Bulk Package	Gas Type	8 ϕ × 5L	Pb-free and PET sleeve
SS-	331	M	0J	BK	-	0805	
Series	Capacitance	Capacitance Tolerance	Rated Voltage	Lead Configuration & Package	Rubber Type	Case Size	Lead Wire and Sleeve type

Note: For more details, please refer to "Part Numbering System (Radial Type)" on page 11.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lelon:

<u>SS010M1HBK-0405P</u>	<u>SS010M1HBK-0305P</u>	<u>SS0R1M1HBK-0305P</u>	<u>SS0R33M1HBK-0305P</u>	<u>SS0R47M1HBK-0305P</u>
<u>SS2R2M1VBK-0305P</u>	<u>SS3R3M1EBK-0305P</u>	<u>SS4R7M1CBK-0305P</u>	<u>SS0R1M1HBK-0405P</u>	<u>SS100M1ABK-0405P</u>
<u>SS100M1CBK-0405P</u>	<u>SS100M1EBK-0505P</u>	<u>SS100M1HBK-0605P</u>	<u>SS100M1VBK-0505P</u>	<u>SS101M0JBK-0605P</u>
<u>SS101M1ABK-0605P</u>	<u>SS101M1CBK-0805P</u>	<u>SS101M1EBK-0805P</u>	<u>SS220M1CBK-0505P</u>	<u>SS220M1EBK-0605P</u>
<u>SS220M1HBK-0605P</u>	<u>SS220M1VBK-0605P</u>	<u>SS221M0JBK-0805P</u>	<u>SS221M1ABK-0805P</u>	<u>SS2R2M1HBK-0405P</u>
<u>SS2R2M1VBK-0405P</u>	<u>SS330M1CBK-0505P</u>	<u>SS3R3M1EBK-0405P</u>	<u>SS3R3M1VBK-0405P</u>	<u>SS470M0JBK-0505P</u>
<u>SS470M1CBK-0605P</u>	<u>SS470M1EBK-0605P</u>	<u>SS470M1VBK-0805P</u>	<u>SS4R7M1CBK-0405P</u>	<u>SS4R7M1EBK-0405P</u>
<u>SS4R7M1HBK-0505P</u>	<u>SS4R7M1VBK-0405P</u>	<u>SS4R7M1VBK0405</u>		