

Honeywell Sensing and Control

Home > Products > Linear and Rotary Potentiometric Sensors > SLF > Product Page

SLW03N4500B6A



Actual product appearance may vary.

Short LongFellow Linear Position Transducer, Water Resistant, 76,2 mm [3.0 in] Electrical Travel, Binder Series 681 Termination, Item Number F56203103

Features

MystR² plastic elements - Tested up to one billion operations
Precious metal wipers - Insures high performance, low noise
.081" thick housing with 6 mm shaft - Rugged construction for manufacturing environment
High performance bearings - Long life even with side load conditions
Shaft seals - Protects internal components from factory environment
Absolute continuous measurement - Accurate position at power -up
High level DC output Works with simple controls

Potential Applications

Injection molding machines
Printing presses
Meat packing equipment
Drill presses
Woodworking machines
Cranes
Front-end loaders

Description

The Short Longfellow is frequently used for measuring linear position or displacement up to 6" on a wide variety of manufacturing and process equipment. The mechanical design of the unit's front bearing, anodized extruded aluminum housing, stainless steel shaft and precious metal wipers are suitable for a factory's harsh environment.

Based on the proprietary MystR² conductive plastic film, it provides a high resolution, absolute position measurement without external signal conditioners. Intrinsically safe for Class I, II and III Division I, Groups A, B, C, D, E, F and G for hazardous (indoor/outdoor) NEMA 4 locations. V max.=30 V, I max.=100 mA, Ci=0, Li=0mH.

Supporting Documentation

Dimensions

Circuitry

Product Specifications	
Supply Voltage	40 Vdc max.
Measurement Type	Linear
Housing Size	125,7 mm [4.95 in]
Total Mechanical Travel	80,0 mm [3.15 in]
Electrical Travel	76,2 mm [3.0 in]
Starting Force (max.)	2,27 kg [5.0 lb]
Linearity	± 0.1 %
Backlash	0,025 mm [.001 in]
Bearing Type	Sleeve
Shaft Material	Stainless Steel
Shaft Diameter	1/4 in - 28 NF -2A thread
Type of Element	MystR [®] conductive plastic film
Housing Style	Anodized Aluminum
Termination	Binder Series 681
Wiper Current	<1 µ A
Resolution	Infinite
Operating Temperature Range	-65 °C to 105 °C [-85 °F to 221 ° F]
Vibration	20 g / 0,75 mm (rms) 5 hz to 2 khz
Shock	50 g 11 ms half sine
Operating Life	one billion dither operations
Total Resistance	4,500 Ohms
Resistance Tolerance	± 20 %
Weight (Ranges)	164 g [0.36 lb]
Sealing	NEMA 4 - Water Resistant
UNSPSC Code	41111945
UNSPSC Commodity	41111945 Linear position sensors
Availability	Global
Comments	Note; Mating Connector, Item Number E02903021, Sold Separately. Options; Electrical Travel, Total Resistance, Linearity, Rod End Bearing, Ball Joint Assembly, Shaft Thread (M6 x 1 Metric), Dual Elements
Series Name	SLF



My Links

[Login to iCOM](#)
[Login as Rep/AD](#)
[Login as Guest](#)
[Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search

▼ Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback