

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

IXE21

M

DRAWING
NUMBER

8

ISSUE

3

REVISIONS

A	CO	51198
GRT	2 APR 82	
B	CO-	57673
AMM	21 MAY 85	

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

REPLACES X72420-XE

RELEASE NO. PR-10598

CHECK

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK




NOTES

- 1 MOUNTING HOLES WILL ACCEPT $.087$ MAX DIA PINS OR SCREWS ON $.188 \pm .002$ CENTERS
- 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3 WEIGHT OF SWITCH ONLY IS $.16$ OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS $.55$ OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE 2:1
OPERATING FORCE ----- 5-17 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 4 OZ MIN	28 VOLTS DC RATING	TOLERANCES
RELEASE TRAVEL ----- .004 MIN	INDUCTIVE ----- SEA LEVEL ----- 4 AMP	APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±
DIFFERENTIAL TRAVEL ----- .005 MAX	RESISTIVE ----- 50,000 FT ----- 2.5 AMP	DIM. TOL. DIM. TOL.
OVERTRAVEL ----- .004 MIN	LAMP ----- SEA LEVEL ----- 7 AMP	NO PLACES X 1/64 X X 0.01/018 X X 0.01/008 X X 0.01/005
	MOTOR ----- 50,000 FT ----- 7 AMP	ONE PLACE X X 0.01/018 X X 0.01/008 X X 0.01/005
	LAMP ----- SEA LEVEL ----- 1 AMP	TWO PLACES X, XX 0.01/018 X, XX 0.01/008 X, XX 0.01/005
	MOTOR ----- SEA LEVEL ----- 2.5 AMP	THREE PLACES X, XXX 0.01/018 X, XXX 0.01/008 X, XXX 0.01/005
	115 V 400 CYCLES ----- SEA LEVEL	ANGLES
	RESISTIVE ----- 7 AMP	
	INDUCTIVE ----- 4 AMP	
	LAMP ----- 1 AMP	
	MOTOR ----- 1.5 AMP	

DESIGN UNITS	SI METRIC	US CUSTOMARY
	☐	☒
WEIGHT	3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1XE21](#)