

SKKT 210, SKKH 210



SEMIPACK® 3

Thyristor / Diode Modules

SKKT 210

SKKH 210

Features

- Heat transfer through aluminium nitride ceramic isolated metal baseplate
- Precious metal pressure contacts for high reliability
- Thyristor with amplifying gate
- UL recognized, file no. E 63 532


Typical Applications

- DC motor control
(e. g. for machine tools)
- AC motor starters
- Temperature control
(e. g. for ovens, chemical processes)
- Professional light dimming
(studios, theaters)

- 1) See the assembly instructions
- 2) The screws must be lubricated

V_{RSM} V	V_{RRM}, V_{DRM} V	$I_{TRMS} = 350$ A (maximum value for continuous operation) $I_{TAV} = 210$ A (sin. 180; $T_c = 90$ °C)		
900	800	SKKT 210/08E		
1300	1200	SKKT 210/12E	SKKH 210/12E	
1500	1400	SKKT 210/14E	SKKH 210/14E	
1700	1600	SKKT 210/16E	SKKH 210/16E	
1900	1800	SKKT 210/18E	SKKH 210/18E	
2100	2000	SKKT 210/20E H4	SKKH 210/20E H4	
2300	2200	SKKT 210/22E H4	SKKH 210/22E H4	







Symbol	Conditions	Values	Units
I_{TAV}	sin. 180; $T_c = 85$ (100) °C	230 (167)	A
I_D	P16/200F; $T_a = 35$ °C; B2 / B6	420 / 550	A
I_{RMS}	P16/200F; $T_a = 35$ °C; W1 / W3	526 / 3 * 440	A
I_{TSM}	$T_{vj} = 25$ °C; 10 ms	8500	A
	$T_{vj} = 130$ °C; 10 ms	7500	A
i^2t	$T_{vj} = 25$ °C; 8,3 ... 10 ms	361000	A²s
	$T_{vj} = 130$ °C; 8,3 ... 10 ms	281000	A²s
V_T	$T_{vj} = 25$ °C; $I_T = 750$ A	max. 1,5	V
$V_{T(TO)}$	$T_{vj} = 130$ °C	0,95	V
r_T	$T_{vj} = 130$ °C	0,6	mΩ
I_{DD}, I_{RD}	$T_{vj} = 130$ °C; $V_{RD} = V_{RRM}, V_{DD} = V_{DRM}$	max. 50	mA
t_{gd}	$T_{vj} = 25$ °C; $I_G = 1$ A; $di_G/dt = 1$ A/μs	1	μs
t_{gr}	$V_D = 0,67 * V_{DRM}$	2	μs
$(di/dt)_{cr}$	$T_{vj} = 130$ °C	max. 250	A/μs
$(dv/dt)_{cr}$	$T_{vj} = 130$ °C	max. 1000	V/μs
t_q	$T_{vj} = 130$ °C	50 ... 150	μs
I_H	$T_{vj} = 25$ °C; typ. / max.	150 / 500	mA
I_L	$T_{vj} = 25$ °C $R_G = 33$ Ω; typ. / max.	300 / 2000	mA
V_{GT}	$T_{vj} = 25$ °C; d.c.	min. 3	V
I_{GT}	$T_{vj} = 25$ °C; d.c.	min. 200	mA
V_{GD}	$T_{vj} = 130$ °C; d.c.	max. 0,25	V
I_{GD}	$T_{vj} = 130$ °C; d.c.	max. 10	mA
$R_{th(j-c)}$	cont.; per thyristor / per module	0,14 / 0,07	K/W
$R_{th(j-c)}$	sin. 180; per thyristor / per module	0,15 / 0,075	K/W
$R_{th(j-c)}$	rec. 120; per thyristor / per module	0,165 / 0,083	K/W
$R_{th(c-s)}$	per thyristor / per module	0,04 / 0,02	K/W
T_{vj}		- 40 ... + 130	°C
T_{stg}		- 40 ... + 130	°C
V_{isol}	a. c. 50 Hz; r.m.s.; 1 s / 1 min.	3600 / 3000	V~
V_{isol}	a. c. 50 Hz; r.m.s.; 1 s / 1 min. for SKK ...H4	4800 / 4000	V~
M_s	to heatsink	9 ± 15 % ¹⁾	Nm
M_t	to terminal	9 ± 15 % ²⁾	Nm
a		5 * 9,81	m/s²
m	approx.	750	g
Case	SKKT	A 73 a	
	SKKH	A 76 a	









SKKT

SKKH




SKKT 210, SKKH 210



SKKT 210, SKKH 210



SKKT 210, SKKH 210



This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.