


# TPS76515, TPS76518, TPS76525, TPS76527 TPS76528, TPS76530, TPS76533, TPS76550, TPS76501 ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS

SLVS236 – AUGUST 1999



- 150-mA Low-Dropout Voltage Regulator
- Available in 1.5-V, 1.8-V, 2.5-V, 2.7-V, 2.8-V, 3.0-V, 3.3-V, 5.0-V Fixed Output and Adjustable Versions
- Dropout Voltage to 85 mV (Typ) at 150 mA (TPS76550)
- Ultra-Low 35- $\mu$ A Typical Quiescent Current
- 3% Tolerance Over Specified Conditions for Fixed-Output Versions
- Open Drain Power Good
- 8-Pin SOIC Package
- Thermal Shutdown Protection



## description

This device is designed to have an ultra-low quiescent current and be stable with a 4.7- $\mu$ F capacitor. This combination provides high performance at a reasonable cost.

Because the PMOS device behaves as a low-value resistor, the dropout voltage is very low (typically 85 mV at an output current of 150 mA for the TPS76550) and is directly proportional to the output current. Additionally, since the PMOS pass element is a voltage-driven device, the quiescent current is very low and independent of output loading (typically 35  $\mu$ A over the full range of output current, 0 mA to 150 mA). These two key specifications yield a significant improvement in operating life for battery-powered systems. This LDO family also features a sleep mode; applying a TTL high signal to  $\overline{\text{EN}}$  (enable) shuts down the regulator, reducing the quiescent current to less than 1  $\mu$ A (typ).



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 1999, Texas Instruments Incorporated

# TPS76515, TPS76518, TPS76525, TPS76527

## TPS76528, TPS76530, TPS76533, TPS76550, TPS76501

### ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS

SLVS236 – AUGUST 1999

#### description (continued)


Power good (PG) is an active high output, which can be used to implement a power-on reset or a low-battery indicator.

The TPS765xx is offered in 1.5-V, 1.8-V, 2.5-V, 2.7-V, 2.8-V, 3.0-V, 3.3-V and 5.0-V fixed-voltage versions and in an adjustable version (programmable over the range of 1.25 V to 5.5 V). Output voltage tolerance is specified as a maximum of 3% over line, load, and temperature ranges. The TPS765xx family is available in 8 pin SOIC package.

#### AVAILABLE OPTIONS

| $T_J$          | OUTPUT VOLTAGE (V)            | PACKAGED DEVICES |
|----------------|-------------------------------|------------------|
|                | TYP                           | SOIC (D)         |
| –40°C to 125°C | 5.0                           | TPS76550D        |
|                | 3.3                           | TPS76533D        |
|                | 3.0                           | TPS76530D        |
|                | 2.8                           | TPS76528D        |
|                | 2.7                           | TPS76527D        |
|                | 2.5                           | TPS76525D        |
|                | 1.8                           | TPS76518D        |
|                | 1.5                           | TPS76515D        |
|                | Adjustable<br>1.25 V to 5.5 V | TPS76501D        |

The TPS76501 is programmable using an external resistor divider (see application information). The D package is available taped and reeled. Add an R suffix to the device type (e.g., TPS76501DR).




† See application information section for capacitor selection details.


Figure 1. Typical Application Configuration for Fixed Output Options

TPS76515, TPS76518, TPS76525, TPS76527  
TPS76528, TPS76530, TPS76533, TPS76550, TPS76501  
**ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS**  
SLVS236 – AUGUST 1999

**functional block diagram—adjustable version**



**functional block diagram—fixed-voltage version**



TPS76515, TPS76518, TPS76525, TPS76527

TPS76528, TPS76530, TPS76533, TPS76550, TPS76501

ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS

SLVS236 – AUGUST 1999

Terminal Functions – SOIC Package

| TERMINAL<br>NAME       | NO. | I/O | DESCRIPTION                                                                 |
|------------------------|-----|-----|-----------------------------------------------------------------------------|
| $\overline{\text{EN}}$ | 4   | I   | Enable input                                                                |
| FB/NC                  | 1   | I   | Feedback input voltage for adjustable device (no connect for fixed options) |
| GND                    | 3   |     | Regulator ground                                                            |
| IN                     | 5   | I   | Input voltage                                                               |
| IN                     | 6   | I   | Input voltage                                                               |
| OUT                    | 7   | O   | Regulated output voltage                                                    |
| OUT                    | 8   | O   | Regulated output voltage                                                    |
| PG                     | 2   | O   | PG output                                                                   |

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>

|                                                     |                               |
|-----------------------------------------------------|-------------------------------|
| Input voltage range <sup>‡</sup> , $V_I$            | –0.3 V to 13.5 V              |
| Voltage range at $\overline{\text{EN}}$             | –0.3 V to 16.5 V              |
| Maximum PG voltage                                  | 16.5 V                        |
| Peak output current                                 | Internally limited            |
| Continuous total power dissipation                  | See dissipation rating tables |
| Output voltage, $V_O$ (OUT, FB)                     | 7 V                           |
| Operating virtual junction temperature range, $T_J$ | –40°C to 125°C                |
| Storage temperature range, $T_{\text{stg}}$         | –65°C to 150°C                |
| ESD rating, HBM                                     | 2 kV                          |

<sup>†</sup> Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

<sup>‡</sup> All voltage values are with respect to network terminal ground.

DISSIPATION RATING TABLE 1 – FREE-AIR TEMPERATURES

| PACKAGE | AIR FLOW<br>(CFM) | $T_A < 25^\circ\text{C}$<br>POWER RATING | DERATING FACTOR<br>ABOVE $T_A = 25^\circ\text{C}$ | $T_A = 70^\circ\text{C}$<br>POWER RATING | $T_A = 85^\circ\text{C}$<br>POWER RATING |
|---------|-------------------|------------------------------------------|---------------------------------------------------|------------------------------------------|------------------------------------------|
| D       | 0                 | 568 mW                                   | 5.68 mW/°C                                        | 312 mW                                   | 227 mW                                   |
|         | 250               | 904 mW                                   | 9.04 mW/°C                                        | 497 mW                                   | 361 mW                                   |

recommended operating conditions

|                                                        | MIN | MAX | UNIT |
|--------------------------------------------------------|-----|-----|------|
| Input voltage, $V_I$ <sup>☆</sup>                      | 2.7 | 10  | V    |
| Output voltage range, $V_O$                            | 1.2 | 5.5 | V    |
| Output current, $I_O$ (Note 1)                         | 0   | 150 | mA   |
| Operating virtual junction temperature, $T_J$ (Note 1) | –40 | 125 | °C   |

<sup>☆</sup> To calculate the minimum input voltage for your maximum output current, use the following equation:  $V_{I(\text{min})} = V_{O(\text{max})} + V_{\text{DO}(\text{max load})}$ .

NOTE 1: Continuous current and operating junction temperature are limited by internal protection circuitry, but it is not recommended that the device operate under conditions beyond those specified in this table for extended periods of time.



**TPS76515, TPS76518, TPS76525, TPS76527**  
**TPS76528, TPS76530, TPS76533, TPS76550, TPS76501**  
**ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS**

SLVS236 – AUGUST 1999

electrical characteristics over recommended operating free-air temperature range,  
 $V_i = V_{O(\text{typ})} + 1 \text{ V}$ ,  $I_O = 10 \mu\text{A}$ ,  $\overline{\text{EN}} = 0 \text{ V}$ ,  $C_O = 4.7 \mu\text{F}$  (unless otherwise noted)

| PARAMETER                                                                                |                                    | TEST CONDITIONS                                                                                 | MIN                                               | TYP                | MAX | UNIT                  |
|------------------------------------------------------------------------------------------|------------------------------------|-------------------------------------------------------------------------------------------------|---------------------------------------------------|--------------------|-----|-----------------------|
| Output voltage<br>(10 μA to 150 mA load)<br>(see Note 2)                                 | TPS76501                           | 5.5 V ≥ V <sub>O</sub> ≥ 1.25 V, T <sub>J</sub> = 25°C                                          | V <sub>O</sub>                                    |                    |     | V                     |
|                                                                                          |                                    | 5.5 V ≥ V <sub>O</sub> ≥ 1.25 V, T <sub>J</sub> = −40°C to 125°C                                | 0.97V <sub>O</sub>                                | 1.03V <sub>O</sub> |     |                       |
|                                                                                          | TPS76515                           | T <sub>J</sub> = 25°C, 2.7 V < V <sub>IN</sub> < 10 V                                           | 1.5                                               |                    |     |                       |
|                                                                                          |                                    | T <sub>J</sub> = −40°C to 125°C, 2.7 V < V <sub>IN</sub> < 10 V                                 | 1.455                                             | 1.545              |     |                       |
|                                                                                          | TPS76518                           | T <sub>J</sub> = 25°C, 2.8 V < V <sub>IN</sub> < 10 V                                           | 1.8                                               |                    |     |                       |
|                                                                                          |                                    | T <sub>J</sub> = −40°C to 125°C, 2.8 V < V <sub>IN</sub> < 10 V                                 | 1.746                                             | 1.854              |     |                       |
|                                                                                          | TPS76525                           | T <sub>J</sub> = 25°C, 3.5 V < V <sub>IN</sub> < 10 V                                           | 2.5                                               |                    |     |                       |
|                                                                                          |                                    | T <sub>J</sub> = −40°C to 125°C, 3.5 V < V <sub>IN</sub> < 10 V                                 | 2.425                                             | 2.575              |     |                       |
|                                                                                          | TPS76527                           | T <sub>J</sub> = 25°C, 3.7 V < V <sub>IN</sub> < 10 V                                           | 2.7                                               |                    |     |                       |
|                                                                                          |                                    | T <sub>J</sub> = −40°C to 125°C, 3.7 V < V <sub>IN</sub> < 10 V                                 | 2.619                                             | 2.781              |     |                       |
|                                                                                          | TPS76528                           | T <sub>J</sub> = 25°C, 3.8 V < V <sub>IN</sub> < 10 V                                           | 2.8                                               |                    |     |                       |
|                                                                                          |                                    | T <sub>J</sub> = −40°C to 125°C, 3.8 V < V <sub>IN</sub> < 10 V                                 | 2.716                                             | 2.884              |     |                       |
|                                                                                          | TPS76530                           | T <sub>J</sub> = 25°C, 4.0 V < V <sub>IN</sub> < 10 V                                           | 3.0                                               |                    |     |                       |
|                                                                                          |                                    | T <sub>J</sub> = −40°C to 125°C, 4.0 V < V <sub>IN</sub> < 10 V                                 | 2.910                                             | 3.090              |     |                       |
|                                                                                          | TPS76533                           | T <sub>J</sub> = 25°C, 4.3 V < V <sub>IN</sub> < 10 V                                           | 3.3                                               |                    |     |                       |
|                                                                                          |                                    | T <sub>J</sub> = −40°C to 125°C, 4.3 V < V <sub>IN</sub> < 10 V                                 | 3.201                                             | 3.399              |     |                       |
|                                                                                          | TPS76550                           | T <sub>J</sub> = 25°C, 6.0 V < V <sub>IN</sub> < 10 V                                           | 5.0                                               |                    |     |                       |
|                                                                                          |                                    | T <sub>J</sub> = −40°C to 125°C, 6.0 V < V <sub>IN</sub> < 10 V                                 | 4.850                                             | 5.150              |     |                       |
| Quiescent current (GND current)<br>EN = 0V, (see Note 2)                                 |                                    | 10 μA < I <sub>O</sub> < 150 mA, T <sub>J</sub> = 25°C                                          | 35                                                |                    |     | μA                    |
|                                                                                          |                                    | I <sub>O</sub> = 150 mA, T <sub>J</sub> = −40°C to 125°C                                        | 50                                                |                    |     |                       |
| Output voltage line regulation (ΔV <sub>O</sub> /V <sub>O</sub> )<br>(see Notes 2 and 3) |                                    | V <sub>O</sub> + 1 V < V <sub>I</sub> ≤ 10 V, T <sub>J</sub> = 25°C                             | 0.01                                              |                    |     | %/V                   |
| Load regulation                                                                          |                                    | I <sub>O</sub> = 10 μA to 150 mA                                                                | 0.3%                                              |                    |     |                       |
| Output noise voltage                                                                     |                                    | BW = 300 Hz to 50 kHz,<br>C <sub>O</sub> = 4.7 μF, T <sub>J</sub> = 25°C                        | 200                                               |                    |     | μVrms                 |
| Output current Limit                                                                     |                                    | V <sub>O</sub> = 0 V                                                                            | 0.8 1.2                                           |                    |     | A                     |
| Thermal shutdown junction temperature                                                    |                                    |                                                                                                 | 150                                               |                    |     | °C                    |
| Standby current                                                                          |                                    | $\overline{\text{EN}} = V_I$ , T <sub>J</sub> = 25°C,<br>2.7 V < V <sub>I</sub> < 10 V          | 1                                                 |                    |     | μA                    |
|                                                                                          |                                    | $\overline{\text{EN}} = V_I$ , T <sub>J</sub> = −40°C to 125°C<br>2.7 V < V <sub>I</sub> < 10 V | 10                                                |                    |     | μA                    |
| FB input current                                                                         |                                    | TPS76501                                                                                        | FB = 1.5 V                                        |                    |     | 2 nA                  |
| High level enable input voltage                                                          |                                    |                                                                                                 | 2.0                                               |                    |     | V                     |
| Low level enable input voltage                                                           |                                    |                                                                                                 | 0.8                                               |                    |     | V                     |
| Power supply ripple rejection (see Note 2)                                               |                                    | f = 1 kHz,<br>I <sub>O</sub> = 10 μA, T <sub>J</sub> = 25°C                                     | 63                                                |                    |     | dB                    |
| PG                                                                                       | Minimum input voltage for valid PG |                                                                                                 | I <sub>O</sub> (PG) = 300μA                       |                    |     | 1.1 V                 |
|                                                                                          | Trip threshold voltage             |                                                                                                 | V <sub>O</sub> decreasing                         |                    |     | 92 98 %V <sub>O</sub> |
|                                                                                          | Hysteresis voltage                 |                                                                                                 | Measured at V <sub>O</sub>                        |                    |     | 0.5 %V <sub>O</sub>   |
|                                                                                          | Output low voltage                 |                                                                                                 | V <sub>I</sub> = 2.7 V, I <sub>O</sub> (PG) = 1mA |                    |     | 0.15 0.4 V            |
|                                                                                          | Leakage current                    |                                                                                                 | V(PG) = 5 V                                       |                    |     | 1 μA                  |
| Input current (EN)                                                                       |                                    | $\overline{\text{EN}} = 0 \text{ V}$                                                            | −1 0 1                                            |                    |     | μA                    |
|                                                                                          |                                    | $\overline{\text{EN}} = V_I$                                                                    | −1 1                                              |                    |     |                       |

NOTE: 2. Minimum IN operating voltage is 2.7 V or  $V_{O(\text{typ})} + 1 \text{ V}$ , whichever is greater. Maximum IN voltage 10 V.

TPS76515, TPS76518, TPS76525, TPS76527

TPS76528, TPS76530, TPS76533, TPS76550, TPS76501

ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS

SLVS236 – AUGUST 1999

electrical characteristics over recommended operating free-air temperature range,  $V_i = V_{O(\text{typ})} + 1 \text{ V}$ ,  $I_O = 10 \mu\text{A}$ ,  $\overline{\text{EN}} = 0 \text{ V}$ ,  $C_O = 4.7 \mu\text{F}$  (unless otherwise noted) (continued)

| PARAMETER                       |          | TEST CONDITIONS                                                          | MIN | TYP | MAX | UNIT |
|---------------------------------|----------|--------------------------------------------------------------------------|-----|-----|-----|------|
| Dropout voltage<br>(See Note 4) | TPS76528 | $I_O = 150 \text{ mA}$ , $T_J = 25^\circ\text{C}$                        |     | 190 |     | mV   |
|                                 |          | $I_O = 150 \text{ mA}$ , $T_J = -40^\circ\text{C to } 125^\circ\text{C}$ |     |     | 330 |      |
|                                 | TPS76530 | $I_O = 150 \text{ mA}$ , $T_J = 25^\circ\text{C}$                        |     | 160 |     |      |
|                                 |          | $I_O = 150 \text{ mA}$ , $T_J = -40^\circ\text{C to } 125^\circ\text{C}$ |     |     | 280 |      |
|                                 | TPS76533 | $I_O = 150 \text{ mA}$ , $T_J = 25^\circ\text{C}$                        |     | 140 |     |      |
|                                 |          | $I_O = 150 \text{ mA}$ , $T_J = -40^\circ\text{C to } 125^\circ\text{C}$ |     |     | 240 |      |
|                                 | TPS76550 | $I_O = 150 \text{ mA}$ , $T_J = 25^\circ\text{C}$                        |     | 85  |     |      |
|                                 |          | $I_O = 150 \text{ mA}$ , $T_J = -40^\circ\text{C to } 125^\circ\text{C}$ |     |     | 150 |      |

NOTES: 3. If  $V_O \leq 1.8 \text{ V}$  then  $V_{\text{imin}} = 2.7 \text{ V}$ ,  $V_{\text{imax}} = 10 \text{ V}$ :

$$\text{Line Reg. (mV)} = (\%/V) \times \frac{V_O(V_{\text{imax}} - 2.7 \text{ V})}{100} \times 1000$$

If  $V_O \geq 2.5 \text{ V}$  then  $V_{\text{imin}} = V_O + 1 \text{ V}$ ,  $V_{\text{imax}} = 10 \text{ V}$ :

$$\text{Line Reg. (mV)} = (\%/V) \times \frac{V_O(V_{\text{imax}} - (V_O + 1 \text{ V}))}{100} \times 1000$$

4. IN voltage equals  $V_{O(\text{Typ})} - 100 \text{ mV}$ ; TPS76501 output voltage set to 3.3 V nominal with external resistor divider. TPS76515, TPS76518, TPS76525, and TPS76527 dropout voltage limited by input voltage range limitations (i.e., TPS76530 input voltage needs to drop to 2.9 V for purpose of this test).

Table of Graphs

|                                    |                              | FIGURE  |
|------------------------------------|------------------------------|---------|
| Output voltage                     | vs Load current              | 2, 3    |
|                                    | vs Free-air temperature      | 4, 5    |
| Ground current                     | vs Load current              | 6, 7    |
|                                    | vs Free-air temperature      | 8, 9    |
| Power supply ripple rejection      | vs Frequency                 | 10      |
| Output spectral noise density      | vs Frequency                 | 11      |
| Output impedance                   | vs Frequency                 | 12      |
| Dropout voltage                    | vs Free-air temperature      | 13, 14  |
| Line transient response            |                              | 15, 17  |
| Load transient response            |                              | 16, 18  |
| Output voltage                     | vs Time                      | 19      |
| Dropout voltage                    | vs Input voltage             | 20      |
| Equivalent series resistance (ESR) | vs Output current            | 21 – 24 |
| Equivalent series resistance (ESR) | vs Added ceramic capacitance | 25, 26  |

TPS76515, TPS76518, TPS76525, TPS76527  
TPS76528, TPS76530, TPS76533, TPS76550, TPS76501  
ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS

SLVS236 – AUGUST 1999

TYPICAL CHARACTERISTICS




Figure 2




Figure 3




Figure 4




Figure 5

TPS76515, TPS76518, TPS76525, TPS76527

TPS76528, TPS76530, TPS76533, TPS76550, TPS76501

ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS

SLVS236 – AUGUST 1999

## TYPICAL CHARACTERISTICS

TPS76533  
GROUND CURRENT  
VS  
LOAD CURRENT




Figure 6

TPS76515  
GROUND CURRENT  
VS  
LOAD CURRENT




Figure 7

TPS76533  
GROUND CURRENT  
VS  
FREE-AIR TEMPERATURE




Figure 8

TPS76515  
GROUND CURRENT  
VS  
FREE-AIR TEMPERATURE




Figure 9

TPS76515, TPS76518, TPS76525, TPS76527  
TPS76528, TPS76530, TPS76533, TPS76550, TPS76501  
ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS  
SLVS236 – AUGUST 1999

TYPICAL CHARACTERISTICS




Figure 10




Figure 11




Figure 12

TPS76515, TPS76518, TPS76525, TPS76527

TPS76528, TPS76530, TPS76533, TPS76550, TPS76501

ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS

SLVS236 – AUGUST 1999

## TYPICAL CHARACTERISTICS




Figure 13




Figure 14




Figure 15








Figure 16

**TPS76515, TPS76518, TPS76525, TPS76527**  
**TPS76528, TPS76530, TPS76533, TPS76550, TPS76501**  
**ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS**  
 SLVS236 – AUGUST 1999

**TYPICAL CHARACTERISTICS**



TPS76515, TPS76518, TPS76525, TPS76527

TPS76528, TPS76530, TPS76533, TPS76550, TPS76501

ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS

SLVS236 – AUGUST 1999

## TYPICAL CHARACTERISTICS




Figure 21




Figure 22




Figure 23




Figure 24

<sup>†</sup> Equivalent series resistance (ESR) refers to the total series resistance, including the ESR of the capacitor, any series resistance added externally, and PWB trace resistance to  $C_O$ .

TPS76515, TPS76518, TPS76525, TPS76527  
TPS76528, TPS76530, TPS76533, TPS76550, TPS76501  
ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS

SLVS236 – AUGUST 1999

TYPICAL CHARACTERISTICS






Figure 27. Test Circuit for Typical Regions of Stability (Figures 20 through 23) (Fixed Output Options)

<sup>†</sup> Equivalent series resistance (ESR) refers to the total series resistance, including the ESR of the capacitor, any series resistance added externally, and PWB trace resistance to  $C_O$ .

**TPS76515, TPS76518, TPS76525, TPS76527****TPS76528, TPS76530, TPS76533, TPS76550, TPS76501****ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS**

SLVS236 – AUGUST 1999

**APPLICATION INFORMATION**

The TPS765xx family includes eight fixed-output voltage regulators (1.5 V, 1.8 V, 2.5 V, 2.7 V, 2.8 V, 3.0 V, 3.3 V, and 5.0 V), and an adjustable regulator, the TPS76501 (adjustable from 1.25 V to 5.5 V).

**device operation**

The TPS765xx features very low quiescent current, which remains virtually constant even with varying loads. Conventional LDO regulators use a pnp pass element, the base current of which is directly proportional to the load current through the regulator ( $I_B = I_C/\beta$ ). The TPS765xx uses a PMOS transistor to pass current; because the gate of the PMOS is voltage driven, operating current is low and invariable over the full load range.

Another pitfall associated with the pnp-pass element is its tendency to saturate when the device goes into dropout. The resulting drop in  $\beta$  forces an increase in  $I_B$  to maintain the load. During power up, this translates to large start-up currents. Systems with limited supply current may fail to start up. In battery-powered systems, it means rapid battery discharge when the voltage decays below the minimum required for regulation. The TPS765xx quiescent current remains low even when the regulator drops out, eliminating both problems.

The TPS765xx family also features a shutdown mode that places the output in the high-impedance state (essentially equal to the feedback-divider resistance) and reduces quiescent current to 1  $\mu$ A (typ). If the shutdown feature is not used,  $\overline{EN}$  should be tied to ground. Response to an enable transition is quick; regulated output voltage is reestablished in typically 160  $\mu$ s.

**minimum load requirements**

The TPS765xx family is stable even at zero load; no minimum load is required for operation.

**FB - pin connection (adjustable version only)**

The FB pin is an input pin to sense the output voltage and close the loop for the adjustable option. The output voltage is sensed through a resistor divider network to close the loop as it is shown in Figure 29. Normally, this connection should be as short as possible; however, the connection can be made near a critical circuit to improve performance at that point. Internally, FB connects to a high-impedance wide-bandwidth amplifier and noise pickup feeds through to the regulator output. Routing the FB connection to minimize/avoid noise pickup is essential.

**external capacitor requirements**

An input capacitor is not usually required; however, a ceramic bypass capacitor (0.047  $\mu$ F or larger) improves load transient response and noise rejection if the TPS765xx is located more than a few inches from the power supply. A higher-capacitance electrolytic capacitor may be necessary if large (hundreds of milliamps) load transients with fast rise times are anticipated.

Like all low dropout regulators, the TPS765xx requires an output capacitor connected between OUT and GND to stabilize the internal control loop. The minimum recommended capacitance value is 4.7  $\mu$ F and the ESR (equivalent series resistance) must be between 300-m $\Omega$  and 20- $\Omega$ . Capacitor values 4.7  $\mu$ F or larger are acceptable, provided the ESR is less than 20  $\Omega$ . Solid tantalum electrolytic, aluminum electrolytic, and multilayer ceramic capacitors are all suitable, provided they meet the requirements described previously.

**TPS76515, TPS76518, TPS76525, TPS76527**  
**TPS76528, TPS76530, TPS76533, TPS76550, TPS76501**  
**ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS**  
 SLVS236 – AUGUST 1999

## APPLICATION INFORMATION

### external capacitor requirements (continued)




Figure 28. Typical Application Circuit (Fixed Versions)

### programming the TPS76501 adjustable LDO regulator

The output voltage of the TPS76501 adjustable regulator is programmed using an external resistor divider as shown in Figure 29. The output voltage is calculated using:

$$V_O = V_{\text{ref}} \times \left(1 + \frac{R_1}{R_2}\right) \quad (1)$$

Where

$V_{\text{ref}} = 1.224 \text{ V typ}$  (the internal reference voltage)

Resistors R1 and R2 should be chosen for approximately 7-μA divider current. Lower value resistors can be used but offer no inherent advantage and waste more power. Higher values should be avoided as leakage currents at FB increase the output voltage error. The recommended design procedure is to choose R2 = 169 kΩ to set the divider current at 7 μA and then calculate R1 using:

$$R_1 = \left(\frac{V_O}{V_{\text{ref}}} - 1\right) \times R_2 \quad (2)$$




Figure 29. TPS76501 Adjustable LDO Regulator Programming

**TPS76515, TPS76518, TPS76525, TPS76527****TPS76528, TPS76530, TPS76533, TPS76550, TPS76501****ULTRA-LOW QUIESCIENT CURRENT 150-mA LOW-DROPOUT VOLTAGE REGULATORS**

SLVS236 – AUGUST 1999

**APPLICATION INFORMATION****power-good indicator**

The TPS765xx features a power-good (PG) output that can be used to monitor the status of the regulator. The internal comparator monitors the output voltage: when the output drops to between 92% and 98% of its nominal regulated value, the PG output transistor turns on, taking the signal low. The open-drain output requires a pullup resistor. If not used, it can be left floating. PG can be used to drive power-on reset circuitry or used as a low-battery indicator.

**regulator protection**

The TPS765xx PMOS-pass transistor has a built-in back diode that conducts reverse currents when the input voltage drops below the output voltage (e.g., during power down). Current is conducted from the output to the input and is not internally limited. When extended reverse voltage is anticipated, external limiting may be appropriate.

The TPS765xx also features internal current limiting and thermal protection. During normal operation, the TPS765xx limits output current to approximately 0.8 A. When current limiting engages, the output voltage scales back linearly until the overcurrent condition ends. While current limiting is designed to prevent gross device failure, care should be taken not to exceed the power dissipation ratings of the package. If the temperature of the device exceeds 150°C(typ), thermal-protection circuitry shuts it down. Once the device has cooled below 130°C(typ), regulator operation resumes.

**power dissipation and junction temperature**

Specified regulator operation is assured to a junction temperature of 125°C; the maximum junction temperature should be restricted to 125°C under normal operating conditions. This restriction limits the power dissipation the regulator can handle in any given application. To ensure the junction temperature is within acceptable limits, calculate the maximum allowable dissipation,  $P_{D(max)}$ , and the actual dissipation,  $P_D$ , which must be less than or equal to  $P_{D(max)}$ .

The maximum-power-dissipation limit is determined using the following equation:

$$P_{D(max)} = \frac{T_{Jmax} - T_A}{R_{\theta JA}}$$

Where

$T_{Jmax}$  is the maximum allowable junction temperature

$R_{\theta JA}$  is the thermal resistance junction-to-ambient for the package, i.e., 176°C/W for the 8-terminal SOIC.

$T_A$  is the ambient temperature.

The regulator dissipation is calculated using:

$$P_D = (V_I - V_O) \times I_O$$

Power dissipation resulting from quiescent current is negligible. Excessive power dissipation will trigger the thermal protection circuit.

## PACKAGING INFORMATION

| Orderable part number      | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6) |
|----------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------|
| <a href="#">TPS76501D</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76501               |
| TPS76501D.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76501               |
| <a href="#">TPS76501DR</a> | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76501               |
| TPS76501DR.A               | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76501               |
| <a href="#">TPS76515D</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76515               |
| TPS76515D.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76515               |
| <a href="#">TPS76518D</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76518               |
| TPS76518D.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76518               |
| <a href="#">TPS76518DR</a> | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76518               |
| TPS76518DR.A               | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76518               |
| <a href="#">TPS76525D</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76525               |
| TPS76525D.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76525               |
| <a href="#">TPS76528D</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76528               |
| TPS76528D.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76528               |
| <a href="#">TPS76533D</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76533               |
| TPS76533D.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76533               |
| <a href="#">TPS76533DR</a> | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76533               |
| TPS76533DR.A               | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76533               |
| <a href="#">TPS76550D</a>  | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76550               |
| TPS76550D.A                | Active        | Production           | SOIC (D)   8   | 75   TUBE             | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76550               |
| <a href="#">TPS76550DR</a> | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76550               |
| TPS76550DR.A               | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | NIPDAU                               | Level-1-260C-UNLIM                | -40 to 125   | 76550               |

<sup>(1)</sup> **Status:** For more details on status, see our [product life cycle](#).

<sup>(2)</sup> **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

<sup>(3)</sup> **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

<sup>(4)</sup> **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

<sup>(5)</sup> **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

<sup>(6)</sup> **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TPS76501DR | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TPS76518DR | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TPS76533DR | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| TPS76550DR | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |


## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device     | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS76501DR | SOIC         | D               | 8    | 2500 | 350.0       | 350.0      | 43.0        |
| TPS76518DR | SOIC         | D               | 8    | 2500 | 350.0       | 350.0      | 43.0        |
| TPS76533DR | SOIC         | D               | 8    | 2500 | 350.0       | 350.0      | 43.0        |
| TPS76550DR | SOIC         | D               | 8    | 2500 | 350.0       | 350.0      | 43.0        |

## TUBE



\*All dimensions are nominal


| Device      | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| TPS76501D   | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76501D.A | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76515D   | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76515D.A | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76518D   | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76518D.A | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76525D   | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76525D.A | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76528D   | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76528D.A | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76533D   | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76533D.A | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76550D   | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |
| TPS76550D.A | D            | SOIC         | 8    | 75  | 505.46 | 6.76   | 3810   | 4      |




**D0008A**

**SOIC - 1.75 mm max height**

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE  
EXPOSED METAL SHOWN  
SCALE:8X



## SOLDER MASK DETAILS

4214825/C 02/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

## EXAMPLE STENCIL DESIGN

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE  
BASED ON .005 INCH [0.125 MM] THICK STENCIL  
SCALE:8X

4214825/C 02/2019

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated