

LCR CAPACITORS(EU) LTD

RC SUPPRESSOR
TYPE: FE-SP-CR23

Sudden interruption of current in an inductive circuit normally produces a high voltage surge. Damage to contacts occur due to arcing.

In Thyristor or Triac Circuits incorrect functioning may result due to high dv/dt

The LCR RC network will suppress arcing and also reduce dv/dt


The RC network also suppresses radio interference over a wide frequency range

Encapsulation is of self extinguishing material.

0.8mm Capacitor wire
L = 35mm $\pm$ 5mm

CHARACTERISTICS

Capacitance Range:	100NF
Capacitance Tolerance:	10%
Voltage A.C.:	250 VAC (CLASS X)
Power Rating	1/2 Watt
Humidity Classification	50 / 10 / 56
Temperature Range.	-55°C TO 100°C
Resistance	100R
Leads:	0.8 mm Tinned Copper Wire Capacitor 0.6 mm Tinned Copper Wire Resistor



CAPACITY UF	L	W	H	PCM
0.1UF	25	9	18.5	22.5

OTHER VOLTAGES AND VALUES ARE AVAILABLE UPON REQUEST

LCR CAPACITORS (EU) LTD

UNIT 18 , RASSAU INDUSTRIAL ESTATE , EBBW VALE , GWENT NP23 5SD .
TEL. 01495 307070 FAX. 01495 306965