








VIEW A-A


mat'l. code				surface		tolerance		projection		product family			
				ISO1302 ✓		ISO1101 ISO406				MOD JACK			
ltr ecn nodr date				tolerances unless otherwise				wise specified		title			
T	ECR	S00022	BC LOH	26JAN.00	angle	line	0.X±0.3			8 POS HORIZONTAL P.C.B. MOD JACK ASSY			
U	ECR	V10424	LUNOVR	12FEB.01			0.XX±0.15						
V	N05-0002	YS	06JAN.01	0.XXX±0.05									
					0°±2'		scale 2.0						
W	N08-0074	SH MMD	30APR.08	dr		JANET	15JUN.98			dwg no		sheet 1 of 3	size
X	ELX-N-010667	SH MMD	13MAR.12	engr		JANET	15JUN.98			68899		A4	
				chr	M	CHENG	19FEB.01						
				appd	M	CHENG	19FEB.01			type Product Customer Drawing			
sheet index		revision		X	X								
		sheet		1	2	3							

RECOMMENDED BOARD LAYOUT
VIEWED FROM TOP

KEYED STYLE



LEFT EAR MOUNTING



SECTION D-D

NOTE :

- 1 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 2 THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.60mm MINIMUM THICK CIRCUIT BOARD.
- 3 IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION.

mat'l. code				surface		tolerance		projection		product family			
				ISO1302 ✓		ISO1101 ISO406				MOD JACK			
l t r e c n n o d r				date		tolerances unless otherwise		specified		title			
T	ECR	S00022	BC LOH	26JAN.00		angle	0.X±0.3			8 POS HORIZONTAL P.C.B. MOD JACK ASSY			
U	ECR	V10424	LMHWR	12FEB.01			0.XX±0.15						
V	N05-0002	YS	06JAN.01	0'±2'			0.XXX±0.05						
								scale 2.0					
W	N08-0074	SH MMD	30APR.08	dr	JANET	15JUN.98			dwg no		sheet 2 of 3		size
X	ELX-N-010667	SH MMD	13MAR.12	enr	JANET	15JUN.98			68899		A4		
				chr	M CHENG	19FEB.01							
				appd	M CHENG	19FEB.01							
sheet		revision											
index		sheet											



1 | 2

FCIconnect.com

3 |

4

PRODUCT NO.	DIM. A	DIM. B	STYLE	POSITIONS LOADED	CONTACT PLATING	HOUSING COLOR	MOUNTING EARS	REMARKS
68899-001 -001LF	-	-	UNKEYED	ALL	0.76um /30*u GXT	BLACK	YES	-
-002 -002LF	1.25 /0.050	2.69 /0.106	KEYED	ALL	5u' Au + high performance lubricant	BLACK	YES	-
-003 -003LF	-	-	UNKEYED	2,3,4,5,6,7	5u' Au + high performance lubricant	BLACK	YES	-
-004 -004LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	BLACK	NO	-
-004RLF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	RED	NO	-
-004GLF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	GREEN	NO	-
-005 -005LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	GRAY	NO	-
-006 -006LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	BLACK	YES	-
-007 -007LF	1.25 /0.050	2.69 /0.106	KEYED	ALL	5u' Au + high performance lubricant	BLACK	NO	-
-008 -008LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	BLACK	LEFT ONLY	-
-009 -009LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	BLACK	RIGHT ONLY	-
-010 -010LF	-	-	UNKEYED	ALL	1,27um /50*u GXT	BLACK	YES	-
-011 -011LF	-	-	UNKEYED	1,4,5,8	5u' Au + high performance lubricant	BLACK	YES	-
-012 -012LF	-	-	UNKEYED	ALL	5u' Au + high performance lubricant	BLACK	NO	-
-013 -013LF	-	-	UNKEYED	ALL	1,27um /50*u GXT	BLACK	NO	-
-014 -014LF	1.25 /0.050	2.69 /0.106	KEYED	ALL	5u' Au + high performance lubricant	BLACK	NO	-
-015 -015LF	1.25 /0.050	2.69 /0.106	KEYED	ALL	1,27um /50*u GXT	BLACK	NO	-

LEAD FREE PRODUCT NO.

mat'l. code		surface ISO1302 ✓		tolerance ISO1101 ISO406		projection 		product family MOD JACK		
l tr ecn nodr		date		tolerances unless otherwise specified		mm		title		
T	ECR S00022	BC LOH	26JAN.00	0.X±0.3		mm		8 POS HORIZONTAL		
U	ECR V10424	UNIMOR	12FEB.01	0.XX±0.15		mm		P.C.B. MOD JACK ASSY		
V	N05-0002	YS	06JAN.01	0'±2'		scale 2.0				
W	N08-0074	SH MMD	30APR.08	dr	JANET	15JUN.98	dwg no sheet 3 of 3 size			
X	ELX-N-010667	SH MMD	13MAR.12	enr	JANET	15JUN.98	68899 A4			
				chr	M CHENG	19FEB.01	type Product Customer Drawing			
				appd	M CHENG	19FEB.01				
sheet	revision									
index	sheet									