

Single Phase Bridge Rectifiers




CM1500 Series

Features:

- Metal case for maximum heat dissipation
- Surge overload ratings to 400 amperes



CM Series



Dimensions : Inches (Millimetres)

Mechanical Data

Case	: Metal
Terminals	: Plated 25 inches faston
Mounting Position	: Any

Single Phase Bridge Rectifiers



CM1500 Series

Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%

Parameter	CM1500	CM1501	CM1502	CM1504	CM1506	CM1508	Unit
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	V
Maximum RMS Bridge Input Voltage	35	70	140	280	420	560	
Maximum DC Blocking Voltage	50	100	200	400	800	800	
Maximum Average Forward Current at T _A = 55°C	15						A
Non-repetitive Peak Forward Surge Current, Rated Load	300						
Maximum Forward Voltage Per Bridge Element Specified Current at 7.5 A	1.2						V
Maximum Reverse Current at Rated DC Blocking Voltage Per Element	10						µA
I ² t Rating for Fusing (t <8.35 ms)	374						A ² S
Typical Thermal Resistance (Figure 3) RθJC	2.5						°C / W
Operating Temperature Range T _J	-55 to +150						°C
Storage Temperature Range T _A							

Note : * Unit mounted on metal heat-sink

Rating and Characteristic Curves

Figure 1 Output Current VS. Case Temperature
Resistive or Inductive Load $T_J = 150^\circ\text{C}$





Figure 2 Typical Instantaneous Forward Characteristics at $T_J = 25^\circ\text{C}$



Single Phase Bridge Rectifiers



CM1500 Series

Figure 3 Output Current VS. Ambient Temperature
Resistive or Inductive Load Bridge Mounted on 8
Inches x 8 Inches Aluminium Plate 25 Inches Thick





Figure 4 Power Dissipation VS. Average
Output Current Resistive or Inductive Load
 $T_J = 150^\circ\text{C}$



Specification Table

Current Rating (A)	VRRM (V)	Maximum AC Input Voltage (V)	Part Number
15	50	35	CM1500
	100	70	CM1501
	200	140	CM1502
	400	280	CM1504
	600	420	CM1506
	800	500	CM1508

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

