



150mm sq.**San Ace 150****General Specifications**

- Material.....Frame: Plastics (Flammability: UL94V-0),
Impeller: Plastics (Flammability: UL94V-1)
- Expected LifeRefer to specifications (L10:Survival rate:90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire⊕red ⊖black or blue (Sensor) yellow
- Storage Temperature ...-30°C to +70°C (Non-condensing)

150×150×50mm [Mass : 450g] **9GV type** **Specifications** The following nos. **have pulse sensors and ribs.** For ribless, append "1" to the model no.

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Airflow [m ³ /min] [CFM]	Max. Static Pressure [Pa] [inchH ₂ O]	SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]
9GV1512H501	12	10.2 to 13.8	2.9	34.8	3,900	8.54	300	61	-20 to +70	40,000/60°C
9GV1512M501			1.2	14.4	3,000	6.35	224	53		
9GV1524M501	24	20.4 to 27.6	0.6	14.4	3,000	6.35	224	53		

Other sensor specifications are available as options. Please refer to the index (p. 508).

Dimensions (unit: mm) (With ribs)**Reference Dimensions of Mounting Holes and Vent Opening (unit: mm)**


Options (unit: mm)

Finger Guards

Model : 109-1051 Surface treatment : Nickel-chrome plating (silver) Color


Model : 109-1052 Surface treatment : Nickel-chrome plating (silver) Color

Inlet side, Outlet side




Mass : 63g

Outlet side




Mass : 53g


Airflow - Static Pressure Characteristics



9GV1512H501



9GV1512M501



9GV1524M501

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sanyo Denki:

[9GV1512H502](#) [9GV1512M502](#) [9GV1512H5021](#) [9GV1512M5021](#) [9GV1512P5M03](#)