


A DIVISION OF MINNEAPOLIS-MONETWEILL REGULATOR COMPANY
FREEPORT, ILLINOIS
FED. MFR. CODE 91929

105 ML1-E1



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



1- ROLLER ASSEMBLY MAY BE RE-ASSEMBLED 90° FROM POSITION SHOWN.
2- IT IS ESSENTIAL THAT THE CONDUIT OPENING BE PROPERLY SEALED IN ORDER TO MAINTAIN THE EXPLOSION PROOF PROPERTIES.
3- SWITCH WILL PERFORM SATISFACTORILY IN TEMPERATURES TO MINUS 30°F.
- LISTED BY UNDERWRITERS LABORATORY, INC. FOR USE IN CLASS I GROUPS C AND D VAPOR-AIR
4- ATMOSPHERES, AND CLASS 2 GROUPS E, F AND G DUST-AIR ATMOSPHERES

CHARACTERISTICS	ELECTRICAL DATA		SCALE 1/2 TO 1
OPERATING FORCE — — — 6 LBS. APPROX.	CONTACT ARRANGEMENT TWO CIRCUIT DOUBLE THROW DOUBLE BREAK		DO NOT SCALE PRINT
RELEASE FORCE — — — — 4 LBS. APPROX.	10 A-120, 240, OR 480 VAC, 1/2 HP-120 VAC 1 HP-240 VAC; 0.8 A-115 VDC; 0.4 A-230 VDC PILOT DUTY: 720VA-HEAVY DUTY 600 VAC MAX		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:
DIFFERENTIAL TRAVEL — — — .020 MAX.	(A)		ONE PLACE (.0) ±.030
OVERTRAVEL — — — — .475 MIN.	(B)		TWO PLACE (.00) ±.015
SWITCH-BASIC REPLACEMENT — — — — 1 MN1	(C)		THREE PLACE (.000) ±.008
			ANGLES ±
			WEIGHT 1 LB. 13 OZ.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[105ML1-E1](#)