


DO NOT SCALE

DIMENSIONS IN mm

METRIC


THIRD ANGLE

PROJECTION




NOTES:

- 1 FOR USE ON STANDARD APPLICATORS.(RIGHT-LEFT FEED)
- 2 FOR USE ON MINIATURE APPLICATORS.(LEFT-RIGHT FEED)
- 3 FOR USE ON MINIATURE APPLICATORS, AMP O-MATOR APPLICATION.(LEFT-RIGHT FEED)
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION B-B



SECTION A-A

WIRE RANGE :
0,5-1,0mm² AWG
INSULATION RANGE :
1,8-3,3mm DIA.

OBSOLETE 4	2	SEL. GOLD	-	8-163301-3
	3 1		BRASS	1-163301-7
	2	NICKEL	BRASS	1-163301-2
	1	NICKEL	BRASS	1-163301-1
	2	PRE-TINPLATED	PHOSPHOR BR.	163301-8
4 OBSOLETE	2	UNPLATED	PHOSPHOR BR.	163301-7
	2	PRE-TINPLATED	BRASS	163301-6
4 OBSOLETE	2	UNPLATED	BRASS	163301-5
	1	PRE-TINPLATED	PHOSPHOR BR.	163301-4
	1	UNPLATED	PHOSPHOR BR.	163301-3
SUP BY 163301-6	1	PRE-TINPLATED	BRASS	163301-2
	1	UNPLATED	BRASS	163301-1
		PLATING	PLATING	MATERIAL
				PARTNUMBER

					CUSTOMER DRAWING			FOR REFERENCE ONLY WILL NOT BE UPDATED				
					© COPYRIGHT 19 - BY -							
					ALL INTERNATIONAL RIGHTS RESERVED.							
					THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION _____,19____							
					NAME PIN MATE-N-LOK.			 TE Connectivity				
K2	REVISED PER ECO-11-05294		RK	HMR	05APR11							
DR.: J.V.D.HEIJDEN.		CHK.: A.BIJNEN.		APP.: L.V.SOEST.		DWG.No.			REV.LTR.		SHEET	
DATE: 10-04-92		DATE: -		DATE: -		C-163301			K2		1 OF 1	
												A3

