



AC-Capacitors, Suppression Capacitors Class X2 AC 275 V (Code pos. 9 = 2) (MKT)

Dimensions in mm



PCM (mm)	PITCH CODE POS. 10	TERMINAL Ø d (mm)
15	F	0.5
22.5	I	0.5
27.5	K	0.5
37.5	P	0.5

LEAD LENGTH		ORDERING CODE*						
X (mm)	CODE POS. 12	1-4	5-7	8	9	10	11-13	
30 ⁺⁵	A	1779	...	.	2	.	A 0 0	
40 ⁺⁵	B	1779	...	.	2	.	B 0 0	
50 ⁺⁵	C	1779	...	.	2	.	C 0 0	
60 ⁺⁵	E	1779	...	.	2	.	E 0 0	
80 ⁺⁵	D	1779	...	.	2	.	D 0 0	
100 ⁺¹⁰	L	1779	...	.	2	.	L 0 0	
150 ⁺¹⁰	R	1779	...	.	2	.	R 0 0	


MAXIMUM PULSE RISE TIME: (d_U/d_t) in V/µs

RATED VOLTAGE	PITCH (mm)		
	15.0	22.5	27.5
AC 275V	200	150	100

RATED VOLTAGE:

AC 275 V, 50/60 Hz

PERMISSIBLE DC VOLTAGE:

DC 630 V

TERMINALS:

Insulated stranded copper wire, type LiY 0.5 mm² (or AWG 20) ends stranded and tinned

COATING:

Plastic case, epoxy resin sealed, flame retardant UL 94V-0

CLIMATIC TESTING CLASS ACC. TO EN 60068-1:
40/100/56

FURTHER TECHNICAL DATA:

See page 21 (Document No 26504)

FEATURES:

Product is completely lead (Pb)-free

Product is RoHS compliant

CAPACITANCE RANGE:

E12 series 0.01 µFX2 - 2.2 µFX2

preferred values acc. to E6

CAPACITANCE TOLERANCE:

Standard: ± 20 %/ ± 10 %

DISSIPATION FACTOR TANδ:

< 0.1 % measured at 1 kHz

INSULATION RESISTANCE: FOR C ≤ 0.33 µF:

30 GΩ average value

15 GΩ minimum value

TIME CONSTANT FOR C > 0.33 µF:

10 000 sec. average value

5000 sec. minimum value

TEST VOLTAGE:

(Electrode/electrode): DC 2150 V/2 sec.

REFERENCE STANDARDS:

EN 60068-1, EN 132 400, 1994

IEC 60384-14/2, 1993; UL 1283, UL 1414

CSA 22.2 No. 8-M 86, CSA 22.2 No. 1-M 90

DIELECTRIC:


Polypropylene film

ELECTRODES:

Metal evaporated

CONSTRUCTION:

Metallized film capacitor, single design

Between interconnected terminations and case (foil method):
AC 2500 V for 2 sec. at 25 °C

Impedance (Z) as a function of frequency (f) at T_a = 20 °C (average).
Measurement with lead length 6 mm.

RoHS
COMPLIANT

APPROVALS

COUNTRY	SPECIFICATION	ELECTRICAL VALUES	APPROVAL REFERENCE	APPROVAL MARK
U.S.A. (for AC 250 V)	UL 1283 UL 1414	0.01 - 2.2 μ FX 0.01 - 1.0 μ FX	E 76297 Pending	
Canada (for AC 250 V)	C 22.2 No. 8-M 1986 C 22.2 No. 1-M 1994	0.01 - 2.2 μ FX 0.01 - 1.0 μ FX	Pending Pending	
CB TEST-CERTIFICATE (for AC 275 V)		0.01 - 2.2 μ FX2	DE 1-8222	
Germany	EN 132 400; 1999-06 IEC 60384-14, 2nd edition; 1995-06	0.01 - 4.7 μ FX2	40000787	

CAPACITANCE CODE POS. 5-7	TOL. CODE POS. 8 K = ± 10 % M = ± 20 % (mm)	PITCH		BOX NO.	DIMENSIONS W x H x L (+ 0.2/- 0.4 mm)	WEIGHT LEAD LENGTH D = 80 mm (g)	QUANTITY PACKAGE LEAD LENGTH D = 80 mm (pcs)	ORDERING CODE*					
		(mm)	CODE POS. 10					TYPE	C-VALUE	TOL.	VOLTAGE	PITCH	LEAD LENGTH DESIGN
0.047 μFX2	K/M	15.0	F	05	5.3 x 10.3 x 17.8	2.6	1000	1779	347	.	2	F	.00
0.056 μFX2	K	15.0	F	05	5.3 x 10.3 x 17.8	2.6	1000	1779	356	K	2	F	.00
0.068 μFX2	K/M	15.0	F	05	6.0 x 12.0 x 17.9	3.2	900	1779	368	.	2	F	.00
0.082 μFX2	K	15.0	F	49	6.0 x 12.0 x 17.9	3.2	900	1779	382	K	2	F	.00
0.1 μFX2	M	10.0	D	91	6.4 x 12.5 x 12.8	3.0	900	1779	410	K	2	D	.00
0.1 μFX2	K/M	15.0	F	49	6.0 x 12.0 x 17.9	3.2	900	1779	410	M	2	F	.00
0.12 μFX2	K	15.0	F	07	7.3 x 13.3 x 17.8	3.6	800	1779	412	K	2	F	.00
0.15 μFX2	K/M	15.0	F	07	7.3 x 13.3 x 17.8	3.6	800	1779	415	M	2	F	.00
0.15 μFX2	K/M	22.5	I	09	6.3 x 14.3 x 26.3	4.5	650	1779	415	M	2	I	.00
0.18 μFX2	K	15.0	F	28	8.3 x 17.3 x 17.8	4.7	600	1779	418	K	2	F	.00
0.22 μFX2	K	15.0	F	28	8.3 x 17.3 x 17.8	4.7	600	1779	422	K	2	F	.00
0.22 μFX2	M	15.0	F	28	8.3 x 17.3 x 17.8	4.7	600	1779	422	M	2	F	.00
0.22 μFX2	K/M	22.5	I	11	7.3 x 15.3 x 26.3	5.3	500	1779	422	.	2	I	.00
0.22 μFX2	M	22.5	I	09	6.3x 14.3 x 26.3	3.2	650	1779	422	M	2	I	.00
0.27 μFX2	K	22.5	I	12	8.3 x 16.3 x 26.3	4.8	500	1779	427	K	2	I	.00
0.33 μFX2	K	15.0	F	35	10.3 x 17.3 x 17.9	7.7	750	1779	433	K	2	F	.00
0.33 μFX2	M	15.0	F	46	10.0 x 16.0 x 17.9	7.4	750	1779	433	M	2	F	.00
0.33 μFX2	K/M	22.5	I	12	8.3 x 16.3 x 26.3	5.8	500	1779	433	M	2	I	.00
0.39 μFX2	K	22.5	I	01	8.3 x 16.3 x 26.3	6.7	500	1779	439	K	2	I	.00
0.47 μFX2	M	15.0	F	70	10.8 x 18.3 x 17.8	7.6	750	1779	447	M	2	F	.00
0.47 μFX2	K/M	22.5	I	01	8.8 x 16.8 x 26.3	6.9	500	1779	447	.	2	I	.00
0.47 μFX2	K/M	27.5	K	23	8.8 x 16.3 x 31.3	8.0	500	1779	447	.	2	K	.00
0.56 μFX2	K	27.5	K	29	8.8 x 18.3 x 31.3	10.3	350	1779	456	K	2	K	.00
0.68 μFX2	K/M	22.5	I	45	10.8 x 20.8 x 26.3	9.0	500	1779	468	.	2	I	.00
0.68 μFX2	K/M	27.5	K	14	11.0 x 20.3 x 31.3	10.2	250	1779	468	.	2	K	.00
0.82 μFX2	K	27.5	K	14	11.0 x 20.3 x 31.3	10.2	300	1779	482	K	2	K	.00
1.0 μFX2	M	22.5	I	25	12.3 x 22.3 x 26.3	12.2	500	1779	510	M	2	I	.00
1.0 μFX2	K	27.5	K	15	13.0 x 23.3 x 31.3	14.1	300	1779	510	K	2	K	.00
1.0 μFX2	M	27.5	K	14	11.0 x 20.3 x 31.3	9.1	125	1779	510	M	2	K	.00
1.2 μFX2	K	27.5	K	15	13.0 x 23.3 x 31.3	14.1	250	1779	512	K	2	K	.00
1.5 μFX2	K/M	27.5	K	18	14.5 x 24.3 x 31.3	16.2	250	1779	515	M	2	K	.00
1.8 μFX2	K	27.5	K	40	17.8 x 32.3 x 31.3	25.6	150	1779	518	K	2	K	.00
2.2 μFX2	K/M	27.5	K	40	17.8 x 32.4 x 31.2	25.6	80	1779	522	.	2	K	.00
2.2 μFX2	M	27.5	K	70	16.3 x 29.3 x 31.3	22.0	750	1779	447	M	2	F	.00

Inbuilt discharging resistor on request (with larger case dimensions).

* With  and  mark, the ordering code is a 4 on digit 12.

Ordering example: 1779 410 M 2 F D40



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.