

Kynar Wires

Prototyping Wires

pro-POWER



Features:

- Wire wrapping-making solderless connections of wires to terminals remains the preferred method for both automatic and semi-automatic termination in the wiring of computer back panels
- Due to kynar's superior mechanical properties, high temperature characteristics and economical price, Kynar insulated wire wrap products are the most popular choice in the industry
- These insulated wires are available in guage size 26, in single conductor or twisted pair constructions, and may be ordered to a variety of UL or CSA listings, as well as conforming to Mil-W-81822/3

Specifications and Standard Put-Up Data UL Style 1423

105°C, Voltage Not Specified, 4 mil Minimum Average Wall, 3 mil Minimum at Any Point, Silver Plated Copper Conductor					
Conductor		Overall Diameter			Standard Put-Up (ft)
AWG	Diameter	Minimum	Nominal	Maximum	
26	0.0159	0.0245	0.026	0.0275	11,000

Dimensions : Inches

Specifications and Standard Put-Up Data UL Style 1422

105°C, Voltage Not Specified, 5 mil Minimum Average Wall, 4 mil Minimum at Any Point, Silver Plated Copper Conductor					
Conductor		Overall Diameter			Standard Put-Up (ft)
AWG	Diameter	Minimum	Nominal	Maximum	
26	0.0159	0.0255	0.027	0.0285	9,000

Dimensions : Inches

Specifications and Standard Put-Up Data Mil-W081822/3B

135°C, 300 V, Silver Plated Oxygen Free Conductor					
Conductor		Overall Diameter			Standard Put-Up (ft)
AWG	Diameter	Minimum	Nominal	Maximum	
26	0.0159	0.028	0.0295	0.031	9,000

Dimensions : Inches

Prototyping Wires

Insulation Properties :

Characteristics	Value
Specific Gravity	1.75
Tensile Strength at Yield 75°F (p.s.i)	5,200
Elongation at Break (%)	50 to 250
Dielectric Constant at 60 Cycle	8.4
Dielectric Constant V / mil	950
Hardness Durometer Shore D	75 to 80
Flexural Modulus at 75°F (p.s.i)	156 to 260 × 10 ³
Water Absorption (%)	0.04
Service Temperature	275°F (135°C)
Flamability	V-0

Specification Table

AWG Size	Colours	Conductor Size (Inches)	Number of Conductors	Part Number
26	Black	0.0159	1	100-26BK
	Blue			100-26B
	White			100-26W

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.