

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A

A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH — BASIC

CATALOG LISTING

V3L-3005

CQ-X1563

S

V3L-3005

M

DRAWING
NUMBER

X 2 6

X 3 8

ISSUE

X 4 3

REPLACES X72667-VEL

RELEASE NO. PR-20453

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

REVISIONS

A C055729

K E W

4 SEP 84

B C0

1 OCT 85

C OBS

CO 73412

CSL

17 NOV 92

D RE-INS

PR 20453

DAW


15 DEC 92

E CQ

73569


K D R

19 JUL 93



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE --- 88 GRAM MAX

RELEASE FORCE --- 6 GRAM MIN

DIFFERENTIAL TRAVEL --- .032 MAX

OVERTRAVEL --- .090 MIN

RELEASE TRAVEL --- .017 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

S P D T

15.1A 1/2HP 125 OR 250 VAC
1/2A 125 VDC, 1/4A 250 VDC
5A 125 VAC "L"



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

DESIGN UNITS ☐ SI METRIC

☒ US CUSTOMARY

WEIGHT

FO-52848-A

DRAWN

GRT 7 MAY 81 CHECK

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V3L-3005](#)