

NOTES :

1. MATERIAL:-



- PIN:- (0.65)/.0255 SQ. BRASS WIRE.
- HOUSING:- 15% GLASS FILLED POLYESTER
- UL 94 V-0 COLOUR BLACK

2. FOR PLATING VERSIONS AND VOID VERSIONS SEE SHEET 2.



3. MEASUREMENT POINT FOR MINIMUM PLATING THICKNESS.

4. FOR PRODUCT SPEC SEE PS-99020-0001

5. RECOMMENDED PCB THICKNESS: 1.60mm



SECTION K-K



CKT	DIM A	DIM B	DIM C
6	(5.08)/.200	(9.96)/.392	(8.12)/.320
8	(7.62)/.300	(12.50)/.492	(10.66)/.420
10	(10.16)/.400	(15.04)/.592	(13.20)/.520
12	(12.70)/.500	(17.58)/.692	(15.74)/.620
14	(15.24)/.600	(20.12)/.792	(18.28)/.720
16	(17.78)/.700	(22.66)/.892	(20.82)/.820
18	(20.32)/.800	(25.20)/.992	(23.36)/.920
20	(22.86)/.900	(27.74)/.1092	(25.90)/.1020
22	(25.40)/.1000	(30.28)/.1192	(28.44)/.1120
24	(27.94)/.1100	(32.82)/.1292	(30.98)/.1220
26	(30.48)/.1200	(35.36)/.1392	(33.52)/.1320
28	(33.02)/.1300	(37.90)/.1492	(36.06)/.1420
30	(35.56)/.1400	(40.44)/.1592	(38.60)/.1520
32	(38.10)/.1500	(42.98)/.1692	(41.15)/.1620
34	(40.64)/.1600	(45.52)/.1792	(43.68)/.1720
36	(43.18)/.1700	(48.06)/.1892	(46.22)/.1820
38	(45.72)/.1800	(50.60)/.1992	(48.76)/.1920
40	(48.26)/.1900	(53.14)/.2092	(51.30)/.2020
42	(50.80)/.2000	(55.68)/.2192	(53.84)/.2120
44	(53.34)/.2100	(58.22)/.2292	(56.38)/.2220
46	(55.88)/.2200	(60.76)/.2392	(58.92)/.2320
48	(58.42)/.2300	(63.30)/.2492	(61.46)/.2420
50	(60.96)/.2400	(65.84)/.2592	(64.00)/.2520
52	(63.50)/.2500	(68.38)/.2692	(66.54)/.2620
54	(66.04)/.2600	(70.92)/.2792	(69.08)/.2720
56	(68.58)/.2700	(73.46)/.2892	(71.62)/.2820
58	(71.12)/.2800	(76.00)/.2992	(74.16)/.2920
60	(73.66)/.2900	(78.54)/.3092	(76.70)/.3020
62	(76.20)/.3000	(81.08)/.3192	(79.24)/.3120
64	(78.74)/.3100	(83.62)/.3292	(81.78)/.3220
66	(81.28)/.3200	(86.16)/.3392	(84.32)/.3320
68	(83.82)/.3300	(88.70)/.3492	(86.86)/.3420

CHANGE DWG REVISION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO:	REV	DESCRIPTION	SYMBOL	mm	INCH	MM/IN	NTS	INCH	INCH	INCH	INCH	INCH	INCH
S2012-0132	CA1	DRWN:ATSEE CHKD:SKANG APPR:MLONG	F _A =0 F _E =0 F _P =0	4 PLACES ± --- ± --- 3 PLACES ± --- ± .004 2 PLACES ± 0.10 ± --- 1 PLACE ± --- ± ---	ANGULAR ± 1/2°	DRAWN BY: KS CHECKED BY: ATSEE APPROVED BY: MLONG MATERIAL NO. SEE TABLE	DATE: 1988/08/23 DATE: 2010/02/11 DATE: 2010/02/19	TITLE: C-GRID III DUAL ROW STRAIGHT SHROUDED HEADER	MOLEX INCORPORATED	DOCUMENT NO. SDA-90130	SHEET NO. 1 OF 4		

VERSION FULLY LOADED

NOTES :

1. FOR ASSEMBLY, SEE SHEET 1.
2. REFER TO LEGEND FOR PLATING OPTIONS.

90130 - * * * *

PLATING TYPES

STYLE: - 1. STRAIGHT PIN VERSION

8. VERSION WITH VOIDS


- 1 - TYPE A:
3.04µm MIN. TIN OVER 1.27µm - 2.54µm NICKEL.
- 2 - TYPE E:
0.38µm MIN. GOLD IN SELECTED AREA
& 3.04µm MIN. TIN IN SELECTED AREA
OVER 1.3µm MIN. NICKEL OVERALL.
- 3 - TYPE F:
0.76µm MIN. GOLD IN SELECTED AREA.
& 3.04µm MIN. TIN IN SELECTED AREA
OVER 1.3µm MIN. NICKEL OVERALL.
- 4 - TYPE G:
0.05 -0.10µm GOLD FLASH IN SELECTED AREA
& 3.04µm MIN. TIN IN SELECTED AREA
OVER 1.3µm MIN. NICKEL OVERALL.

VOIDED OPTIONS


NO OF CKTS	HSG CKT SIZE	VOIDED PART NUMBER	VOID POSITION	PLATING TYPE
9	10	90130-8190	3	A
9	10	90130-8309	2	F
9	10	90130-8311	1	F
11	12	90130-8212	12	E
11	12	90130-8213	2	E
11	12	90130-8313	2	F
11	12	90130-8191	3	A

	NO OF CKTS	HSG CKT SIZE	PART NUMBER			
			PLATING TYPE A	PLATING TYPE E	PLATING TYPE F	PLATING TYPE G
	6	6	90130-X106	90130-X206	90130-X306	90130-X406
	8	8	X108	X208	X308	X408
	10	10	X110	X210	X310	X410
	12	12	X112	X212	X312	X412
	14	14	X114	X214	X314	X414
	16	16	X116	X216	X316	X416
	18	18	X118	X218	X318	X418
	20	20	X120	X220	X320	X420
	22	22	X122	X222	X322	X422
	24	24	X124	X224	X324	X424
	26	26	X126	X226	X326	X426
	28	28	X128	X228	X328	X428
	30	30	X130	X230	X330	X430
	32	32	X132	X232	X332	X432
	34	34	X134	X234	X334	X434
	36	36	X136	X236	X336	X436
	38	38	X138	X238	X338	X438
	40	40	X140	X240	X340	X440
	42	42	X142	X242	X342	X442
	44	44	X144	X244	X344	X444
	46	46	X146	X246	X346	X446
	48	48	X148	X248	X348	X448
	50	50	X150	X250	X350	X450
	52	52	X152	X252	X352	X452
	54	54	X154	X254	X354	X454
	56	56	X156	X256	X356	X456
	58	58	X158	X258	X358	X458
	60	60	X160	X260	X360	X460
	62	62	X162	X262	X362	X462
	64	64	X164	X264	X364	X464
	66	66	X166	X266	X366	X466
	68	68	90130-X168	90130-X268	90130-X368	90130-X468

CHANGE DWG REVISION EC NO: S2012-0132 2011/08/16 DRWN:ATSEE CHKD:SKANG 2011/08/18 APPR:MLONG	DESCRIPTION	QUALITY SYMBOLS F_A=0 F_E=0 F_F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY KS	DATE 1988/08/23	C-GRID III DUAL ROW STRAIGHT SHROUDED HEADER				
			4 PLACES	± ---	± ---	CHECKED BY ATSEE	DATE 2010/02/11					
			3 PLACES	± ---	± .004							
			2 PLACES	± 0.10	± ---	APPROVED BY MLONG	DATE 2010/02/19	MOLEX INCORPORATED				
			1 PLACE	± ---	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
			ANGULAR ±1/2°			SEE TABLE		SDA-90130		2 OF 4		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						



VERSION FULLY LOADED



NOTES :


- MATERIAL:-
- PIN:- (0.65)/.0255 SQ. BRASS WIRE.
- HOUSING:- 15% GLASS FILLED POLYESTER
- UL 94 V-0 COLOUR BLACK

- FOR PLATING VERSIONS AND VOID VERSIONS
SEE SHEET 2.


△ MEASUREMENT POINT FOR MINIMUM PLATING THICKNESS.

- FOR PRODUCT SPEC SEE PS-99020-0001

- RECOMMENDED PCB THICKNESS: 1.60mm



RECOMMENDED P.C. BOARD
HOLE PATTERN



SECTION K-K

CKT	DIM A	DIM B	DIM C
6	(5.08)/ .200	(9.96)/ .392	(8.12)/ .320
8	(7.62)/ .300	(12.50)/ .492	(10.66)/ .420
10	(10.16)/ .400	(15.04)/ .592	(13.20)/ .520
12	(12.70)/ .500	(17.58)/ .692	(15.74)/ .620
14	(15.24)/ .600	(20.12)/ .792	(18.28)/ .720
16	(17.78)/ .700	(22.66)/ .892	(20.82)/ .820
18	(20.32)/ .800	(25.20)/ .992	(23.36)/ .920
20	(22.86)/ .900	(27.74)/ 1.092	(25.90)/ 1.020
22	(25.40)/ 1.000	(30.28)/ 1.192	(28.44)/ 1.120
24	(27.94)/ 1.100	(32.82)/ 1.292	(30.98)/ 1.220
26	(30.48)/ 1.200	(35.36)/ 1.392	(33.52)/ 1.320
28	(33.02)/ 1.300	(37.90)/ 1.492	(36.06)/ 1.420
30	(35.56)/ 1.400	(40.44)/ 1.592	(38.60)/ 1.520
32	(38.10)/ 1.500	(42.98)/ 1.692	(41.15)/ 1.620
34	(40.64)/ 1.600	(45.52)/ 1.792	(43.68)/ 1.720
36	(43.18)/ 1.700	(48.06)/ 1.892	(46.22)/ 1.820
38	(45.72)/ 1.800	(50.60)/ 1.992	(48.76)/ 1.920
40	(48.26)/ 1.900	(53.14)/ 2.092	(51.30)/ 2.020
42	(50.80)/ 2.000	(55.68)/ 2.192	(53.84)/ 2.120
44	(53.34)/ 2.100	(58.22)/ 2.292	(56.38)/ 2.220
46	(55.88)/ 2.200	(60.76)/ 2.392	(58.92)/ 2.320
48	(58.42)/ 2.300	(63.30)/ 2.492	(61.46)/ 2.420
50	(60.96)/ 2.400	(65.84)/ 2.592	(64.00)/ 2.520
52	(63.50)/ 2.500	(68.38)/ 2.692	(66.54)/ 2.620
54	(66.04)/ 2.600	(70.92)/ 2.792	(69.08)/ 2.720
56	(68.58)/ 2.700	(73.46)/ 2.892	(71.62)/ 2.820
58	(71.12)/ 2.800	(76.00)/ 2.992	(74.16)/ 2.920
60	(73.66)/ 2.900	(78.54)/ 3.092	(76.70)/ 3.020
62	(76.20)/ 3.000	(81.08)/ 3.192	(79.24)/ 3.120
64	(78.74)/ 3.100	(83.62)/ 3.292	(81.78)/ 3.220
66	(81.28)/ 3.200	(86.16)/ 3.392	(84.32)/ 3.320
68	(83.82)/ 3.300	(88.70)/ 3.492	(86.86)/ 3.420

CHANGE DWG REVISION	DESCRIPTION	REV
EC NO: S2012-0132	DRW:ATSEE	1
2011/08/16	CHKD:SKANG	2
2011/08/18	APPR:MLONG	3
CA1		

QUALITY SYMBOLS
F _A =0
F _B =0
F _P =0

GENERAL TOLERANCES (UNLESS SPECIFIED)
4 PLACES ± ---
3 PLACES ± ---
2 PLACES ± 0.10
1 PLACE ± ---
ANGULAR ± 1/2°
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
MM/IN	NTS	INCH	
DRAWN BY	DATE	TITLE	
KS	1988/08/23		
CHECKED BY	DATE		
ATSEE	2010/02/11		
APPROVED BY	DATE		
MLONG	2010/02/19		
MATERIAL NO.			
SEE TABLE			

MOLEX INCORPORATED
C-GRID III DUAL ROW STRAIGHT SHROUDED HEADER
SDA-90130
3 OF 4

	10	9	8	7	6	5	4	3	2	1		
	VERSION FULLY LOADED											
F	NO OF CKTS	HSG CKT SIZE	PART NUMBER									
			PLATING TYPE A	PLATING TYPE E	PLATING TYPE F	PLATING TYPE G						F
	6	6	90130-X106	90130-X206	90130-X306	90130-X406						
	8	8	X108	X208	X308	X408						
	10	10	X110	X210	X310	X410						
	12	12	X112	X212	X312	X412						
	14	14	X114	X214	X314	X414						
E	16	16	X116	X216	X316	X416						E
	18	18	X118	X218	X318	X418						
	20	20	X120	X220	X320	X420						
	22	22	X122	X222	X322	X422						
	24	24	X124	X224	X324	X424						
	26	26	X126	X226	X326	X426						
	28	28	X128	X228	X328	X428						
	30	30	X130	X230	X330	X430						
D	32	32	X132	X232	X332	X432						D
	34	34	X134	X234	X334	X434						
	36	36	X136	X236	X336	X436						
	38	38	X138	X238	X338	X438						
	40	40	X140	X240	X340	X440						
	42	42	X142	X242	X342	X442						
	44	44	X144	X244	X344	X444						
	46	46	X146	X246	X346	X446						
C	48	48	X148	X248	X348	X448						C
	50	50	X150	X250	X350	X450						
	52	52	X152	X252	X352	X452						
	54	54	X154	X254	X354	X454						
	56	56	X156	X256	X356	X456						
	58	58	X158	X258	X358	X458						
	60	60	X160	X260	X360	X460						
	62	62	X162	X262	X362	X462						
B	64	64	X164	X264	X364	X464						B
	66	66	X166	X266	X366	X466						
	68	68	90130-X168	90130-X268	90130-X368	90130-X468						
A												A