

MLG1005S10NJT000

Applications		Commercial Grade
Feature		Multilayer
		Non-Magnetic Core (Dielectric Ceramic)
Series	MLG Series / MLG1005S Type	
Status	PROD	





Size	
Length(L)	1.00mm +/-0.05mm
Width(W)	0.50mm +/-0.05mm
Thickness(T)	0.50mm +/-0.05mm
Recommended Land Pattern (A)	0.50mm Nom.
Recommended Land Pattern (B)	0.40mm Nom.
Recommended Land Pattern (C)	0.50mm Nom.

Electrical Characteristics	
Inductance	10nH +/-5% at 100MHz
Rated Current (Temperature Rise) [Max.]	500mA (20degC Rise)
Self-Resonant Frequency [Min.]	2.5GHz
Self-Resonant Frequency [Typ.]	3.4GHz
Q [Min.]	8 at 100MHz
Q [Typ.]	11 at 100MHz
DC Resistance [Nom.]	220mΩ
DC Resistance [Max.]	350mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	10000Pcs Min.
Weight	0.001g



MLG1005S10NJT000

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



MLG1005S10NJT000

MLG1005S10NJT000



MLG1005S10NJT000

MLG1005S10NJT000

MLG1005S10NJT000

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)

DC Bias Characteristic

no data available

Temperature Characteristic

no data available

Temperature Rise by DC

no data available