

INTRODUCTION:

Adam Tech Friction Lock Header & Housing set was designed to attach wires to a PCB. This series features a friction locking header which mates to a polarized wire housing with crimp contacts. This set provides a secure, easy to mate connection with superior electrical characteristics.

FEATURES:

Precision .025" sq. posts
Secure friction lock
Polarized anti-vibration design
Available in 2 - 20 positions

MATING CONNECTORS:

All industry standard .100 centerline compatible latching headers and housings

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL94V-2
Insulator Color: White
Contacts: Phosphor bronze and Brass

Contact Plating:

Tin over copper underplate overall

Electrical:

Operating voltage: 250V AC max.
Current rating: 3 Amps max.
Insulation resistance: 1000 MΩ min.
Dielectric withstanding voltage: 500V AC for 1 minute

Mechanical:

Recommended wire size: 22 to 28 Awg with .059" O.D. insulation max.

Temperature Rating:


Operating temperature: -40°C to +105°C

PACKAGING:

Anti-ESD plastic bags


SAFETY AGENCY APPROVALS:

UL Recognized File No. E224053
CSA Certified File No. LR1578596




ORDERING INFORMATION


FRICTION LOCK HEADER




HOUSING




CRIMP CONTACT




LHA STRAIGHT




MTA HOUSING





LHA RIGHT ANGLE



MTA-C CONTACT



LHA REVERSE RIGHT ANGLE



Recommended PCB Layout

A = .100 [2.54] x No. of Spaces
B = .100 [2.54] X No. of Spaces + .100 [2.54]
C = .100 [2.54] X No. of Spaces + .122 [3.11]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADAM TECH:](#)

[LHA-09-TS](#) [LHA-06-TS](#) [LHA-03-TS](#) [LHA-08-TS](#) [LHA-10-TS](#) [LHA-04-TS](#) [LHA-05-TS](#) [LHA-02-TS](#) [LHA-07-TS](#)