

Features


Regulated Converters

- 6-Side Shielding
- External ON/OFF control
- 1.6kVDC Isolation
- UL/CSA/EN-60950-1 Certified
- Wide 4:1 Input Voltage Range
- Continuous Short Circuit Protection
- Efficiency up to 91%
- Fixed Switching Frequency

RECOM
DC/DC Converter

REC20-Z

20 Watt
2" x 1"
Single and Dual Output



UL
E224736

IEC/EN60950-1 Certified
UL60950 Certified
CSA C22.2 NO. 60950 Certified
EN55022 Certified


Description

The REC20-xxxxS_DZ -series offer single and dual regulated outputs in a 2"x1" package with 1.6kVDC isolation and are suitable for higher power industrial applications. Remote on/off control is standard. The higher current outputs have raised output voltages to compensate for track losses as standard. The converter is fully certified to UL/EN/IEC safety standards.

Selection Guide

Part Number	Input Voltage Range [VDC]	Output Voltage [VDC]	Output Current [mA]	Efficiency typ. [%]	max. Capacitive Load [μ F]
REC20-243.4SZ	9-36	3.4	5000	88	13000
REC20-245.1SZ	9-36	5.1	4000	90	9600
REC20-2412SZ	9-36	12	1667	89.5	1650
REC20-2415SZ	9-36	15	1333	90	1050
REC20-2405DZ	9-36	$\pm$ 5	$\pm$ 2000	87	$\pm$ 4800
REC20-2412DZ	9-36	$\pm$ 12	$\pm$ 834	89	$\pm$ 625
REC20-2415DZ	9-36	$\pm$ 15	$\pm$ 667	89	$\pm$ 525
REC20-483.4SZ	18-75	3.4	5000	88	13000
REC20-485.1SZ	18-75	5.1	4000	90	9600
REC20-4812SZ	18-75	12	1667	89.5	1650
REC20-4815SZ	18-75	15	1333	90.5	1050
REC20-4805DZ	18-75	$\pm$ 5	$\pm$ 2000	87	$\pm$ 4800
REC20-4812DZ	18-75	$\pm$ 12	$\pm$ 835	90	$\pm$ 625
REC20-4815DZ	18-75	$\pm$ 15	$\pm$ 667	91	$\pm$ 525

Model Numbering



Ordering Examples:

REC20-4812SZ, Single Output, 18-75Vin (4:1) and 12Vout
REC20-2412DZ, Dual Output, 9-36Vin (4:1) and $\pm$ 12Vout



Specifications (measured @ $t_a = 25^\circ\text{C}$, nominal input voltage, full load and after warm up unless otherwise specified)

BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Typ.	Max.
Input Voltage Range	nom. Vin= 24V nom. Vin= 48V	9VDC 18VDC		36VDC 75VDC
Start/up Time			10ms	
Under Voltage Lockout (UVLO)	nom. Vin= 24V	DC-DC ON DC-DC OFF	9VDC 7.5VDC	
	nom. Vin= 48V	DC-DC ON DC-DC OFF	18VDC 16VDC	
Output Voltage Trimming	see calculation below			$\pm 10\%$
CTRL ON/OFF	DC-DC ON DC-DC OFF			Open or $2.5\text{V} < V_r < 12\text{V}$ Short or $0\text{V} < V_r < 1.2\text{V}$
Internal Operating Frequency			300kHz	
Minimum Load		0%		
Output Ripple and Noise ⁽¹⁾				100mVp-p

Notes:

Note1: Ripple and Noise is measured with a 20MHz bandwidth and a 0.1 μF ceramic capacitor.

Output Voltage Trimming



Vout	3.4V	5.1V	12V	15V
R1	4.71 k Ω	2.3 k Ω	19.43 k Ω	25.6 k Ω
R2	2.7 k Ω	2.2 k Ω	5.1 k Ω	
R3	15 k Ω	9.1 k Ω	36 k Ω	
Vref	1.24 V	2.5 V		

Trim Calculation

V_{out} = nom. output voltage

ΔV_{out} = output voltage trim

R_{up} = trim up resistor

R_{down} = trim down resistor

a = trim up factor

b = trim down factor

$$\Delta V_{out} = V_{out} - V_{out_{trimmed}}$$

$$R_{up} = \left[\frac{a \cdot R_2}{R_2 - a} \right] - R_3 = k\Omega$$

$$R_{down} = \left[\frac{b \cdot R_1}{R_1 - b} \right] - R_3 = k\Omega$$

$$a = \left[\frac{V_{ref}}{(V_{out} + \Delta V_{out}) - V_{ref}} \right] \cdot R_1 = k\Omega$$

$$b = \left[\frac{(V_{out} + \Delta V_{out}) - V_{ref}}{V_{ref}} \right] \cdot R_2 = k\Omega$$

Trim Up:

$V_{out} = 5.1\text{V}$, $\Delta V_{out} = 0.51\text{V}$ (10%), $V_{ref} = 2.5\text{V}$

$$a = \left[\frac{2.5\text{V}}{(5.1\text{V} + 0.51\text{V}) - 2.5\text{V}} \right] \cdot 2.3\text{k}\Omega = \mathbf{1.843\text{k}\Omega}$$

$$R_{up} = \left[\frac{1.843\text{k}\Omega \cdot 2.2\text{k}\Omega}{2.2\text{k}\Omega - 1.843\text{k}\Omega} \right] - 9.1\text{k}\Omega = \mathbf{2.255\text{k}\Omega}$$

Trim down:

$V_{out} = 5.1\text{V}$, $\Delta V_{out} = -0.51\text{V}$ (-10%), $V_{ref} = 2.5\text{V}$

$$b = \left[\frac{[5.1\text{V} + (-0.51\text{V})] - 2.5\text{V}}{2.5\text{V}} \right] \cdot 2.2\text{k}\Omega = \mathbf{1.839\text{k}\Omega}$$


$$R_{down} = \left[\frac{1.839\text{k}\Omega \cdot 2.3\text{k}\Omega}{2.3\text{k}\Omega - 1.839\text{k}\Omega} \right] - 9.1\text{k}\Omega = \mathbf{0.080\text{k}\Omega}$$

continued on next page


Specifications (measured @ $t_a = 25^\circ\text{C}$, nominal input voltage, full load and after warm up unless otherwise specified)

Efficiency vs. Load

REC20-485.1SZ



REC20-4815SZ




REGULATIONS


Parameter	Condition	Type	Values
Output Accuracy			$\pm 1.0\%$ max.
Line Regulation	low line to high line, full load		$\pm 0.2\%$ max.
Load Regulation	0% to 100% load	single output	$\pm 0.5\%$ max.
		dual output	$\pm 1.0\%$ max.
Cross Regulation	25% to 100% load	dual output	$\pm 5.0\%$ max.
Transient Response Recovery Time	25% load step change		250 μs typ.

Deviation vs. Load

REC20-485.1SZ



REC20-2415SZ





Specifications (measured @ $t_a = 25^\circ\text{C}$, nominal input voltage, full load and after warm up unless otherwise specified)

PROTECTIONS		
Parameter	Condition	Value
Short Circuit Protection (SCP)	below $100\text{m}\Omega$	continuous, automatic recovery
Over Voltage Protection (OVP)	3.4Vout Zener Diode Clamp 5.1Vout 12Vout 15Vout	4.5VDC typ. 7VDC typ. 16VDC typ. 20VDC typ.
Over Load Protection (OLP)		180% typ.
Isolation Voltage	I/P to O/P tested for 1 minute	1.6kVDC
Isolation Capacitance		1200pF typ.
Isolation Resistance		$1\text{G}\Omega$ min.

ENVIRONMENTAL		
Parameter	Condition	Value
Operating Temperature Range	with derating (see graph)	-40°C to $+100^\circ\text{C}$
Maximum Case Temperature		$+105^\circ\text{C}$
Temperature Coefficient		$0.02\%/^\circ\text{C}$ typ.
Thermal Impedance	natural convection (0.1m/s)	12°C/W
Operating Altitude		5000m
Operating Humidity	non-condensing	5% - 95% RH max.
Vibration		MIL-STD-202G
MTBF	according to MIL-HDBK-217F G.B., $+25^\circ\text{C}$, referring to REC20-485.1SZ	1098×10^3 hours

Derating Graph

@ nominal input voltage, full load and natural convection (0.1m/s)



Notes:

Note2: For more details, please contact our technical support service at techsupportAT@recom-power.com

Specifications (measured @ $t_a = 25^\circ\text{C}$, nominal input voltage, full load and after warm up unless otherwise specified)

SAFETY AND CERTIFICATIONS


Certificate Type	Report / File Number	Standard
CB General Safety	E224736	IEC60950-1, 2nd Edition, 2013
UL General Safety		UL60950-1, 2nd Edition, 2014
EN General Safety		EN60950-1, 2nd Edition, 2013
CAN/CSA General Safety		C22.2 No. 60950-1-07, 2014

EMC Compliance	Condition	Standard / Criterion
EMI	without external filter with external filter (see filter suggestions)	EN55022, Class A EN55022, Class B
ESD	Air: $\pm 8\text{kV}$; Contact: $\pm 4\text{kV}$	EN61000-4-2, Criteria B
Radiated Immunity	10V/m	EN61000-4-3, Criteria A
Fast Transient	$\pm 1\text{kV}$	EN61000-4-4, Criteria B
Surge ⁽³⁾	$\pm 1\text{kV}$	EN61000-4-5, Criteria A
Conducted Immunity	10Vr.m.s	EN61000-4-6, Criteria A
Power Magnetic Field	50Hz 1A/m (r.m.s)	EN61000-4-8, Criteria A

Notes:

Note3: An external MOV is required if the module has to meet EN61000-4-5. The MOV suggest: NichTek SVI32-380

EMC Filtering - Suggestions for Class B




MODEL	C1	C2	L1	C3	C4
REC20-24xxS(D)Z	4.7 μF /50V	4.7 μF /50V	1.5mH CMC	1000pF/2kV	1000pF/2kV
REC20-48xxS(D)Z	2.2 μF /100V	2.2 μF /100V	2.0mH CMC	1000pF/2kV	1000pF/2kV

DIMENSION and PHYSICAL CHARACTERISTICS

Parameter	Type	Value
Material	Case	nickel plated copper
	Base	non conductive black plastic
	PCB	FR4
	Potting	silicone (UL94 V-0)
Package Dimension (LxWxH)		50.8 x 25.4 x 10.2mm
Package Weight		27g typ.

continued on next page

Specifications (measured @ ta= 25°C, nominal input voltage, full load and after warm up unless otherwise specified)



PACKAGING INFORMATION		
Packaging Dimension (LxWxH)	Tube	520.0 x 54.5 x 21.0mm
Packaging Quantity		18pcs
Storage Temperature Range		-55°C to +125°C