





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
1	-		G1	REDRAWN, ET00-0212-04	19 OCT 2004	HY GT
			G2	REVISED PER - ECO-09-026346	26NOV09	KK AEG





SECTION A - A



- 1 POLYETHYLENE
- 2 PA6 UNFILLED, UL 94 V2, VERSION ACCORDING TO IEC 60695-2-11, IEC 60335-1, GLOW WIRE.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE 3	NATURAL	SEE NOTE 2	3-180930-0	G
	ORANGE	SEE NOTE 1	2-180930-9	G
	GRAY		2-180930-7	G
	BROWN		2-180930-6	G
OBSOLETE 3	BLACK		2-180930-5	G
	YELLOW		2-180930-4	G
	BLUE		2-180930-3	G
	GREEN		2-180930-2	G
	RED		2-180930-1	G
	NATURAL		2-180930-0	G
NOTE	COLOUR	MATERIAL	TYCO P/N	REV



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.4
1 PLC ±0.4
2 PLC ±0.4
3 PLC ±0.4
4 PLC ±0.4
ANGLES ±1°
FINISH -

DWN

H. YAALI

13JUL2004

CHK

-

APVD

-

PRODUCT SPEC

108-20035

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

tyco Electronics AMP Italia S.p.A.
C.so F.lli Cervi, 15 COLLEGNO (TO)

NAME

INSULATING BOOT

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=180930

RESTRICTED TO

-

SCALE

3:1

SHEET

1

OF

1

REV

G2