



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

Customer Specification

PART NO. 6426

Construction

			Diameters (In)			
1) Component 1	51 X 1 PAIR					
a) Conductor	22 (7/30) AWG TC		0.030			
b) Insulation	0.013" Wall, Nom. PVC		0.056			
(1) Print	ALPHANUMERIC NUMBERS - 1-ONE ALTERNATING AND INVERTED					
(2) Color Code	Alpha Wire Color Code BR					
Pair	Color	Pair	Color	Pair		
1	BLACK#1-RED#1	18	BLACK#18-RED#18	35		
2	BLACK#2-RED#2	19	BLACK#19-RED#19	36		
3	BLACK#3-RED#3	20	BLACK#20-RED#20	37		
4	BLACK#4-RED#4	21	BLACK#21-RED#21	38		
5	BLACK#5-RED#5	22	BLACK#22-RED#22	39		
6	BLACK#6-RED#6	23	BLACK#23-RED#23	40		
7	BLACK#7-RED#7	24	BLACK#24-RED#24	41		
8	BLACK#8-RED#8	25	BLACK#25-RED#25	42		
9	BLACK#9-RED#9	26	BLACK#26-RED#26	43		
10	BLACK#10-RED#10	27	BLACK#27-RED#27	44		
11	BLACK#11-RED#11	28	BLACK#28-RED#28	45		
12	BLACK#12-RED#12	29	BLACK#29-RED#29	46		
13	BLACK#13-RED#13	30	BLACK#30-RED#30	47		
14	BLACK#14-RED#14	31	BLACK#31-RED#31	48		
15	BLACK#15-RED#15	32	BLACK#32-RED#32	49		
16	BLACK#16-RED#16	33	BLACK#33-RED#33	50		
17	BLACK#17-RED#17	34	BLACK#34-RED#34	51		
c) Pair	2/Cond Cabled Together					
(1) Twists:	8.0 Twists/foot (approx.)					
2) Cable Assembly	51 Components Cabled					
a) Twists:	1.1 Twists/foot (min)					
b) Core Wrap	Clear Mylar Tape, 25% Overlap, Min.					
3) Shield:	Alum/Mylar Tape, 25% Overlap, Min.					
a) Foil Direction	Foil Facing In					
b) Drain Wire	24 (7/32) AWG TC					
4) Jacket	0.075" Wall, Nom.,PVC		0.914 (0.956 Max.)			
a) Color(s)	SLATE					
b) Print	ALPHA WIRE-* P/N 6426 51PR 22 AWG SHIELDED 105C (UL) TYPE PLTC SUN RES OR TYPE CM OR C(UL) 60C TYPE CMG FT4 ROHS * = Factory Code <i>[Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]</i>					

Applicable Specifications

1) UL	CM	105°C
	PLTC	105°C
	SUN RES	
2) CSA International	C(UL) TYPE CMG	60°C
	FT4	

Environmental

1) EU Directive 2002/95/EC(RoHS):	All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.
2) California Proposition 65:	The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-20 to 105°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	564 Lbs, Maximum
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	300 V _{RMS}
2) Mutual Capacitance	32 pf/ft @1 kHz, Nominal
3) Ground Capacitance	58 pf/ft @1 kHz, Nominal
4) Characteristic Impedance	71
5) Inductance	0.19 µH/ft, Nominal
6) Conductor DCR	16.6 /1000ft @20°C, Nominal
7) OA Shield DCR	8.2 /1000ft @20°C, Nominal

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	48 x 26 x 18 Continuous length
b) 500 FT	30 x 14 x 12 Continuous length
<i>[Spool dimensions may vary slightly]</i>	

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207

Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

RoHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number:6426


6426 , RoHS-Compliant Commencing With 8/1/2005 Production

*This document certifies that the Alpha part numbers cited above are manufactured in accordance with Directive 2002/95/EC of the European Parliament and of the Council of 27 January 2003, better known as the RoHS Directives, with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. The reader is referred to these Directives for the specific definitions and extents of these Directives. **No Exemptions are required for RoHS Compliance on this item.***

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE)	
Including Deca-BDE	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire Company:



Dave Watson, Director of Engineering & QA

11/1/2012

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[6426 SL002](#)