








16 HEX

2.80 [0.110]

RECOMMENDED
MOUNTING HOLE

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8	FERRULE	COPPER	NICKEL	1		DRAWN	GRS	01/20/09						
7	SLEEVE	DELTRIN	NATURAL	1		CHECKED								
6	HEX NUT	BRASS	NICKEL	1		ISSUED			PART DESCRIPTION TNC BULKHEAD CRIMP JACK (FOR RG-174/U, 316/U DOUBLE BRAID)					
5	LOCK WASHER	BRASS	NICKEL	1		SHEET	1 OF 1							
4	GASKET	SILICONE	RED	1										
3	CONTACT PIN	BER. COPPER	GOLD	1				PART NO. 122358						
2	INSULATOR	DELTRIN	NATURAL	1										
1	BODY	BRASS	NICKEL	1			DWG. NO. 122358.DWG REV. NC SIZE A SCALE NA							
	DESCRIPTION	MATERIAL	FINISH	QTY										