





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		K2	REVISED PER ECR-12-013219	08JAN13	KH	KR

D

C


B

A



- 1 PREMIER FASTON TERMINALS, BASE P/N 42219 ARE USED FOR -1. LOW-INSERTION FASTONS, BASE P/N 63306 ARE USE FOR -2.
- 2 NICKEL PLATE 0.00381 [.000150] MIN
- 3 TIN PLATE 0.002032 [.000080] MIN.
- 4 MATERIAL: HOUSING - 4/6 NYLON (150°C)
TERMINAL - SEE TABLE
- 5 FINISH: HOUSING - COLOR, BLACK
TERMINAL - SEE TABLE

OBSOLETE	BULK	#4M HD BRASS	3 TIN
OBSOLETE	BULK	#2 HD STEEL	2 NICKEL
	STANDARD	BRASS	3 TIN
	STANDARD	#2 HD STEEL	2 NICKEL
	PACKAGING	TERMINAL MATERIAL	TERMINAL FINISH

2.79-4.32 [.110-.170] DIA		0.8-2.0 mm ² [18-14]	0.813 [.032]	5-521011-2			
				5-521011-1			
				521011-2			
				521011-1			
INSULATION RANGE		WIRE SIZE	MATING TAB THK ±0.025 [±.001]	PART NO.			
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN JR RUTH 12/7/92	 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK MS FEHER 12/7/92					
		APVD V KARACIEVSKY 12/7/92		NAME ASSEMBLY, ULTRA-POD, RECEPTACLE, 6.35 [.250] SERIES			
		PRODUCT SPEC 108-1285					
		APPLICATION SPEC 114-2124					
MATERIAL 		FINISH 		SIZE A2	CAGE CODE 00779	DRAWING NO C=521011	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 5:1		SHEET 1 of 1		REV K2