




LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	OWN
			J	REVISED PER ECR-13-004343	30JUL13	KH
						APVD
						KR

- 1 FITS 0.81±0.025 X 4.75 [.032±.001 X .187] TAB
- 2 WIRE SIZE: 0.3–0.9mm² [22–18 AWG], STRANDED ONLY.
 STRIP LENGTH 7.14 [.281]
- 3 INSULATION SIZE: 4.19 [.165] MAX DIA.
- 4 SUPPLIED AS LOOSE PIECE



OBSOLETE	TYPE 6/6 NYLON	RED TRANSLUCENT	0.41 [.016] #4H PH BRZ	TIN	2–520337–4
	TYPE 6/6 NYLON	RED TRANSLUCENT	BRASS	TIN	2–520337–2
	MATERIAL	COLOR	MATERIAL	FINISH	PART NO
HOUSING			TERMINAL		
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN P FORTNEY	8/10/90	TE TE Connectivity RECEPTACLE ASSEMBLY,ULTRA–FAST FLAG, 4.75 [.187] SERIES,LOOSE PIECE
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK MS FEHER	8/23/90	
		0 PLC ± – 1 PLC ± – 2 PLC ± 0.38 [.015] 3 PLC ± – 4 PLC ± – ANGLES ± ± –	APVD D BRATINA	8/24/90	
			PRODUCT SPEC 108–2043		
MATERIAL SEE TABLE		FINISH SEE TABLE	APPLICATION SPEC 114–2123		SIZE A2
			WEIGHT –		CAGE CODE 00779
			CUSTOMER DRAWING		DRAWING NO G-520337
			SCALE 8:1	SHEET 1 of 1	REV J
					RESTRICTED TO –

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-520337-1](#)