

Features

Regulated Converters

- 1kVDC & 2kVDC Isolation
- UL94V-0 Package Material
- RoHS 6/6
- Toroidal Magnetics
- Optional Continuous Short Circuit Protected
- Built-In EN55022 Class A Filter

Description

The R1Z series DC/DC converter has been designed for isolating or converting DC power rails where an SMD format with regulated output is required, although it is no larger than a standard unregulated SMD converter.

Selection Guide

Part Number SMD	2kVDC	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Max Capacitive Load ⁽¹⁾
R1Z-xx3.3*	(/H)	3.3, 5, 12, 15, 24	3.3	303	2200µF
R1Z-xx05*	(/H)	3.3, 5, 12, 15, 24	5	200	1200µF
R1Z-xx09*	(/H)	3.3, 5, 12, 15, 24	9	111	680µF
R1Z-xx12*	(/H)	3.3, 5, 12, 15, 24	12	84	680µF
R1Z-xx15*	(/H)	3.3, 5, 12, 15, 24	15	66	470µF

xx= Input Voltage (other input and output voltage combinations available on request)

*add suffix -R for tape & reel packing e.g. R1Z-0505-R

*add suffix /P for continuous short circuit protection, e.g. R1Z-0505/P-R

Specifications (measured at T_A = 25°C, nominal input voltage, full load and after warm-up)

Input Voltage Range	±5%	
Output Voltage Accuracy	±2%	
Line Voltage Regulation	1% max.	
Load Voltage Regulation	1% max.	
Output Ripple and Noise (at 20MHz BW)	100mVp-p max.	
Operating Frequency	20kHz min. / 40kHz typ. / 80kHz max.	
Efficiency at Full Load	50% min. / 60% typ.	
Minimum Load	10% (2)	
No Load Power Consumption	134mW min. / 217mW typ. / 350mW max.	
Isolation Voltage	(tested for 1 second)	1000VDC
	(rated for 1 minute**)	500VAC / 60Hz
Isolation Voltage	H-Suffix (tested for 1 second)	2000VDC
	H-Suffix (rated for 1 minute**)	1000VAC / 60Hz
Isolation Capacitance	70pF typ.	
Isolation Resistance	10 GW min.	
Short Circuit Protection	1 Second	
P-Suffix	Continuous	
Operating Temperature Range (natural convection)	-40°C to +70°C (see Graph)	
Storage Temperature Range	-55°C to +125°C	
Reflow Temperature	ROHS compliant	245°C (30 sec) max.
Vapor Phase Process		230°C (90 sec) max.
	(for more details see Application Notes)	
Relative Humidity	95% RH	
Package Weight	1.6g	
Packing Quantity	33 pcs per tube 250 pcs per Reel	
MTBF	R1Z (+25°C)	using MIL-HDBK 217F 2203 x 103 hours
	(+70°C)	using MIL-HDBK 217F 391 x 103 hours
	R1Z/P (+25°C)	using MIL-HDBK 217F 2387 x 103 hours
	(+70°C)	using MIL-HDBK 217F 641 x 103 hours

For detailed information see Application Notes chapter "MTBF"

Conducted / Radiated Emissions	EN55022	Level A
EN General Safety	Report: SPCLVD1211033-3	EN60950-1:2006 + A12:2011
EN Medical Safety	Report: MDD1205098-4 + RM1205098-4	IEC/EN 60601-1 3rd Edition
	Medical Report + ISO14971 Risk Assessment	
UL General Safety	Report: E358085	UL60950-1, 2nd Edition

ECONOLINE

DC/DC-Converter

with 3 year Warranty

RECOM

1 Watt SMD Miniature Isolated Single Output




E358085



EN-60950-1 Certified
EN-60601-1 Certified*
UL-60950-1 Certified
(*/H suffix)

R1Z

Derating-Graph (Ambient Temperature)




*Any data referred to in this datasheet are of indicative nature and based on our practical experience only. For further details, please refer to our Application Notes.


Refer to Application Notes

Typical Characteristics


R1Z-3.3xx/P




R1Z-05xx/P




R1Z-12xx/P




R1Z-15xx/P




R1Z-3.3xx



R1Z-05xx



R1Z-12xx




Notes

Note 1: Maximum capacitive load is defined as the capacitive load that will allow start up in under 1second without damage to the converter


Note 2: The R1Z series requires a minimum of 10% load on the output to maintain specified regulation. Operating under no-load conditions will not damage these devices; however, they may not meet all listed specifications.

R1Z-15xx




Package Style and Pinning (mm)

10 PIN Single SMD Package



Recommended Footprint Details



Ordering Example: R1Z-0505 (5V Input, 5V Output, not short circuit protected)
R1Z-0505/HP (5V Input, 5V Output, 2kVDC Isolation and short circuit protection)

Pin Connections

Pin #	Function
1	-Vin
2	+Vin
4	-Vout
5	-Vout
7	+Vout
10	NC

NC= No Connection

XX.X ± 0.5 mm
XX.XX ± 0.25 mm

The product information and specifications are subject to change without prior notice. RECOM products are not authorized for use in safety-critical applications (such as life support) without RECOM's explicit written consent. A safety-critical application is defined as an application where a failure of a RECOM product may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The buyer shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.