


Data Sheet

Type Number: 6016
Designation IEC: CR 2016
System: Li-Manganese dioxide /
 Organic Electrolyte
UL Recognition: MH 13654 (N)
Nominal Voltage [V]: 3
Typical Capacity C [mAh]: 90
 Load 15 kOhm, at 20 °C down to 2.0 V
Weight, approx [g]: 1,8
Volume [ccm]: 0,5
Coding: Manufacturing Month/Year
 by Letter Code



Temperature Ranges [°C]: **min.** **max.**
Storage: -55 70
Discharge: -20 65
Dimensions [mm]: **min.** **max.**
Diameter [A]: 19,7 20
Height [B]: 1,4 1,6
Shoulder Diameter[E]: 18,4
Shoulder Height [C]: 0,1

Segment: Electronic

Main Applications: Watch
 Photo
 Electronic

Typical Capacities (at 20° C):

Discharge Type:	Load	End Voltage:	2.0 V
Continuous	15000	Ω Time:	450 h
24h/d, 7d/w		Capacity [mAh]:	90
Current [μA]: 200		Energy [mWh]:	270