





Disconnect Terminals

Disconnect Terminals		SAKR	SAKR-D With StB test points	SAKC 4	SAKC 10
					
		Lever	Plug	Pull Pin	Pull Pin
Terminal Block Selection Data					
Available Options	Version				
With 2 StB test points KrS PA		0412260000	0183360000	0546460000*	
With 2 StB test points KrS Blue PA		0412280000	0183380000		
With 2 StB test points KrS without diode PA			0413160000*		
Beige PA		0412160000	0172160000	0412960000* 0299960000*	
Blue PA		0412180000	0172180000		
Without diode PA			0413060000** 0185760000**		
With diode PA			0263360000*** 0299560000***		
Orange PA		1461960000			
KrG		0412120000		0340720000 0357520000	0324020000
KrS					0324030000
With 1 StB test point KrG					1404520000
With 2 StB test points KrG		0412220000		0340620000 0357620000	0324120000 1404620000
With 2 StB test points KrS					0324130000
Dimensions					
Width / Length / Height mm (in.)	for TS 32 11 for TS 35 12	6.5/42/40.5 (.26/1.81/1.60)	6.5/42/57 (.26/1.81/2.24)	6.5/40/67 (.26/1.57/2.64)	12/65/70.5 (.47/2.56/2.76)
Insulation stripping length	mm (in.)	6.5/46/38 (.26/1.81/ 1.50)	6.5/46/54.5 (.26/1.81/2.14)	6.5/49.5/59.5 (.26/1.95/2.34)	12/65/66 (.47/2.56/2.6)
Technical Data					
Rated voltage / rated current / wire size	UL CSA VDE	300 V / 10 A / #22...12 AWG 300 V / 10 A / #26...12 AWG 380 VAC / 10 A / 4 mm²	300 V / 10 A / #22...12 AWG 300 V / 10 A / #22...12 AWG 380 VAC / 10 A / 4 mm²	300 V / 25 A / #22...12 AWG 300 V / 25 A / #22...10 AWG 380 VAC / 25 A / 4 mm²	600 V / 25 A / #22...8 AWG 600 V / 25 A / #20...10 AWG 500 VAC / 27 A / 10 mm²
Torque	Nm (lb. in.)	0.6 / 0.5 StB (8.0 / 4.5 StB)	0.6 / 0.5 StB (8.0 / 4.5 StB)	0.6 / 0.5 StB (7.0 / 4.5 StB)	3.0 (26.0)
Clamping screw	M	3	3	3	4
Selected Accessory Data*					
End Plate (thickness mm)		Type Part No.	Type Part No.	Type Part No.	Type Part No.
Beige PA		AP (1.5) 0211360000	AP (1.5) 0211360000		
Blue PA		AP (1.5) 0211380000			
KrG		AP (1.5) 0211320000		AP (1.5) 0117920000	AP (3.0) 0146720000
KrS					AP (3.0) 0146730000
Partition (thickness mm)					
PA				TW (1.5) 0130160000	TW (1.5) 0242960000
KrG					TW (3.0) 0242920000
KrS					TW (3.0) 0242930000
HP		TW (1.0) 0297100000	TW (1.0) 0297100000	TW (1.0) 0297100000	
Jumpers					
	Final number indicates number of poles. See the Accessories Section for more information. When using QB, maximum conductor connection is 2.5 mm².	QB 2 0482700000 QB 3 0482800000 QB 4 0482900000 QB 25 bare* 0134000000	QB 2 0482700000 QB 3 0482800000 QB 4 0482900000 QB 25 bare* 0134000000	QB 2 0482700000 QB 3 0482800000 QB 4 0482900000 QB 25 bare* 0134000000	QL 2 0135500000 QL 3 0135600000 QL 4 0135700000 QL 10 0338500000
QB	Connection sleeve				VH 14 0299700000
	Fixing screw				BS M 4 x 20 0362800000
	Lock washer				SS M 4 0136400000
	Insulation sleeve				
Plugs					
	BST 4			BST 4 red 1339060000	
BST 4	Lock-out device	WTR/SAKR 9525900000			
Dummy plug	Test plug	PS 2.3 0180400000	PS 2.3 0180400000	PS 2.3 0180400000	PS 4 0299600000
	Socket				StB 13.5 0135200000
	Diode plug without diode		DLS 2 0321060000		
	Diode plug with diode 1N4007		DLS 2 0630160000		
	Disconnecter plug (spare)			TST 1380600000	TST 0462700000
Extraction Tool				0623060000	
Marking Tags	Print				
Note: Part numbers are shown for a single card of pre-printed tags numbered 1-50.	Consecutive horizontal	DEK 5/6.5 0468160001	DEK 5/6.5 0468160001	DEK 5/6.5 0468160001	DEK 5/6 0468660001
	Consecutive vertical	DEK 5/6.5 0468260001	DEK 5/6.5 0468260001	DEK 5/6.5 0468260001	DEK 5/6 0468760001