

COMPACT KVM-OVER-IP PLUS LOCAL ACCESS FOR DISTRIBUTED SERVER MANAGEMENT

The Lantronix® Spider Duo® KVM-over-IP is the newest in the popular Spider family of remote KVM solutions. Spider Duo provides secure, remote KVM (keyboard, video and mouse) over-IP capabilities as well as transparent local access.

Flexible KVM-over-IP

The Spider Duo is ideal for those who need local access, as well as the flexibility of KVM-over-IP in a single integrated solution. Its palm-sized, “zero-U” design is perfect for space-constrained applications. What’s more, Spider Duo requires no additional software and allows full BIOS level control of the host system.

Secure Remote Management

Spider Duo makes administration a breeze. Using integrated Virtual Media, users can transfer files, perform upgrades, install patches, redirect local drives and perform full system upgrades by ISO file. Coupled with the optional single port PCU (power control unit), authorized users can also initiate system reboots over the network. Spider Duo allows complete local, plus remote management of the host machine anytime, from virtually anywhere. It provides reliable, secure access to servers located in data centers, kiosks, regional offices, campuses, ATMs, Point-of-sale (POS), training centers, or test and development labs.



Spider Duo Highlights:

- Reduce costs and decrease downtime by remotely managing PCs and servers, down to the BIOS level, while still allowing transparent local access
- Transfer files, install patches, perform upgrades remotely with Virtual Media
- Remotely manage power with the optional power control unit
- Easy configuration and installation with color coded connectors—local and remote management are up and running in minutes

Features and Specifications

> Security

- In-Band (Ethernet) - Dual Ethernet ports
- Hardware based encryption of keyboard, mouse and video data
- IP Source Address Filtering
- Remote Authentication: LDAP, RADIUS, Active Directory
- User/Group management with permissions control
- Configurable port numbers (HTTP, HTTPS, Telnet, SSH)
- Selective disable of Telnet/SSH

> Access

- Local access and up to 8 simultaneous remote users

> Target Server Requirements

- Supports Multiple Operating Systems:
Windows 2000/2003/2008/XP/Vista/7, Unix, Linux, or
MAC OSX 10
- Keyboard/mouse: 1 USB, 1 PS/2 keyboard, and 1 PS/2
mouse connector
- Video Interface: HD15 VGA video output (up to
1600x1200@60Hz)

> Client System Requirements

- Internet Explorer 6.0+, Netscape 5.0+, Firefox 3.0+,
Safari 2.0+
- PIII Processor equivalent or better (recommended)
- Sun Java 2 Runtime Environment
- Telnet/SSH client for command line (CLI) access

> Interfaces

- Network: 10/100Base-T Ethernet Port with activity
indicators (RJ45)
- Serial: RS-232, up to 115,200 bps for serial device
pass-through, unit configuration or PCU controller
- USB
- Local KVM connector
- Computer input connector

> Cables

- Includes local KVM and computer input USB or USB and
PS/2, 21.6" VGA cables

> Environmental

- Operating: 0° to 45° C (32° to 115° F)
- Storage: -20° to 70° C (-4° to 158° F)
- Humidity: 0 to 95% RH (non-condensing)
- Heat Dissipation: 4-8 Watts (14-28 BTU/hr)

> Power Requirements

- Input: 5 VDC @ 1.6A max.

> Certifications

- UL/CUL (CSA-22.2 No. 60950-1-03 / UL-60950-1)
- CE - IEC 60950-1
- C-Tick
- FCC Part 15, Equipment Class A
- VCCI V-3/2006.04 Class A
- AS/NZS CISPR 22: 2006 Class A
- EN55022:1998 +A1:2000 +A2:2003 Class A
- EN61000-3-2: 2000 +A2: 2005 Class A
- EN61000-3-3: 1995 +A1: 2001
- EN55024: 1998 +A1:2001 +A2:2003
- RoHS Compliant

> Warranty

- 2-year limited warranty

> Form Factor

- Dimensions: (H x W x D) 13.2 x 5.8 x 3.6 cm
(5.2 x 2.3 x 1.4 in)
- Weight: USB: 269g (9.50 oz), PS/2: 278g (9.80 oz)



Ordering Information

United States

Call: 800.422.7055
Email: sales@lantronix.com
Buy Online: <http://www.lantronix.com>
NASDAQ: LTRX

Europe

Call: +31 (0) 76.52.3.6.74 4
Email: EMEA@lantronix.com

Japan

Call: +81.3.6277.8802
Email: japan_sales@lantronix.com

China

Call: +86.021.6237.8868
Email: Shanghai@lantronix.com

> Part Number

SLSLP400USB-01

SLSLP400PS2-01

> Description

1 Port Local plus Remote KVM-over-IP with USB
Connectors; 21.6" VGA cables

1 Port Local + Remote KVM-over-IP with PS/2 and
USB Connectors; 21.6" VGA cables

> Accessories

PCU100-01

500-199-R

500-200-R

520-104-R

> Description

Single port power control unit, 100-240VAC,
50/60Hz, 10A (Includes IEC320/C13 to NEMA
inlet and IEC320/C14 to IEC320/C13 outlet power
cables)

Extended length cable (computer input) USB
connector; 59" VGA cable


Extended length cable (computer input) PS/2 and
USB connectors; 59" VGA cable

Replacement DC Power Supply with International
Adapters (100-240VAC, 50-60 Hz; 5 VDC @ 2A)



Remotely manage power with
the optional power control unit.

Spider Duo Application Example



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lantronix](#):

[SLSLP400USB-01](#) [SLSLP400PS2-01](#) [PCU100-01](#) [500-199-R](#) [500-200-R](#) [520-104-R](#)