



UNIVERSAL AC INPUT AC-DC 19" COMPATIBLE EUROCARD MULTI-OUTPUT 45 WATTS SWITCHING MODE POWER SUPPLIES HIU45 SERIES



FEATURES:

- ACCOMMODATE UNIVERSAL AC SOURCES
- 19" COMPATIBLE EUROCARD FORMAT
- MEET UNIVERSAL SAFETY STANDARDS
- EMI MEET CISPR PUB. 22 & FCC CLASS B
- CE MARKING COMPLIANCE
- 3U X 6HP X 160MM FOR VMEbus STANDARD

SPECIFICATION

INPUT SPECIFICATION

Input Voltage: Range Typ. 90-264Vac.
 Rating 100 to 240Vac.
Input Connector: DIN 41612 at rear.
Input Frequency: 47-63Hz
Inrush Current: Typ. 25-30A @ 230Vac.
Input Current: 0.34A/115Vac & 0.17A/230Vac.
Dielectric Withstand: Meet IEC 60950-1.
EMI: Meet CISPR PUB. 22 & FCC Class B.
Power Fail Signal: Installed.
Remote Inhibit: Available at single output only.
Hold-up Time: Typ. 10mS @115Vac/40-50mS @230Vac.
Earth leakage: Typ. 0.3-0.5A @230Vac.

OUTPUT SPECIFICATION

Output Voltage: See Ratings Chart.
Output Current: See Ratings Chart.
Output Wattage: Typ. 45-50 Watts.
Output Connector: DIN 41612 at rear.
Line Regulation: Typ. 0.1%.
Load Regulation: Main VO1 typ. $\pm 1.0\%$.
 Aux. VO2 typ. $\pm 2-3.0\%$ (P.R.).
 Aux. VO3 typ. $\pm 2-3.0\%$ (P.R.).
Noise & Ripple: Typ. 1% peak to peak.
OVP: Built-in at main VO1 (latch).
Adjustability: Available at main output VO1.
Remote Sense: Installed at main VO1.
Overload Protection (OLP):
 Fully protected against output overload and short circuit.
 Consult the factory for OLP setting.

GENERAL SPECIFICATION

Efficiency: Typ. 60-70%. Switching Frequency: 45K Hz. Circuit Topology: Fixed frequency flyback circuit. Transient Response: Output voltage returns in less than 3mS following a 25% load change. Safety Standard: IEC 60950-1/UL 60950-1 Class I.	Operating Temperature: 0 to +50°C. Storage Temperature: -20 to +85°C. Temperature Coefficient: Typ. 0.04% /°C. Cooling: Free air convection cooling. Construction: 6HP(TE) x 3U 19" compatible Eurocard VMEbus standard. Power Density: 1.4Watts / Cubic Inch.
--	---

Note: Due to requests in market and advances in technology, specifications subject to change without notification.



In application

OUTPUT VOLTAGE / CURRENT RATINGS CHART

SINGLE OUTPUT

MODEL NO	MAIN VO1 ★@# Typ. Volt.
HIU45-S025160	16.0A 2.5V
HIU45-S030140	14.0A 3.0V
HIU45-S050090	9.0A 5.0V
HIU45-S120040	4.0A 12.0V
HIU45-S150032	3.2A 15.0V
HIU45-S240020	2.0A 24.0V
HIU45-S480010	1.0A 48.0V

DUAL OUTPUT

MODEL NO	MAIN VO1 ★@# Typ. Volt.	AUX. VO2 ◇• Typ. Volt.
HIU45-D030E	8.0A 3.0V	2.0A 5.0V
HIU45-D030I	7.0A 3.0V	2.0A 12.0V
HIU45-D050D	6.0A 5.0V	2.0A 3.0V
HIU45-D050I	4.0A 5.0V	2.0A 12.0V
HIU45-D050K	4.0A 5.0V	2.0A 15.0V
HIU45-D050M	4.0A 5.0V	1.0A 24.0V


TRIPLE OUTPUT

MODEL NO	MAIN VO1 ★@ Typ. Volt.	AUX. VO2 ◇• Typ. Volt.	AUX. VO3 ◇ • Typ. Volt.
HIU45-T030EE	5.0A 3.0V	3.0A 5.0V	1.0A 5.0V
HIU45-T030II	5.0A 3.0V	2.0A 12.0V	0.5A 12.0V
HIU45-T030KK	5.0A 3.0V	1.5A 15.0V	0.5A 15.0V
HIU45-T050DE	5.0A 5.0V	2.0A 3.0V	1.0A 5.0V
HIU45-T050DI	5.0A 5.0V	2.0A 3.0V	1.0A 12.0V
HIU45-T050II	4.0A 5.0V	1.5A 12.0V	1.0A 12.0V
HIU45-T050KK	4.0A 5.0V	1.2A 15.0V	0.8A 15.0V

Symbol: "★" OVP built-in. "◇" Floating(or isolated) output. "# " Remote sensing.
 "@ " Adjustable. "•" Installed with Post Regulator (PR).

MECHANICAL DIMENSIONS: MM [INCHES]

WEIGHT: 593.0g (20.92 Oz.)



INPUT & OUTPUT CONNECTORS PIN ASSIGNMENT

ASSIGNMENT	AC INPUT			SINGLE /DUAL/TRIPLE OUTPUT						ASSORTED SIGNAL			
	AC-L	AC-N	AC-G	+VO1	-VO1	+VO2	-VO2	+VO3	-VO3	S+	S-	P.F.	LOGIC INHIBIT
HIU45-1X	28	30	32	4,6	12,14	-	-	-	-	8	10	22	20
HIU45-2X	28	30	32	4	6	8	10	-	-	-	-	22	20
HIU45-3X	28	30	32	4,6	8,10	12	14	16	18	-	-	22	20

Mating connector: DIN41612-H15 Female.