



PRODUCTS

INDUSTRY SOLUTIONS

CAREERS

RESOURCES

CONTACT MOLEX

FIND DISTRIBUTOR

Home: Crimp Terminals &gt;

**Part Number: 50896-7525**

Wire Pin Terminal, Type A, for 2 AWG Wire

Image not available

Status:	Obsolete
Replacement:	Contact Molex
Series:	<a href="#">50896</a>
Category:	Crimp Terminals
Overview:	<a href="#">Wire Pins</a>

CHECK DISTRIBUTOR INVENTORY

- [Add to My Parts](#)
- [Email this page](#)

Go to [Part Detail](#) ▾

Series image - Reference only

**Use With Part(s):**

Terminal Block

**Application Tooling****FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Japan**

Description	Product #
Battery Type Hand Crimper For JIS Terminal	<a href="#">57343-9004</a>

**Crimp Quality Equipment**[Molex also offers wire strippers, pull testers, shut-height gauges, micrometers and more](#)**Previously Available Application Tooling**[Check our list of old tooling that used to be available for this part](#)**Product Environmental Compliance**[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, &amp; Low-Halogen

Multiple Part Industry Compliance Documents

\*IPC 1752A Class C

\*IPC 1752A Class D

\*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? Email [ProductCompliance@molex.com](mailto:ProductCompliance@molex.com)Request Molex's CMRT from [conflictminerals@molex.com](mailto:conflictminerals@molex.com)**Part Detail****COLLAPSE ALL****▼ General**

Status	Obsolete
Category	Crimp Terminals
Series	<a href="#">50896</a>
Application	Power
Overview	<a href="#">Wire Pins</a>
Product Name	Wire Pin
UPC	800753237056

**▼ Physical**

Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Packaging Type	Bag
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	9.40mm max.
Wire Size AWG	2
Wire Size mm <sup>2</sup>	26.66-42.42

**▼ Agency Certification**

Please find UL Certificates by searching the UL Database using the Molex Series Number.

[Click here to visit the UL Database](#)

UL E134962

**PRODUCTS****QUICK LINKS****RESOURCES****STAY CONNECTED**

Antennas

Company Information

Supply Chain Transparency



Application Tooling

Contact Molex

Business Continuity



Cable Assemblies

Cross-Reference

Compliance



Connected Lighting

Koch Industries

ecocare

Connectors

Industries

Feedback | Help

Copper Flex

Investor Relations

Jobs

Electrical Products

Literature

Legal | Trademarks

Industrial Automation

Molex Racing

Mobile Site

Membrane Switches

Press Room / Press Releases

Supplier Portal

Optical Solutions

Product Index

Privacy Policy

Printed Electronic Solutions

Sitemap

Tradeshows

