

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) [Search Tips](#)

☒ Text Search: 'F9D6J-4M3Y'

Your search criteria matched only one product, shown below

F9D6J-4M3Y



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR-326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

▪ Part Number	F9D6J-4M3Y
▪ RoHS Compliancy Status	Compliant
▪ Note	F9D6J-4M3Y replaces F9D6J-4M3
▪ Part Description	FJ® Jack Module to FC singlemode duplex patch cord (one FJ® Jack Module on one end and two FC connectors on the other end) - 9/125µm.
▪ Product Type	FJ® Hybrid Patch Cords
▪ Length (m)	3
▪ Fiber Compatibility	9/125µm
▪ Fiber Cable Size	3mm
▪ Fiber Cable Type	Jacketed
▪ Fiber Type	Singlemode
▪ Cable Color	Yellow
▪ Cable Type	Duplex
▪ CE Compliant	No
▪ Connector 1 Type	FJ® Jack Module
▪ Connector 2 Type	FC Connector
▪ End Configurations	FJ® Jack to FC
▪ Fiber Count	2
▪ Flammability Rating	Riser (OFNR)
▪ Pricing Description	PC FJ Jack To FC 9µm Dupl 3m
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="button" value=""/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.