



20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

NOTES:


- 1) MATERIALS: HOUSING PARTS ARE MADE OF POLYESTER, RATED UL, 94 V-0, COLOR IS BLACK; TERMINALS ARE .015/(0.38) THICK PHOSPHOR BRONZE.
- 2) TERMINAL PLATING OPTIONS PER ES-88-***:
A - SELECT GOLD IN CONTACT AREA: 50 MICROINCHES MIN.,
SELECT MATTE TIN IN PC TAIL AREA: 100 MICROINCHES MIN.,
WITH OVERALL NICKEL UNDERPLATE: 50 MICROINCHES MIN.
- 3) THESE MODULAR JACKS MEET THE PERFORMANCE REQUIREMENTS OF MOLEX PRODUCT SPECIFICATION PS-42410.
- 4) CONNECTORS ARE TO BE PACKED IN THERMOFORMED TRAYS, PER PACKAGING SPECIFICATION PK-42410-492.
- 5) ALL JACKS ARE DESIGNED TO BE USED WITH .062/(1.57) OR .125/(3.18) THICK P.C. BOARDS.
- 6) ALL JACKS CONFORM TO AND ACCEPT PLUGS WHICH CONFORM TO FCC RULES AND REGULATIONS PART 68, SUBPART F, WHEN PLATED WITH 50 MICROINCHES GOLD.
- 7) ALL JACKS MUST BE CAPABLE OF FITTING INTO MOLEX GAGE G-42410 (CONNECTOR SIZE 4).
- 8) SEE SHEETS 2 & 4 FOR CONNECTOR SIZE 6.
- 9) SEE SHEETS 3 & 4 FOR CONNECTOR SIZE 8.
- 10) SEE SHEET 4 FOR ASSEMBLY ITEM NUMBERS.
- 11) THIS MODULAR JACK ASSEMBLY IS ALSO AVAILABLE IN A UL 94V-0 RATED, GLASS-FILLED NYLON. (SEE MOLEX DRAWING SDA-43576)
- 12) ENGRAVED NUMBERS ON HOUSING BODY ARE FOR MOLDING IDENTIFICATION ONLY. THEY ARE NOT INTENDED FOR ASSEMBLY IDENTIFICATION PURPOSES.
- 13) ALL UNTOLERANCED DIMENSIONS ARE SHOWN FOR REFERENCE ONLY.

P.C. BOARD THICKNESS	DIM. "D" (MTG. PEGS)	DIM. "F" (P.C. TAILS)
0.062"	.128 (3.25)	.120 +.015/- .025 (3.05 +.38/- .63)
0.125"	.191 (4.85)	.205 +.015/- .025 (5.21 +.38/- .63)

CONNECTOR SIZE	CIRCUIT SIZE	DIM. "G"
4	4	.150 (3.81)
4	2	.050 (1.27)





PANEL CUT-OUT FOR CONNECTOR SIZE 4



P.C. BOARD LAYOUT FOR CONNECTOR SIZE 4

MOUNTING EARS ARE OPTIONAL



SIZE 4 MODULAR JACK LOADED WITH 4 TERMINALS SHOWN ABOVE
(SEE SHEET 4 FOR PART NUMBER AVAILABILITY)



ADD. DIM	EC NO.: IJCT2011-3830	2011/06/06	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	TITLE	DOCUMENT NO.	SHEET NO.
	PRJ: JAGUILAR	2011/06/09			4:1	INCH						
	CHKD: BEUL	2012/02/14			IN/MM	INCH						
	APPROV: FSH1TH	2012/02/14			IN/MM	INCH						
1			▽=0	mm	INCH	DRAWN BY	DATE	ASSEMBLY, VERTICAL MODULAR JACKS (CONNECTOR SIZE 4)				
			▽=0	3 PLACES ± --- ± ---	GLT	1990/10/12	DATE					
			▽=0	3 PLACES ± --- ± .010	CHECKED BY	DATE						
			▽=0	2 PLACES ± .025 ± ---	BAP	1990/10/12	DATE					
			▽=0	1 PLACE ± --- ± ---	APPROVED BY	DATE						
				ANGULAR ±1/2°	FSH1TH	2012/02/14			MOLEX INCORPORATED			
					MATERIAL NO.		DOCUMENT NO.					
					SEE SHEET 4		SDA-42410-****					
					SIZE D		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							

NOTES:


- 1) MATERIALS: HOUSING PARTS ARE MADE OF POLYESTER, RATED UL 94 V-0. COLOR IS BLACK. TERMINALS ARE .015/(0.38) THICK PHOSPHOR BRONZE.
- 2) TERMINAL PLATING OPTIONS PER ES-88-****:
A - SELECT GOLD IN CONTACT AREA: 50 MICROINCHES MIN.
SELECT MATTE TIN IN PC TAIL AREA: 100 MICROINCHES MIN.
WITH OVERALL NICKEL UNDERPLATE: 50 MICROINCHES MIN.
- 3) THESE MODULAR JACKS MEET THE PERFORMANCE REQUIREMENTS OF MOLEX PRODUCT SPECIFICATION PS-42410.
- 4) CONNECTORS ARE TO BE PACKED IN THERMOFORMED TRAYS, PER PACKAGING SPECIFICATION PK-42410-492.
- 5) ALL JACKS ARE DESIGNED TO BE USED WITH .062/(1.57) OR .125/(3.18) THICK P.C. BOARDS.
- 6) ALL JACKS CONFORM TO AND ACCEPT PLUGS WHICH CONFORM TO FCC RULES AND REGULATIONS PART 68, SUBPART F, WHEN PLATED WITH 50 MICROINCHES GOLD.
- 7) ALL JACKS MUST BE CAPABLE OF FITTING INTO MOLEX GAGE G-42410 (CONNECTOR SIZE 4).
- 8) SEE SHEETS 1 & 4 FOR CONNECTOR SIZE 4.
- 9) SEE SHEETS 2 & 4 FOR CONNECTOR SIZE 6.
- 10) SEE SHEET 4 FOR ASSEMBLY ITEM NUMBERS.
- 11) THIS MODULAR JACK ASSEMBLY IS ALSO AVAILABLE IN A UL 94V-0 RATED, GLASS-FILLED NYLON. (SEE MOLEX DRAWING SDA-43576)
- 12) ENGRAVED NUMBERS ON HOUSING BODY ARE FOR MOLDING IDENTIFICATION ONLY. THEY ARE NOT INTENDED FOR ASSEMBLY IDENTIFICATION PURPOSES.
- 13) ALL UNTOLERANCED DIMENSIONS ARE SHOWN FOR REFERENCE ONLY.

P.C. BOARD THICKNESS	DIM. "D" (MTG. PEGS)	DIM. "F" (P.C. TAILS)
.062/(1.57)	.128 (3.25)	.120 +.015/-.025 (3.05 +.38/-.63)
.125/(3.18)	.191 (4.85)	.205 +.015/-.025 (5.21 +.38/-.63)



CONNECTOR SIZE	CIRCUIT SIZE	DIM. "G"
8	8	.350 (8.89)
8	6	.250 (6.35)
8	4	.150 (3.81)
8	2	.050 (1.27)



PANEL CUT-OUT FOR CONNECTOR SIZE 8



P.C. BOARD LAYOUT FOR CONNECTOR SIZE 8



SIZE 8 MODULAR JACK LOADED WITH 8 TERMINALS SHOWN ABOVE

(SEE SHEET 4 FOR PART NUMBER AVAILABILITY)

SEE SHEET 1 EC NO. UJ2211-3830 DRAWN: JADILUR CHECKED: JADILUR APPROVED: JADILUR	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
		mm	INCH	IN/MM		4:1	INCH	
	▽=0	4 PLACES ± ---	± ---	DRAWN BY	DATE	TITLE	ASSEMBLY, VERTICAL MODULAR JACKS (CONNECTOR SIZE 4)	
	▽=0	3 PLACES ± ---	± .010	CHECKED BY	DATE			
	▽=0	2 PLACES ± 0.25	± ---	BAP	DATE			
▽=0	1 PLACE ± ---	± ---	APPROVED BY	DATE				
		ANGULAR ±1/2°		FSMITH	2012/02/14	MOLLEX	MOLEX INCORPORATED	
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.
				SEE SHEET 4		SDA-42410-****		3 OF 4
				SIZE D THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

		20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
SIZE 4 VERTICAL MODJACK ASSEMBLIES																					
		PART CHARACTERISTICS																			
Y-NOT TOOLED	ASSEMBLY ITEM NUMBER	EXTERNAL CONNECTOR SIZE	NUMBER OF POSITIONS	P.C. BOARD THICKNESS	MOUNTING EARS OPTION	TERMINAL PLATING OPTION															
	42410-4168	4 POS. BODY	4	.062/(1.57)	YES	A															
	42410-4170	↑	↑	.062/(1.57)	NO	A															
	42410-4264	↓	↓	.125/(3.18)	YES	A															
	42410-4266	4 POS. BODY	4	.125/(3.18)	NO	A															
	42410-4312	4 POS. BODY	2	.062/(1.57)	YES	A															
	42410-4314	↑	↑	.062/(1.57)	NO	A															
	42410-4408	↓	↓	.125/(3.18)	YES	A															
	42410-4410	4 POS. BODY	2	.125/(3.18)	NO	A															
SIZE 6 VERTICAL MODJACK ASSEMBLIES																					
		PART CHARACTERISTICS																			
Y-NOT TOOLED	ASSEMBLY ITEM NUMBER	EXTERNAL CONNECTOR SIZE	NUMBER OF POSITIONS	P.C. BOARD THICKNESS	MOUNTING EARS OPTION	TERMINAL PLATING OPTION															
	42410-6168	6 POS. BODY	6	.062/(1.57)	YES	A															
	42410-6170	↑	↑	.062/(1.57)	NO	A															
	42410-6264	↓	↓	.125/(3.18)	YES	A															
	42410-6266	6 POS. BODY	6	.125/(3.18)	NO	A															
	42410-6312	6 POS. BODY	4	.062/(1.57)	YES	A															
	42410-6314	↑	↑	.062/(1.57)	NO	A															
	42410-6320	↓	↓	.062/(1.57)	YES	B															
	42410-6408	↓	↓	.125/(3.18)	YES	A															
	42410-6410	6 POS. BODY	4	.125/(3.18)	NO	A															
	42410-6456	6 POS. BODY	2	.062/(1.57)	YES	A															
	42410-6458	↑	↑	.062/(1.57)	NO	A															
	42410-6552	↓	↓	.125/(3.18)	YES	A															
	42410-6554	6 POS. BODY	2	.125/(3.18)	NO	A															
SIZE 8 VERTICAL MODJACK ASSEMBLIES																					
		PART CHARACTERISTICS																			
Y-NOT TOOLED	ASSEMBLY ITEM NUMBER	EXTERNAL CONNECTOR SIZE	NUMBER OF POSITIONS	P.C. BOARD THICKNESS	KEYING OPTION	MOUNTING EARS OPTION	TERMINAL PLATING OPTION														
	42410-8312	8 POS. BODY	8	.062/(1.57)	NO	YES	A														
	42410-8314	↑	↑	.062/(1.57)	NO	NO	A														
	42410-8360	↑	↑	.062/(1.57)	YES	YES	A														
	42410-8362			.062/(1.57)	YES	NO	A														
	42410-8504			.125/(3.18)	NO	YES	A														
	42410-8506			.125/(3.18)	NO	NO	A														
	42410-8552	↓	↓	.125/(3.18)	YES	YES	A														
	42410-8554	8 POS. BODY	8	.125/(3.18)	YES	NO	A														
	42410-8600	8 POS. BODY	6	.062/(1.57)	NO	YES	A														
	42410-8602	↑	↑	.062/(1.57)	NO	NO	A														
	42410-8648			.062/(1.57)	YES	YES	A														
	42410-8650			.062/(1.57)	YES	NO	A														
	42410-8792			.125/(3.18)	NO	YES	A														
	42410-8794			.125/(3.18)	NO	NO	A														
	42410-8840	↓	↓	.125/(3.18)	YES	YES	A														
	42410-8842	8 POS. BODY	6	.125/(3.18)	YES	NO	A														
	42410-8888	8 POS. BODY	4	.062/(1.57)	NO	YES	A														
	42410-8890	↑	↑	.062/(1.57)	NO	NO	A														
	42410-8936			.062/(1.57)	YES	YES	A														
	42410-8938	↑	↑	.062/(1.57)	YES	NO	A														
	42410-9080			.125/(3.18)	NO	YES	A														
	42410-9082			.125/(3.18)	NO	NO	A														
	42410-9128	↓	↓	.125/(3.18)	YES	YES	A														
	42410-9130	8 POS. BODY	4	.125/(3.18)	YES	NO	A														
	42410-9176	8 POS. BODY	2	.062/(1.57)	NO	YES	A														
	42410-9178	↑	↑	.062/(1.57)	NO	NO	A														
	42410-9224			.062/(1.57)	YES	YES	A														
	42410-9226			.062/(1.57)	YES	NO	A														
	42410-9368			.125/(3.18)	NO	YES	A														
	42410-9370			.125/(3.18)	NO	NO	A														
	42410-9416	↓	↓	.125/(3.18)	YES	YES	A														
	42410-9418	8 POS. BODY	2	.125/(3.18)	YES	NO	A														
SEE SHEET 1 SEC NO: UCP2011-3830 DRAWN: JAGUILAR 2011/06/09 CHKD: BELL 2011/06/09 APPR: F SMITH 2012/02/14																					
		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION									
		▽=0		mm INCH		DRAWN BY DATE		1:1 INCH													
		▽=0		4 PLACES ± --- ± ---		GLT 1990/10/12															
		▽=0		3 PLACES ± --- ± .010		CHECKED BY DATE															
		▽=0		2 PLACES ± 0.25 ± ---		BAP 1990/10/12															
				1 PLACE ± --- ± ---		APPROVED BY DATE															
				ANGULAR ±1/2°		FSMITH 2012/02/14															
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		SEE CHART		DOCUMENT NO.											
						SIZE D		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SDA-42410-****		SHEET NO. 4 OF 4									

SEE SHEET 1
EC NO. UCP2011-3830
DRAWN: JAGUILAR
CHKD: J.BELL
APPR: F.S.M.T.H.
REV
N1

2011/06/06
2011/06/09
2012/02/14

QUALITY SYMBOLS
▽=0
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± .010
2 PLACES ± 0.25 ± ---
1 PLACE ± --- ± ---
ANGULAR ±1/2°

DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY DATE
GLT 1990/10/12

CHECKED BY DATE
BAP 1990/10/12

APPROVED BY DATE
FSMITH 2012/02/14

MATERIAL NO.
SEE CHART

DOCUMENT NO.
SDA-42410-****

SHEET NO.
4 OF 4

SCALE
1:1

DESIGN UNITS
INCH

THIRD ANGLE PROJECTION

ASSEMBLY: VERTICAL
MODULAR JACKS
(CONNECTOR SIZE 4)

MOLEX INCORPORATED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION