





MARKETING SALES DRAWING

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



MOUNTING HARDWARE



Notes:

1. Operating temperature range : -55°C to +125°C.
2. Silver plated case, lead and mounting hardware.
3. Max.recommended mounting torque : 2.0 lb. - in.
4. Max. recommended soldering temperature : 260°C.
See installation recommendations.
5. Nut and lock washer included.
6. Tusonix Standard part number: 4400-035.
Tusonix RoHS compliant part number: 4400-035 LF.
Customer must specify Standard or RoHS part number when ordering.
7. Part Marking: Trademark and variation stamped on hex flats:
Standard Part, Black Ink. RoHS compliant part, green ink for identification.

CAP.(pf)		TOLERANCE	DC WORKING VOLTAGE		I.R. MIN. @ 100 (VDC.)	DWV (VDC)	DC CURRENT (AMPS)	MIN. NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220				
			85°C	125°C				1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
10,000		GMV	70	50	10 G Ω	150	10	4	21	35	50	60

REVISION RECORD Original Release C.O. 20011102-1-02 VARS 035,036,037 & 1MHz COLUMN ADDED. L.E. 11-07-90 5591 RDN TO COMP FMT & ADDED METRIC. S.M. 11-08-01 20011102-1-02 REVISED DWG. DRAWING MADE FOR EACH VAR. S.M. 11-19-02 20021113-1-06 REVISED AND ADDED NOTES. S.M. 11-04-05 20051102-1-02	0		1		2		3		4			--TOLERANCES-- Unless Otherwise Specified		Title BUSHING STYLE EMI FILTER			
	DECIMAL ±		NOTED														
	ANGLES ±				Drawn		S.M. 11-08-01		Scale			5 X					
	TUSONIX		TUCSON, ARIZONA		Approved				B.Mc. 11-08-01								
	A		4400-035														