

Features



1 or 2 Pole 16 A Step relays for direct 35 mm rail (EN 60715) mounting

- 17.4 mm wide
- Test button with mechanical indicators
- Choice of 6 switching sequences
- AC coils and DC coils
- Identification label
- Possible to connect illuminated push buttons with the additional part 026.00
- 35 mm rail (EN 60715) mount
- Cadmium free contact material

20.21





- Single phase switch 1 NO (SPST-NO)
- 35 mm rail (EN 60715) mount



20.22, 24, 26, 28





- Double phase switch
- 35 mm rail (EN 60715) mount



20.23



- Double phase switch 1NO+1NC (SPST-NO+SPST-NC)
- 35 mm rail (EN 60715) mount



FOR UL HORSEPOWER AND PILOT DUTY RATINGS
SEE "General technical information" page V

Contact specification				
Contact configuration		1 NO (SPST-NO)	2 NO (DPST-NO)	1NO+1NC (SPST-NO+SPST-NC)
Rated current/Maximum peak current		A	16/30	16/30
Rated voltage/Maximum switching voltage V AC			250/400	250/400
Rated load AC1		VA	4,000	4,000
Rated load AC15 (230 V AC)		VA	750	750
Nominal lamp rating:incandescent (230 V)		W	2,000	2,000
compensated fluorescent (230 V)		W	750	750
uncompensated fluorescent (230 V)		W	1,000	1,000
halogen (230 V)		W	2,000	2,000
Minimum switching load		mW (V/mA)	1,000 (10/10)	1,000 (10/10)
Standard contact material			AgNi	AgNi
Coil specification				
Nominal voltage (U _N)	V AC (50/60 Hz)	8 - 12 - 24 - 48 - 110 - 120 - 230 - 240		
	V DC	12 - 24 - 48 - 110	12 - 24 - 48 - 110	12 - 24 - 48 - 110
Rated power AC/DC		VA (50 Hz)/W	6.5/5	6.5/5
Operating range		AC	(0.85...1.1)U _N (50 Hz)/(0.9...1.1)U _N (60 Hz)	
		DC	(0.9...1.1)U _N	(0.9...1.1)U _N
Technical data				
Mechanical life AC/DC		cycles	300 · 10 ³	300 · 10 ³
Electrical life at rated load in AC1		cycles	100 · 10 ³	100 · 10 ³
Minimum/Maximum impulse duration			0.1s/1h (according to EN 60669)	0.1s/1h (according to EN 60669)
Insulation between coil and contacts (1.2/50 µs)		kV	4	4
Ambient temperature range		°C	-40...+40	-40...+40
Protection category			IP 20	IP 20
Approvals (according to type)				

Ordering information

Example: 20 series relay, 35 mm rail (EN 60715) mount, double phase switch, 2 NO (DPST-NO) 16 A contacts, coil rated at 12 V DC, AgSnO₂ contacts.

2 0 . 2 2 . 9 . 0 1 2 . 4 0 0 0

Series _____
Type _____
 2 = 35 mm rail (EN 60715) mount
No. of poles _____
 1 = Single phase switch 1 NO (SPST-NO)
 2 = Double phase switch 2 NO (DPST-NO)
 3 = Double phase switch 1 NC+1 NO (SPST-NO+SPST-NC)
 4 = 4 sequence double phase switch 2 NO (DPST-NO)
 6 = 3 sequence double phase switch 2 NO (DPST-NO)
 8 = 4 sequence double phase switch 2 NO (DPST-NO)

Contact material
 0 = AgNi standard
 4 = AgSnO₂
Coil voltage
 See coil specifications
Coil version
 8 = AC (50/60 Hz)
 9 = DC

Technical data

Insulation

Dielectric strength		
between supply and contacts	V AC	3,500
between open contacts	V AC	2,000
between adjacent contacts	V AC	2,000

Other data

Power lost to the environment			
with rated current and coil deenergised	W	1.3 (20.21, 20.23, 20.28)	2.6 (20.22, 20.24, 20.26)
Screw torque	Nm	0.8	0.8
Max. wire size	Coil terminals		Contact terminals
	solid cable		solid cable
	stranded cable		stranded cable
	mm ²	1x4 / 2x2.5	1x6 / 2x4
	AWG	1x12 / 2x14	1x10 / 2x12

If the coil is operated for a prolonged period of time, adequate ventilation of the relays must be provided - suggested gap of 9 mm between adjacent relays.

Coil specifications

DC version data


Nominal voltage U _N	Coil code	Operating range		Resistance R	Consumption I at U _N
V		U _{min} V	U _{max} V	Ω	mA
12	9.012	10.8	13.2	27	440
24	9.024	21.6	26.4	105	230
48	9.048	43.2	52.8	440	110
110	9.110	99	121	2,330	47

AC version data


Nominal voltage U _N	Coil code	Operating range		Resistance R	Consumption I at U _N (50 Hz)
V		U _{min} V	U _{max} V	Ω	mA
8	8.008	6.8	8.8	4	800
12	8.012	10.2	13.2	7.5	550
24	8.024	20.4	26.4	27	275
48	8.048	40.8	52.8	106	150
110	8.110	93.5	121	590	64
120	8.120	102	132	680	54
230	8.230	196	253	2,500	28
240	8.240	204	264	2,700	27.5

Type	Number of steps	Sequence			
		1	2	3	4
20.21	2				
20.22	2				
20.23	2				
20.24	4				
20.26	3				
20.28	4				

Wiring diagrams




Example: 230 V AC supply voltage.



Example: 24 V AC supply voltage.


Accessories

Module for use with illuminated push-buttons



Type 026.00

Sealed construction, 7.5 cm insulated flexible wire termination.



Example of wiring diagram of type 026.00

This module is necessary when using between 1 and a maximum of 15 illuminated push buttons in the coil circuit (Each 1.5 mA max, 230 V AC). It must be connected in parallel to the coil of the relay.



020.01

Adaptor for panel mounting, 17.5 mm wide

020.01



020.24

Sheet of marker tags, plastic, 24 tags, 9x17 mm

020.24

