





NOTES:

1. MATERIALS AND FINISHES(PLATING THICKNESS IN MICRO-INCHES):
BODY – BRASS, NICKEL PLATING
CONTACT – BRASS, GOLD PLATING
INSULATOR – PTFE, NATURAL
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC 0–4 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: –65°C to +165°C
4. SOLDER CONTACT TO CABLE.
WHEN CRIMPING CONTACT PIN TO CABLE, CRIMP WITH AMPHENOL TOOL 227–944 (M22520/5–01) AND DIE SET 227–980–1, CAVITY 'B' (OR CTL–6, .052 DIAMOND; OR CTL–8, .052 DIAMOND)
5. WHEN CRIMPING FERRULE TO CABLE, CRIMP WITH AMPHENOL TOOL 227–944 (M22520/5–01) AND DIE SET 227–980–1, CAVITY 'A' (OR CTL–6 , .255 HEX; OR CTL–8 , .255 HEX)
6. USE WITH CABLE: BELDEN 1505A, 1426A, 9659, 9259, 9240, 8212, 9274, 9275, 9100 AND CLARK CV7559

THIRD ANGLE PROJ.

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
B	ROLLING WAS STAKE\RD–DA05091401J	14–Sep–05	--	SH
B1	ADDED A SLOT	17–Jan–06	--	SH
C	SEE SHEET 1	27–Feb–08	--	AW
D	SEE SHEET 1	17–Mar–10	47967	SH
E	NOTE 4 WAS CHANGED\RD–10121301F	27–Dec–10	48342	SH



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
<0.5mm 0.5 – 6mm 6 – 30mm 30 – 120mm ANGLES ARE:
±0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1°

NOTICE – These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL

REFERENCE

FINISH

DRAWN
F.WANG

ENGINEER
S.LI

APPROVED
S.HSIEH

CAD FILE
F:\DWG\CNPD\31\70008\3000–ESZ

DATE

27–Dec–10

DATE

27–Dec–10

DATE

27–Dec–10

TITLE

BNC PLUG (75 OHM)
FOR RG59 TYPE CABLE
(.032 CENTER CONDUCTOR)

SCALE: 3/1

DWG SIZE
B

SHEET

2 OF 2

CODE ID
74868

REV
E

Amphenol RF

Danbury CT USA, Tainan Taiwan, Shenzhen China
www.amphenolrf.com

DRAWING NO. 31–70008–3000

ITEM NO. 31–70008–3000

PART NO. 31–70008–3000