


TYPE DIM.	POS. 4	POS. 6		POS. 8		
	4 CKTS.	4 CKTS.	6 CKTS.	4 CKTS.	6 CKTS.	8 CKTS.
A	(11.18) / .440	(13.21) / .520	(13.21) / .520	(15.24) / .600	(15.24) / .600	(15.24) / .600
C $(\pm 0.05) / \pm .002$	(7.62) / .300	(10.16) / .400	(10.16) / .400	(11.43) / .450	(11.43) / .450	(11.43) / .450
B $(\pm 0.05) / \pm .002$	(3.81) / .150	(3.81) / .150	(6.35) / .250	(3.81) / .150	(6.35) / .250	(8.89) / .350


P.C.B. MOUNTING PATTERNS - SEE FROM COMPONENT SIDE

FOR SMT JACK TYPE (SURFACE MOUNT)



FOR ALL VERSIONS, CIRCUIT 1 ALWAYS ON THE LEFT SIDE

FOR STANDARD JACK TYPE (THROUGH HOLE)



NOTE:

FOR CONVECTION SOLDERING: DIA 3.25 $\pm$ 0.05 / .128 $\pm$.002
FOR WAVE SOLDERING: DIA 3.20 $\pm$ 0.10 / .126 $\pm$.004

EC NO: MG2005-0106 2004/10/12 DRWN:TMARTIN CHKD:FCARABET 2004/10/12 APPR:KNOLLER 2004/10/13	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
			4 PLACES 3 PLACES 2 PLACES 1 PLACE	± ---	± ---	DRAWN BY FB 2004/09/25	DATE 2004/09/25	TITLE R/A LOW PROFILE JACK PC JACK 4,6,8 CKT SIZE SMT AND STANDARD VERSION		
				± ---	± .006				CHECKED BY DATE	
				± 0.15	± .010					
				± 0.25	± ---					
REV	DESCRIPTION	QUALITY SYMBOLS	ANGULAR ± ---°			APPROVED BY DATE		MOLEX MOLEX INCORPORATED	SHEET NO. 3 OF 9	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART SHEETS 4,5&6				DOCUMENT NO. SDA-95001
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

STANDARD PACKAGING OPEN TRAY ,SEE PACKAGING SPEC PK95001 SHEET 1

PART NO FOR JACK ASSEMBLY

STANDARD VERSION

HOUSING SIZE	LOADED CONTACTS	PLATING	POLYESTER FIBER GLASS FILED 94V0,COLOR BLACK.							
			NO KEY	TOOLED	KEY	TOOLED		TOOLED		TOOLED
			NOT RIBBED		NOT RIBBED					
4	4	2	9500I-244I	X	9500I-2442					
6	4	2	9500I-264I	X	9500I-2642					
6	6	2	9500I-266I	X	9500I-2662					
8	4	2	9500I-284I		9500I-2842					
8	6	2	9500I-286I	X	9500I-2862					
8	8	2	9500I-288I	X	9500I-2882	X				

SPECIAL VERSION HIGH TEMPERATURE

POLYAMIDE FIBER GLASS FILLED
COLOR BLACK

NO KEY	TOOLED	KEY	TOOLED
NOT RIBBED		NOT RIBBED	
9500I-844I	X		
9500I-864I	X		
9500I-866I	X		
9500I-888I	X		

EC NO: MG2005-0106 DRWN:TMARTIN 2004/10/12 CHKD:FCARABET 2004/10/12 APPR:KNOLLER 2004/10/13	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY DP	DATE 1989/06/01	TITLE LOW PROFILE R/A JACK STANDARD AND SMT VERSION STABDARD OPEN TRAY VERS			
		4 PLACES	±---	±---	CHECKED BY FB	DATE 1989/06/01				
		3 PLACES	±---	±---	APPROVED BY JB	DATE 1989/06/01	MOLEX INCORPORATED DOCUMENT NO. SDA-95001			
2 PLACES	±---	±---	MATERIAL NO.		SHEET NO. 4 OF 9					
1 PLACE	±---	±---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						SEE CHART	
		ANGULAR ±---°								