

You are here: eServices & Applied Computing > Display Solutions > ES-1000 LCD Kits > ES-1117N-LEAE

ES-1117N-LEAE

Print page | Email page

17" Color TFT LCD kits for LVDS interface



- RoHS
- ### MainFeatures
- LCD Panel: AUO M170EG01 V8
 - Display: 1280 x 1024 SXGA, 16.2M colors
 - Viewing Angle (L/R/U/D): 70/70/70/60
 - Brightness (nit): 300
 - Response Time (ms): 8
 - Backlight (hrs.): CCFL, 2-tubes, 50,000 hrs
 - Operation Temp.: 0 ~ 50 °C
 - ES-1117N-LEA-03E LCD Kit Cable Length (mm): 500 (optional)
 - Outline Dimensions mm (W x H x D): 358.5 x 296.5 x 17

Introduction

LCD kits (ES-1000 series) provide the most cost effective display solutions with proven features and seamless compatibility with all Advantech SBC boards. They are guaranteed to ease compatibility issues and come with cables, inverters and the assurance of long-term industrial component support.

Ordering Information

Part Number	Description
ES-1117N-LEA-03E	RoHS 17" LCD kit, AUO 260 nites, LVDS-3, SXGA
ES-1117N-LEAE	RoHS 17" LCD kit, AUO 260 nites, LVDS, SXGA

Contact Information

Office	Tel	Email
Advantech North & South America	1-888-576-9668	ePinfo@advantech.com
Advantech Europe Customer Care Center	00 800 24 26 80 80	customercare@advantech.eu
Advantech Headquarters	886-2-2792-7818	MKT.eVideo@advantech.com.tw

Rate this page :

Did the information help you achieve your goal?

☐ Yes ☐ No

Your eMail address:

Your Country:

Afghanistan

Please provide us with comments to help improve this page:

Submit

Find Resources

■ Datasheet (PDF)

■ Downloads

■ Online Catalog

■ Newsletter Subscribe

Services

■ Buy Online

Feature Articles

■ Industrial Computer

Tools

Add to Del.icio.us

DIGG this!

Google bookmark

Yahoo! My Web

Technorati