

Description

The Bay Linear LM78MXX is integrated linear positive regulator with three terminals. The LM78MXX offer several fixed output voltages making them useful in wide range of applications. When used as a zener diode/resistor combination replacement, the LM78MXX usually results in an effective output impedance improvement of two orders of magnitude, lower quiescent current.

The LM78MXX is available in the TO-220, TO-263 & TO-252 packages,

Features

- **Output Current of 500mA**
- **Internal thermal overload protection**
- **Internal Short-Circuit Limited**
- **No External Component**
- **Output Voltage 5.0V, 6V, 8V, 9V, 10V, 12V, 15V**
- **Offer in plastic TO-220 & TO-252**
- **Direct Replacement for LM78MXX**


Applications

- **Post regulator for switching DC/DC converter**
- **Bias supply for analog circuits**

Packaging Information



TO-263-3 (S)



Top View

1. Input
2. GND
3. Output

Ordering Information

Device	Operating Voltage	Temp.
LM78M05	7 to 20	0 to 125 °C
LM78M06	8 to 20	0 to 125 °C
LM78M08	10.5 to 23	0 to 125 °C
LM78M09	11.5 to 24	0 to 125 °C
LM78M10	12.5 to 25	0 to 125 °C
LM78M12	14.5 to 27	0 to 125 °C
LM78M15	17.5 to 30	0 to 125 °C

TO-220 (T)
TO-252 (D)
TO-263 (S)

Absolute Maximum Rating

Parameter	LM78M--	Unit
Input Voltage	35	V
Operating Free-Air, Case, Virtual Junction Temp.	0 to 150	°C
Storage Temperature Range	-65 to 150	
Lead temperature 1.6 mm from case for sec.	260	

Electrical Characteristics (LM78M05)

(V_I=10V, I_O=350mA, 0°C ≤ T_J ≤ 125 °C, unless otherwise specified, C_{IN}=0.33μF, C_D=0.1μF)

Parameter	Symbol	Conditions	MIN	TYP	MAX	UNIT
Output Voltage	V _O	T _J = 25 °C	4.80	5.0	5.2	V
Line Regulation	ΔV _O	V _I = 7V to 25V T _J = 25 °C, I _O =200mA	-	-	100	mV
		V _I = 8V to 25V T _J = 25 °C, I _O =200mA	-	-	50	
Load Regulation	ΔV _O	I _O = 5mA to 500mA, 25 °C	-	-	100	mV
		I _O = 5mA to 200mA, 25 °C	-	-	50	
Ripple Rejection	RR	V _I = 8.0V to 18V, f=120Hz, I _O =300mA	62	-	-	dB
Output Noise Voltage	V _N	F= 10Hz to 100Hz T _J = 25 °C		45		μV/V _O
Dropout Voltage	V _D	T _J = 25 °C		2.0		V
Quiescent Current		T _J = 25 °C		4.0	6.0	mA
Quiescent Current Change	ΔI _Q	V _I = 8V to 25V, T _J = 25 °C, I _O =200mA			0.8	mA
		I _O = 5mA to 350mA, T _J = 25 °C			0.5	

Electrical Characteristics (LM78M06)

(V_I=11V, I_O=350mA, 0°C ≤ T_J ≤ 125 °C, unless otherwise specified, C_{IN}=0.33μF, C_D=0.1μF)

Parameter	Symbol	Conditions	MIN	TYP	MAX	UNIT
Output Voltage	V _O	T _J = 25 °C	5.75	6.0	6.25	V
Line Regulation	ΔV _O	V _I = 8V to 25V T _J = 25 °C, I _O =200mA	-	-	100	mV
		V _I = 9V to 25V T _J = 25 °C, I _O =200mA	-	-	50	
Load Regulation	ΔV _O	I _O = 5mA to 500mA, 25 °C	-	-	120	mV
		I _O = 5mA to 200mA, 25 °C	-	-	60	
Ripple Rejection	RR	V _I = 11.5V to 21.5V, f=120Hz, I _O =300mA	59	-	-	dB
Output Noise Voltage	V _N	F= 10Hz to 100Hz T _J = 25 °C		45		μV/V _O
Dropout Voltage	V _D	T _J = 25 °C		2.0		V
Quiescent Current		T _J = 25 °C		4.0	6.0	mA
Quiescent Current Change	ΔI _Q	V _I = 9V to 25V, T _J = 25 °C, I _O =200mA			0.8	mA
		I _O = 5mA to 350mA, T _J = 25 °C			0.5	

Electrical Characteristics (LM78M08)

($V_I=14V$, $I_O=350mA$, $0^{\circ}C \leq T_J \leq 125^{\circ}C$, unless otherwise specified, $C_{IN}=0.33\mu F$, $C_D=0.1\mu F$)

Parameter	Symbol	Conditions	MIN	TYP	MAX	UNIT
Output Voltage	V_O	$T_J = 25^{\circ}C$	7.7	8.0	8.30	V
Line Regulation	ΔV_O	$V_I = 10.5V$ to $25V$ $T_J = 25^{\circ}C$, $I_O=200mA$	-	-	100	mV
		$V_I = 11V$ to $25V$ $T_J = 25^{\circ}C$, $I_O=200mA$	-	-	50	
Load Regulation	ΔV_O	$I_O = 5mA$ to $500mA$, $25^{\circ}C$	-	-	160	mV
		$I_O = 5mA$ to $200mA$, $25^{\circ}C$	-	-	80	
Ripple Rejection	RR	$V_I = 9.0V$ to $19V$, $f=120Hz$, $I_O=300mA$	56	-	-	dB
Output Noise Voltage	V_N	$F=10Hz$ to $100Hz$ $T_J = 25^{\circ}C$		52		$\mu V/V_O$
Dropout Voltage	V_D	$T_J = 25^{\circ}C$		2.0		V
Quiescent Current		$T_J = 25^{\circ}C$		4.0	6.0	mA
Quiescent Current Change	ΔI_Q	$V_I = 10.5V$ to $25V$, $T_J = 25^{\circ}C$, $I_O=200mA$			0.8	mA
		$I_O = 5mA$ to $350mA$, $T_J = 25^{\circ}C$			0.5	

Electrical Characteristics (LM78M10)

($V_I=17V$, $I_O=350mA$, $0^{\circ}C \leq T_J \leq 125^{\circ}C$, unless otherwise specified, $C_{IN}=0.33\mu F$, $C_D=0.1\mu F$)

Parameter	Symbol	Conditions	MIN	TYP	MAX	UNIT
Output Voltage	V_O	$T_J = 25^{\circ}C$	9.6	10.0	10.40	V
Line Regulation	ΔV_O	$V_I = 12.5V$ to $25V$ $T_J = 25^{\circ}C$, $I_O=200mA$	-	-	100	mV
		$V_I = 13V$ to $25V$ $T_J = 25^{\circ}C$, $I_O=200mA$	-	-	50	
Load Regulation	ΔV_O	$I_O = 5mA$ to $500mA$, $25^{\circ}C$	-	-	200	mV
		$I_O = 5mA$ to $200mA$, $25^{\circ}C$	-	-	100	
Ripple Rejection	RR	$V_I = 9.0V$ to $19V$, $f=120Hz$, $I_O=300mA$	55	-	-	dB
Output Noise Voltage	V_N	$F=10Hz$ to $100Hz$ $T_J = 25^{\circ}C$		65		$\mu V/V_O$
Dropout Voltage	V_D	$T_J = 25^{\circ}C$		2.0		V
Quiescent Current		$T_J = 25^{\circ}C$		4.1	6.0	mA
Quiescent Current Change	ΔI_Q	$V_I = 10.5V$ to $25V$, $T_J = 25^{\circ}C$, $I_O=200mA$			0.8	mA
		$I_O = 5mA$ to $350mA$, $T_J = 25^{\circ}C$			0.5	

Electrical Characteristics (LM78M12)

($V_I=19V$, $I_O=350mA$, $0^{\circ}C \leq T_J \leq 125^{\circ}C$, unless otherwise specified, $C_{IN}=0.33\mu F$, $C_D=0.1\mu F$)

Parameter	Symbol	Conditions	MIN	TYP	MAX	UNIT
Output Voltage	V_O	$T_J = 25^{\circ}C$	11.5	12.0	12.5	V
Line Regulation	ΔV_O	$V_I = 14.5V \text{ to } 30V$ $T_J = 25^{\circ}C$, $I_O=200mA$	-	-	100	mV
		$V_I = 16V \text{ to } 30V$ $T_J = 25^{\circ}C$, $I_O=200mA$	-	-	50	
Load Regulation	ΔV_O	$I_O = 5mA \text{ to } 500mA$, $25^{\circ}C$	-	-	240	mV
		$I_O = 5mA \text{ to } 200mA$, $25^{\circ}C$	-	-	120	
Ripple Rejection	RR	$V_I = 15.0V \text{ to } 25V$, $f=120Hz$, $I_O=300mA$	55	-	-	dB
Output Noise Voltage	V_N	$F= 10Hz \text{ to } 100Hz$ $T_J = 25^{\circ}C$		75		$\mu V/V_O$
Dropout Voltage	V_D	$T_J = 25^{\circ}C$		2.0		V
Quiescent Current		$T_J = 25^{\circ}C$		4.1	6.0	mA
Quiescent Current Change	ΔI_Q	$V_I = 14.5V \text{ to } 30V$, $T_J = 25^{\circ}C$, $I_O=200mA$			0.8	mA
		$I_O = 5mA \text{ to } 350mA$, $T_J = 25^{\circ}C$			0.5	

Electrical Characteristics (LM78M15)

($V_I=19V$, $I_O=350mA$, $0^{\circ}C \leq T_J \leq 125^{\circ}C$, unless otherwise specified, $C_{IN}=0.33\mu F$, $C_D=0.1\mu F$)

Parameter	Symbol	Conditions	MIN	TYP	MAX	UNIT
Output Voltage	V_O	$T_J = 25^{\circ}C$	14.4	15	15.6	V
Line Regulation	ΔV_O	$V_I = 17.5V \text{ to } 30V$ $T_J = 25^{\circ}C$, $I_O=200mA$	-	-	100	mV
		$V_I = 20V \text{ to } 30V$ $T_J = 25^{\circ}C$, $I_O=200mA$	-	-	50	
Load Regulation	ΔV_O	$I_O = 5mA \text{ to } 500mA$, $25^{\circ}C$	-	-	300	mV
		$I_O = 5mA \text{ to } 200mA$, $25^{\circ}C$	-	-	150	
Ripple Rejection	RR	$V_I = 15.0V \text{ to } 25V$, $f=120Hz$, $I_O=300mA$	54	-	-	dB
Output Noise Voltage	V_N	$F= 10Hz \text{ to } 100Hz$ $T_J = 25^{\circ}C$		100		$\mu V/V_O$
Dropout Voltage	V_D	$T_J = 25^{\circ}C$		2.0		V
Quiescent Current		$T_J = 25^{\circ}C$		4.1	6.0	mA
Quiescent Current Change	ΔI_Q	$V_I = 17.5V \text{ to } 30V$, $T_J = 25^{\circ}C$, $I_O=200mA$			0.8	mA
		$I_O = 5mA \text{ to } 350mA$, $T_J = 25^{\circ}C$			0.5	

Electrical Characteristics (LM78M18)

($V_I=26V$, $I_O=350mA$, $0^\circ C \leq T_J \leq 125^\circ C$, unless otherwise specified, $C_{IN}=0.33\mu F$, $C_D=0.1\mu F$)

Parameter	Symbol	Conditions	MIN	TYP	MAX	UNIT
Output Voltage	V_O	$T_J = 25^\circ C$	17.3	18	18.7	V
Line Regulation	ΔV_O	$V_I = 21V \text{ to } 33V$ $T_J = 25^\circ C$, $I_O=200mA$	-	-	100	mV
		$V_I = 24V \text{ to } 33V$ $T_J = 25^\circ C$, $I_O=200mA$	-	-	50	
Load Regulation	ΔV_O	$I_O = 5mA \text{ to } 500mA$, $25^\circ C$	-	-	360	mV
		$I_O = 5mA \text{ to } 200mA$, $25^\circ C$	-	-	180	
Ripple Rejection	RR	$V_I = 18.5V \text{ to } 28.5V$, $f=120Hz$, $I_O=300mA$	53	-	-	dB
Output Noise Voltage	V_N	$F= 10Hz \text{ to } 100Hz$ $T_J = 25^\circ C$		100		$\mu V/V_O$
Dropout Voltage	V_D	$T_J = 25^\circ C$		2.0		V
Quiescent Current		$T_J = 25^\circ C$		4.2	6.0	mA
Quiescent Current Change	ΔI_Q	$V_I = 21V \text{ to } 33V$, $T_J = 25^\circ C$, $I_O=200mA$			0.8	mA
		$I_O = 5mA \text{ to } 350mA$, $T_J = 25^\circ C$			0.5	

Electrical Characteristics (LM78M20)

($V_I=29V$, $I_O=350mA$, $0^\circ C \leq T_J \leq 125^\circ C$, unless otherwise specified, $C_{IN}=0.33\mu F$, $C_D=0.1\mu F$)

Parameter	Symbol	Conditions	MIN	TYP	MAX	UNIT
Output Voltage	V_O	$T_J = 25^\circ C$	19.2	20	20.8	V
Line Regulation	ΔV_O	$V_I = 23V \text{ to } 33V$ $T_J = 25^\circ C$, $I_O=200mA$	-	-	100	mV
		$V_I = 24V \text{ to } 33V$ $T_J = 25^\circ C$, $I_O=200mA$	-	-	50	
Load Regulation	ΔV_O	$I_O = 5mA \text{ to } 500mA$, $25^\circ C$	-	-	400	mV
		$I_O = 5mA \text{ to } 200mA$, $25^\circ C$	-	-	200	
Ripple Rejection	RR	$V_I = 22V \text{ to } 32V$, $f=120Hz$, $I_O=300mA$	53	-	-	dB
Output Noise Voltage	V_N	$F= 10Hz \text{ to } 100Hz$ $T_J = 25^\circ C$		110		$\mu V/V_O$
Dropout Voltage	V_D	$T_J = 25^\circ C$		2.0		V
Quiescent Current		$T_J = 25^\circ C$		4.2	6.0	mA
Quiescent Current Change	ΔI_Q	$V_I = 23V \text{ to } 35V$, $T_J = 25^\circ C$, $I_O=200mA$			0.8	mA
		$I_O = 5mA \text{ to } 350mA$, $T_J = 25^\circ C$			0.5	

Electrical Characteristics (LM78M24)

($V_I=29V$, $I_O=350mA$, $0^{\circ}C \leq T_J \leq 125^{\circ}C$, unless otherwise specified, $C_{IN}=0.33\mu F$, $C_D=0.1\mu F$)

Parameter	Symbol	Conditions	MIN	TYP	MAX	UNIT
Output Voltage	V_O	$T_J = 25^{\circ}C$	23	24	25	V
Line Regulation	ΔV_O	$V_I = 27V \text{ to } 38V$ $T_J = 25^{\circ}C$, $I_O=200mA$	-	-	100	mV
		$V_I = 28V \text{ to } 38V$ $T_J = 25^{\circ}C$, $I_O=200mA$	-	-	50	
Load Regulation	ΔV_O	$I_O = 5mA \text{ to } 500mA$, $25^{\circ}C$	-	-	480	mV
		$I_O = 5mA \text{ to } 200mA$, $25^{\circ}C$	-	-	240	
Ripple Rejection	RR	$V_I = 22V \text{ to } 32V$, $f=120Hz$, $I_O=300mA$	50	-	-	dB
Output Noise Voltage	V_N	$F= 10Hz \text{ to } 100Hz$ $T_J = 25^{\circ}C$		170		$\mu V/V_O$
Dropout Voltage	V_D	$T_J = 25^{\circ}C$		2.0		V
Quiescent Current		$T_J = 25^{\circ}C$		4.2	6.0	mA
Quiescent Current Change	ΔI_Q	$V_I = 27V \text{ to } 38V$, $T_J = 25^{\circ}C$, $I_O=200mA$			0.8	mA
		$I_O = 5mA \text{ to } 350mA$, $T_J = 25^{\circ}C$			0.5	

Advance Information- These data sheets contain descriptions of products that are in development. The specifications are based on the engineering calculations, computer simulations and/ or initial prototype evaluation.

Preliminary Information- These data sheets contain minimum and maximum specifications that are based on the initial device characterizations. These limits are subject to change upon the completion of the full characterization over the specified temperature and supply voltage ranges.

The application circuit examples are only to explain the representative applications of the devices and are not intended to guarantee any circuit design or permit any industrial property right to other rights to execute. Bay Linear takes no responsibility for any problems related to any industrial property right resulting from the use of the contents shown in the data book. Typical parameters can and do vary in different applications. Customer's technical experts must validate all operating parameters including "Typical" for each customer application.

LIFE SUPPORT AND NUCLEAR POLICY

Bay Linear products are not authorized for and should not be used within life support systems which are intended for surgical implants into the body to support or sustain life, in aircraft, space equipment, submarine, or nuclear facility applications without the specific written consent of Bay Linear President.
