


Dual SCR POW-R-BLOK™ Modules 90 Amperes/1200-1600 Volts



Outline Drawing

Dimension	Inches	Millimeters
A	3.681 Max.	93.5 Max.
B	3.150	80
C	1.181 Max.	30 Max.
D	1.024 Max.	26 Max.
E	0.906	23
F	0.827	21
G	0.650	16.5
H	0.512	13
J	0.354	9
K	0.256	6.5
L	0.256 Dia.	Dia. 6.5
M	M5 Metric	M5



CM431290, CM431690
Dual SCR POW-R-BLOK™ Modules
90 Amperes/1200-1600 Volts

Description:

Powerex Dual SCR POW-R-BLOK™ Modules are designed for use in applications requiring phase control and isolated packaging. The modules are isolated for easy mounting with other components on common heatsinks.

Features:

- ☐ Isolated Mounting
- ☐ Glass Passivated Chips
- ☐ Metal Baseplate
- ☐ Low Thermal Impedance

Applications:

- ☐ Battery Supplies
- ☐ Bridge Circuits
- ☐ AC and DC Motor Control
- ☐ Tap Changers
- ☐ Lighting Control

Ordering Information:

Select the complete eight digit module part number you desire from the table below.

Example: CM431690 is a 1600 Volt, 90 Ampere Dual SCR POW-R-BLOK™ Module.

Type	Voltage Volts (x100)	Current Rating Amperes (90)
CM43	12 16	90



Powerex, Inc., 200 Hillis Street, Youngwood, Pennsylvania 15697-1800 (724) 925-7272

CM431290, CM431690
Dual SCR POW-R-BLOK™ Modules
90 Amperes/1200-1600 Volts

Absolute Maximum Ratings










Characteristics	Symbol	CM431290	CM431690	Units
Peak Forward Blocking Voltage	V_{DRM}	1200	1600	Volts
Transient Peak Forward Blocking Voltage (Non-Repetitive), $t < 5\text{ms}$	V_{DSM}	1350	1700	Volts
DC Forward Blocking Voltage	$V_{\text{D(DC)}}$	960	1280	Volts
Peak Reverse Blocking Voltage	V_{RRM}	1200	1600	Volts
Transient Peak Reverse Blocking Voltage (Non-Repetitive), $t < 5\text{ms}$	V_{RSM}	1350	1700	Volts
DC Reverse Blocking Voltage	$V_{\text{R(DC)}}$	960	1280	Volts
RMS On-State Current	$I_{\text{T(RMS)}}$	140	140	Amperes
Average On-State Current, $T_{\text{C}} = 82^{\circ}\text{C}$	$I_{\text{T(AV)}}$	90	90	Amperes
Peak One-Cycle Surge (Non-Repetitive) On-State Current (60Hz)	I_{TSM}	1800	1800	Amperes
Peak One-Cycle Surge (Non-Repetitive) On-State Current (50Hz)	I_{TSM}	1730	1730	Amperes
I^2t (for Fusing), 8.3 milliseconds	I^2t	15000	15000	A^2sec
Critical Rate-of-Rise of On-State Current*	di/dt	100	100	Amperes/ μs
Peak Gate Power Dissipation	P_{GM}	5.0	5.0	Watts
Average Gate Power Dissipation	$P_{\text{G(AV)}}$	0.5	0.5	Watts
Peak Forward Gate Voltage	V_{GFM}	10	10	Volts
Peak Reverse Gate Voltage	V_{GRM}	5.0	5.0	Volts
Peak Forward Gate Current	I_{GFM}	2.0	2.0	Amperes
Storage Temperature	T_{STG}	-40 to 125	-40 to 125	$^{\circ}\text{C}$
Operating Temperature	T_{j}	-40 to 125	-40 to 125	$^{\circ}\text{C}$
Maximum Mounting Torque M6 Mounting Screw	—	26	26	in.-lb.
Maximum Mounting Torque M5 Terminal Screw	—	17	17	in.-lb.
Module Weight (Typical)	—	160	160	Grams
V Isolation	V_{RMS}	2500	2500	Volts

* $T_{\text{j}} = 125^{\circ}\text{C}$, $I_{\text{G}} = 1.0\text{A}$, $V_{\text{D}} = 1/2 V_{\text{DRM}}$

Electrical and Thermal Characteristics, $T_{\text{j}} = 25^{\circ}\text{C}$ unless otherwise specified


Characteristics	Symbol	Test Conditions	CM431290/CM431690	Units
Blocking State Maximums				
Forward Leakage Current, Peak	I_{DRM}	$T_{\text{j}} = 125^{\circ}\text{C}$, $V_{\text{DRM}} = \text{Rated}$	15	mA
Reverse Leakage Current, Peak	I_{RRM}	$T_{\text{j}} = 125^{\circ}\text{C}$, $V_{\text{RRM}} = \text{Rated}$	15	mA
Conducting State Maximums				
Peak On-State Voltage	V_{TM}	$I_{\text{TM}} = 270\text{A}$	1.4	Volts
Switching Minimums				
Critical Rate-of-Rise of Off-State Voltage	dv/dt	$T_{\text{j}} = 125^{\circ}\text{C}$, $V_{\text{D}} = 2/3 V_{\text{DRM}}$	500	Volts/ μs
Thermal Maximums				
Thermal Resistance, Junction-to-Case	$R_{\theta(\text{J-C})}$	Per Module	0.3	$^{\circ}\text{C/Watt}$
Thermal Resistance, Case-to-Sink (Lubricated)	$R_{\theta(\text{C-S})}$	Per Module	0.2	$^{\circ}\text{C/Watt}$
Gate Parameters Maximums				
Gate Current-to-Trigger	I_{GT}	$V_{\text{D}} = 6\text{V}$, $R_{\text{L}} = 2\Omega$	100	mA
Gate Voltage-to-Trigger	V_{GT}	$V_{\text{D}} = 6\text{V}$, $R_{\text{L}} = 2\Omega$	2.0	Volts
Non-Triggering Gate Voltage	V_{GDM}	$T_{\text{j}} = 125^{\circ}\text{C}$, $V_{\text{D}} = 1/2 V_{\text{DRM}}$	0.25	Volts

CM431290, CM431690
Dual SCR POW-R-BLOK™ Modules
 90 Amperes/1200-1600 Volts




CM431290, CM431690
Dual SCR POW-R-BLOCK™ Modules
 90 Amperes/1200-1600 Volts

**MAXIMUM ON-STATE POWER DISSIPATION
(REVERSE PARALLEL CONNECTION)**




NOTE: THE CURVES INDICATE THE RELATIONSHIP BETWEEN THE AVERAGE ON-STATE POWER DISSIPATION PER MODULE AND THE RMS ON-STATE CURRENT.

**MAXIMUM ALLOWABLE CASE TEMPERATURE
(SINGLE PHASE BRIDGE CONNECTION)**




NOTE: THE CURVES INDICATE THE RELATIONSHIP BETWEEN THE CASE TEMPERATURE AND THE DC OUTPUT CURRENT (FOR TWO ELEMENTS) WHEN USED IN THE SINGLE PHASE BRIDGE CONFIGURATION.

**MAXIMUM ON-STATE POWER DISSIPATION
(SINGLE PHASE BRIDGE CONNECTION)**




NOTE: THE CURVES INDICATE THE RELATIONSHIP BETWEEN THE AVERAGE ON-STATE POWER DISSIPATION AND THE DC OUTPUT CURRENT FOR THE SINGLE PHASE BRIDGE CONFIGURATION (POWER DISSIPATION EXPRESSED FOR EACH MODULE AND DC OUTPUT CURRENT EXPRESSED FOR THE PAIR)

**MAXIMUM ALLOWABLE CASE TEMPERATURE
(THREE PHASE BRIDGE CONNECTION)**



NOTE: THE CURVES INDICATE THE RELATIONSHIP BETWEEN THE CASE TEMPERATURE AND THE DC OUTPUT CURRENT (FOR THREE MODULES) IN THE THREE PHASE CONFIGURATION.

**MAXIMUM ON-STATE POWER DISSIPATION
(THREE PHASE BRIDGE CONNECTION)**



NOTE: THE CURVES INDICATE THE RELATIONSHIP BETWEEN THE ON-STATE POWER DISSIPATION (PER MODULE) AND THE DC OUTPUT CURRENT (FOR THREE MODULES) IN THE THREE PHASE BRIDGE CONFIGURATION.