





PRODUCT NO	PLASTIC MAT'L	COLOR	TERMINAL MAT'L	TERMINAL PLATING
86730-001	PBT	BLACK	PHOSPHOR BRONZE	0.2um MIN Au OVERPLATE
-101	PBT	BLACK	PHOSPHOR BRONZE	0.762um MIN Au OVERPLATE
-301	PBT	BLACK	PHOSPHOR BRONZE	0.381um MIN Au OVERPLATE
401	PBT	BLACK	PHOSPHOR BRONZE	3.81um MIN SnPb OVERPLATE
-002	PBT	BLUE	PHOSPHOR BRONZE	0.2um MIN Au OVERPLATE
-102	PBT	BLUE	PHOSPHOR BRONZE	0.762um MIN Au OVERPLATE
-302	PBT	BLUE	PHOSPHOR BRONZE	0.381um MIN Au OVERPLATE
402	PBT	BLUE	PHOSPHOR BRONZE	3.81um MIN SnPb OVERPLATE

OBSOLETE

OBSOLETE



SECTION Y - Y





NOTES:-

- HOUSING MAT'L IS PER UL 94V-0
- PRODUCT TO BE MATED WITH 0.5mm SQ PIN.
- PRODUCT DESCRIPTION CODE :

XXXXX - XXXLF
LEAD FREE ④
EXTENSION NUMBER
BASE NUMBER

- 86730-XXXLF IS SAME AS 86730-XXX.THE SUFFIX "LF" IS ADDED JUST FOR EASY LEAD FREE IDENTIFICATION
- THE HOUSING WILL WITHSTAND EXPOSURE TO 200°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- A $\triangle$ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

CONFIDENTIAL

rev ecn no dr date K S04-0271 KBM 2004-12-21 L S06-0236 KHL 2006-07-17 M S09-0252 NBR 2009-08-10 - - - - H S50056 BSL 1995-03-23 J S04-0049 JPEH 2004-03-19				www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		MM 		
				TOLERANCES UNLESS OTHERWISE SPECIFIED											
				Dr	J. TAN	2004-08-03	ANGULAR	LINEAR	0.X	±-	size A3	Scale 10:1			
				Eng	JPEH	2004-08-03			0.XX	±0.25					
Chr	KH LEE	2009-08-10	0°	±3°	0.XXX	±-			ECN	S09-0252					
Appr	JOEY NG	2009-08-10	Product family				MINITEK	Spec ref -							
		title MINITEK JUMPER MINITEK					dwg no 86730	Rev. M							
		catalog no -													
		CUSTOMER										sheet 1 of 1			